

High Temperature Pressure Data Logger Part of the NOMAD® Family

OM-CP-PR140



- ✓ Operates up to 140°C (284°F)
- ✓ Submersible (IP68)
- ✓ User Replaceable Battery
- ✓ Rugged
- ✓ Programmable Start Time
- ✓ Software Battery Life Indicator

The OM-CP-PR140 is a pressure data logger designed for use in autoclave validation and mapping. This rugged device can withstand temperatures up to 140°C (284°F) and is completely submersible (IP68).

The OM-CP-PR140 is built with a precision stainless steel pressure gauge. The device has an accuracy of ±0.03 Bar (±0.435 psi), which can be achieved over a wide temperature range, from 20 to 140°C (68 to 284°F).

The OM-CP-PR140 can be programmed to take readings as often as once per second (1 Hz), and has non-volatile memory that can store up to 32,700 measurements.

Simply place the OM-CP-PR140 in the OM-CP-IFC400 docking station, connect to an available USB port on your computer, and the device can be started, stopped or downloaded using our user friendly software. Graphical, tabular and summary data is provided for analysis and can be viewed in psia, mmHg, bar, Torr and kPa. The data can also be automatically exported to Excel® for further calculations. The storage medium is non-volatile solid state memory, providing maximum data security even if the battery becomes discharged.


Specifications

Pressure Sensor: Semiconductor strain gauge

Pressure Range: 0 to 5 bar (0 to 72.5 psia)

Pressure Resolution: 0.1 mBar (0.0015 psia)

Calibrated Accuracy: ±0.03 bar (±0.435 psi) (20 to 140°C/68 to 284°F)



OM-CP-IFC400, Windows® software displays data in graphical or tabular format.

Pressure Response Time: 0.1 ms (10 to 90% FSR)

Repeatability: ±0.5% FSR; ±0.2% typical

Reading Rate: 1 second to 1 every 24 hours

Memory: 32,700 readings; software configurable memory wrap

Start Modes: Software programmable immediate start or delay start up to six months

Real Time Recording: May be used with PC to monitor and record data in real time

Calibration: Digital calibration through software

Calibration Interval: Monthly calibration recommended

Data Format: psia, bar, mbar, atm, Torr, Pa, kPa, MPa, mmHg, inHg, inH₂O, mH₂O, foot, meter

Battery Type: 3.6V lithium battery included; user replaceable

Battery Life: 2 years typical

Time Accuracy: ±1 minute/month at 20°C



OM-CP-PR140 data logger and OM-CP-IFC400 docking station shown actual size.

Computer Interface: USB (OM-CP-IFC400 interface cable required); 125,000 baud

Software: XP SP3/Vista/Windows 7 (32- and 64-bit)

Operating Environment: -20 to 140°C (-4 to 284°F) 0 to 100% RH, may be used above 60°C (140°F) for up to 8 hrs per 24 hr period

Dimensions: 50.8 L x 25.4 mm dia. (2.0 x 1.0")

Weight: 85 g (3 oz)

Enclosure: Stainless Steel

To Order Visit omega.com/om-cp-pr140 for Pricing and Details	
Model No.	Description
OM-CP-PR140	High temperature pressure data logger
OM-CP-PR140-CERT†	High temperature pressure data logger and NIST calibration certificate
OM-CP-IFC400	Docking station with USB cable, software and manual
OM-CP-BAT110	Replacement 3.6V high temperature lithium battery

Comes complete with 3.6V lithium battery. Operator's manual and USB interface cable are included with the OM-CP-IFC400 software/cable package (required for data logger operation, sold separately).

Ordering Example: OM-CP-PR140-CERT, high temperature pressure data logger with NIST calibration certificate.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters