



Voltage Data Loggers Part of the NOMAD® Family

OM-CP-VOLT101A Series



- ✓ 4 Hz Reading Rate
- ✓ Multiple Start/Stop Function
- ✓ Programmable Engineering Units
- ✓ Large Data Storage 1,000,000 Readings
- ✓ 10-Year Battery Life
- ✓ LED Alarming
- ✓ High Speed Download Capability

Voltage is one of the most fundamental and useful types of measurement performed today. Many scientific instruments and sensors provide a voltage output that represents the magnitude of some parameter being measured such as temperature, pH, flow rate, pressure, strain, etc.

The OM-CP-VOLT101A provides a low cost solution for adding recording capability to an already existing measurement system. Its high accuracy and 16-bit resolution place this product at the forefront for low level DC voltage recording devices.

This device is ideal for accurately measuring and recording battery voltages, sensor output signals, photovoltaic studies, as well as many other low level DC voltage sources. With user programmable engineering units, the user can scale the input voltage to most any type of unit desired automatically. This is a unique and very useful feature for presentations.

The OM-CP-VOLT101A is available in four different input ranges: 160 mV, 2.5V, 15V and 30V versions.

† Refer to ordering chart on next page for NIST calibration ordering information.



Data retrieval is simple. Plug the device into an available COM port and our easy-to-use software does the rest. The software converts a PC into a real-time strip chart recorder. Data can be printed in graphical and tabular format or exported to a text or Microsoft Excel file.

Specifications

Input Connection:

Removable screw terminal

Specified Accuracy Range:

Nominal range @ 25°C

Analog Conversion Time: 133 mS

Frequency Rejection: 50/60 Hz

Alarm: User selectable high and low limits; blinking LED for alarm and low battery

Start Modes: Software programmable immediate start, delay start up to 18 months in advance, multiple start/stop mode

Multiple Start/Stop Mode: Start and stop the device multiple times without having to download data or communicate with a PC

Multiple Start/Stop Mode Activation:

To Start Device: Press and hold the pushbutton and the green LED will flash twice a second. After three seconds, the green will flash rapidly for two seconds; the device has started logging.

To Stop Device: Press and hold the pushbutton and the red LED will flash twice a second; after three seconds, red will flash rapidly for two seconds; the device has stopped logging

Memory: 1,000,000 readings; software configurable memory wrap; 330,000 readings in enhanced start/stop mode

Wrap Around: Yes

Reading Rate: 1 reading every second to 1 every 24 hours

LED Functionality:

Green LED Blinks: 10 seconds to indicate logging 15 seconds to indicate delay start mode

Red LED Blinks: 10 seconds to indicate low battery and/or memory 1 second to indicate an alarm condition

Input Types and Ranges

Input Ranges	OM-CP-VOLT101A-160MV	OM-CP-VOLT101A-2.5V	OM-CP-VOLT101A-15V	OM-CP-VOLT101A-30V
Voltage Range	±160 mV	-3 to 3 Vdc	-8 to 24 Vdc	-8 to 32 Vdc
Voltage Resolution	5 µV	0.1 mV	0.5 mV	1.0 mV
Calibrated Accuracy	±0.01%	±0.05%	±0.05%	±0.05%
Input Impedance	>1 MΩ	125 kΩ	125 kΩ	125 kΩ
Overload Protection	±5V**	±50V*	±50V*	±50V*
Input Type	Differential	Single ended	Single ended	Single ended

* Indefinitely

** For 10 seconds

OM-CP-VOLT101A-15V data logger, shown actual size.



OM-CP-IFC200, Windows software displays data in graphical or tabular format.

Password Protection: An optional password may be programmed into the device to restrict access to configuration options. Data may be read out without the password

Real Time Recording: May be used with PC to monitor and record data in real time

Calibration: Digital calibration through software

Calibration Date: Automatically recorded within device

Battery Type: 3.6V lithium battery (included) user replaceable

Battery Life: 10 years typical at a 15 minute reading rate

Data Format: Date and time stamped V, mV, V, engineering units specified through software

Time Accuracy: ±1 minute/month (at 20°C, stand alone logging)

Computer Interface: USB (interface cable required); 115,200 baud

Software: WIN XP SP3, VISTA and 7 (32 and 64-bit)

Operating Environment:

-40 to 80°C (-40 to 176°F)

0 to 95% RH non-condensing

Dimensions: 64 L x 36 W x 16 mm D (2.5 x 1.4 x 0.6")

Weight: 0.9 oz (24 g)

Materials: ABS plastic

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)	
Model No.	Description
OM-CP-VOLT101A-2.5V	Voltage data logger, -3 to 3 Vdc range
OM-CP-VOLT101A-2.5V-CERT†	Voltage data logger, -3 to 3 Vdc with NIST calibration certificate
OM-CP-VOLT101A-15V	Voltage data logger, -8 to 24 Vdc range
OM-CP-VOLT101A-15V-CERT†	Voltage data logger, -8 to 24 Vdc with NIST calibration certificate
OM-CP-VOLT101A-30V	Voltage data logger, -8 to 32 Vdc range
OM-CP-VOLT101A-30V-CERT†	Voltage data logger, -8 to 32 Vdc with NIST calibration certificate
OM-CP-VOLT101A-160MV	Voltage data logger, ±160 mV range range
OM-CP-VOLT101A-160MV-CERT†	Voltage data logger, ±160 mV with NIST calibration certificate
OM-CP-IFC200	Windows software and 3.7 m (12') USB interface cable
OM-CP-BAT105	Replacement 3.6V lithium battery

Comes complete with 3.6V lithium battery. Operator's manual and USB interface cable are included with the OM-CP-IFC200 Windows® software (software is required to operate the data logger and is sold separately).

Ordering Example: OM-CP-VOLT101A-2.5V-CERT, voltage data logger, -3 to 3 Vdc with NIST calibration certificate and OM-CP-IFC200 Windows software and USB cable

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters