

Temperature Humidity Alarm with Logging Capability

OM-THA2



- ✓ Audible and Visual Alarm
- ✓ Digital Display
- ✓ Log Up To 170 Days of Data
- ✓ Relay Contacts For Remote Alarm or Auto Dialer
- ✓ Remote Sensor

The OM-THA2 is a multi-function unit that monitors temperature, relative humidity and dew point, provides for out-of-range conditions and continuously logs data. It consists of a base unit with an easy to read display and a 4.6 m (15') remote sensor probe.

The alarm function monitors temperature, relative humidity and dew point once every second. If any of the readings reach an alarm threshold, the unit generates an alarm by turning on a beeper and a dry relay contact. The relay can be connected to a telephone dialer, light or bell. The delayed alarm feature can reduce false alarms by ignoring short duration alarm conditions. The unit will also generate an alarm on probe failure.

The logger function records the temperature, relative humidity and dew point into internal non-volatile memory at a user specified interval. The recording is performed continuously after the unit is turned on. No computer setup is necessary to start logging, and all logging settings can be viewed or changed through the front panel functions. When the internal memory becomes full the recording rolls over, over-writing the oldest recorded data. Logged data can be reviewed on a computer using the included Windows software while continuously recording new data.

All the operating settings of the OM-THA2 can be changed from the front panel, without the need for a computer. The two line display provides an easy to read means of viewing or changing settings.

Specifications

SENSOR PROBE

Operating Temperature Range:

-40 to 60°C (-40 to 140°F)



OM-THA2 shown smaller than actual size.

Windows software displays data in graphical or tabular format.

Operating Humidity Range:

0 to 95% RH non-condensing

Temperature Accuracy: ±2°F (±1°C)

Temperature Resolution: 0.1°F (0.1°C)

Humidity Sensor: Polymer capacitive

Humidity Accuracy: ±2% RH

Humidity Resolution: 0.1% RH

Temperature Sensor: Solid state

Calibration: User calibration for temperature and relative humidity

Dimensions: 9.65 L x 2.79 D cm (3.8 x 1.1")

Weight: 25 g (0.9 oz)

Cable Length: 4.6 m (15')

BASE UNIT

Operating Temperature Range:

0 to 54°C (32 to 132°F)

Storage Temperature: -18 to 54°C (0 to 130°F)

Operating Humidity: 0 to 95% RH non-condensing

Power: 12 to 24 Vac/Vdc, 0.78W alarm active

Battery Backup: 9V alkaline battery for 35 hrs operation during power outage

Relay: 5A/250V NO/NC dry contact

Dimensions:

14 L x 11.4 H x 4.1 D cm (5.5 x 4.5 x 1.6")

Weight: 245 g (8.6 oz)

ALARM

Temperature/Relative Humidity Alarm: High/low temperature and humidity alarms, condensation alarm

Alarm Delay: Up to 2 hrs, user-selectable

Alarm Indication: Audible/visual/relay

LOGGING

Sample Rate: 1 sec to 30 min, user-selectable

Data History Storage: 2 hrs to 170 days, depending on sample rate

Memory Capacity: 8150 samples for temperature, humidity and dew point

OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.



To Order	
Model No.	Description
OM-THA2	Temperature humidity alarm
OM-THA2P	Replacement remote sensor probe
OM-61-RS232-DB9	1.8 m (6') RS232 cable with DB9F termination
OM-PL-USBS	USB to RS232 converter
OM-THA2-ADAP	Replacement 115 Vac power adaptor

Comes complete with operator's manual, Windows software on CD ROM and 115 Vac power adaptor.

Ordering Example: OM-THA2, temperature humidity alarm, OM-61-RS232-DB9, RS232 cable, and OCW-1, OMEGACARESM extends standard 1-year warranty to a total of 2 years.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters