

USB-4761 8-Channel Relay/Isolated DI USB Data Acquisition Module



\$275




- Supports USB 1.1/2.0
- Bus-Powered
- 8 Relay Output Channels and 8 Isolated Digital Input Channels
- LED Indicators to Show Activated Relays
- 8 Form C Type Relay Output Channels
- High-Voltage Isolation on Input Channels (2500 Vdc)
- High ESD Protection (2000 Vdc)
- Wide Input Range (5 to 30 Vdc)
- Interrupt Handling Capability
- Suitable for DIN-Rail Mounting
- Lockable USB Cable for Rigid Connection

The USB-4761 is a relay actuator and isolated D/I module for USB bus. It provides 8 optically-isolated digital inputs with isolation protection of 2500 Vdc for collecting digital inputs in noisy environments and 8 relay actuators for serving as on/off control devices or small power switches. For easy monitoring, each relay is equipped with one red LED to show its on/off status.

The USB-4761's 8 optically-isolated digital input channels are ideal for digital input in noisy environments or with floating potentials.

Rugged Protection

The USB-4761 digital input channels feature a rugged isolation protection for industrial, lab and machinery automation applications. It durably withstands voltage up to 2500 Vdc, protecting your host



Windows software displays data in graphical or tabular format.



USB-4761, \$275, shown smaller than actual size.

system from any incidental harms. If connected to an external input source with surge-protection, the USB-4761 can offer up to a maximum of 2000 Vdc ESD (Electrostatic Discharge) protection.

Data collection is simple. Simply plug the data acquisition module into an available USB port and our easy-to-use Windows software does the rest. The software converts your PC into a real-time strip chart recorder. Data can be printed in graphical or tabular format. It can also be exported to a text or Microsoft Excel file.

Specifications

ISOLATED DIGITAL INPUT

- Channels:** 8
- Input Voltage:**
 - Logic 0: 2 V max
 - Logic 1: 5 V min (30 V max)
- Isolation Protection:** 2500 Vdc
- Opto-Isolator Response:** 25 μ s
- Input Current:** 30 Vdc/1A

RELAY OUTPUT

- Channels:** 8

- Relay Type:** SPDT (8 x Form C)
- Contact Rating:** 125 Vac @ 0.5 A, or 30 Vdc @ 1 A
- Relay on Time:** 15 ms max
- Relay off Time:** 5 ms max
- Life Span:** 2 x 10⁷
- Resistance:**
 - Contact: 50 M Ω
 - Insulation: 1 G Ω min (at 500 Vdc)

GENERAL

- Bus Type:** USB 1.1/2.0
- Software:** Windows 2000/XP
- I/O Connector:** On-board screw terminal
- Dimensions:** 80 H x 132 L x 32 mm D (3.1 x 5.2 x 1.3")
- Power Consumption:** 5V @ 100 mA typical (5V @ 400 mA max)
- Power Input:** 5 V from USB line
- Watchdog Timer:** 1.6 sec (system)
- Operating Temperature:** 0 to 60°C (32 to 140°F)
- Storing Temperature:** -20 to 70°C (-4 to 158°F)
- Storing Humidity:** 5 to 95% RH non-condensing

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
USB-4761	\$275	8-channel relay/isolated DI USB module

Comes with Windows Software and complete user manual on CD, a 1.8 m (6') USB 2.0 cable, and DIN rail mounting kit.

Ordering Example: USB-4761, 8-channel relay/isolated DI USB data acquisition module, and OMEGACARESM 1-year extended warranty for USB-4761 (adds 1 year to standard 1-year warranty), \$275 + 27 = \$302.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters