



OM-VLT

Temperature Data Logger with Built-In Printer



- ✓ Monitors, Logs, Prints and Displays Temperature Data vs Time
- ✓ Menu Driven Programming via Front Panel Keys
- ✓ 290 Historical Temperature Readings – Data Can be Printed or Sent to PC on Request
- ✓ Real Time Temperature Printing – Three Printing Modes
- ✓ Integral Temperature Display – Max/Min on Request
- ✓ Adjustable Hi/Lo Alarm Thresholds and Alarm Delay
- ✓ Local Audible/Visual Alarm Indication
- ✓ Alarm Relay for Remote Alarming Applications
- ✓ RS-232 Port for Exporting Real Time Data to PC – No Software Needed
- ✓ Low Battery, Chart Ending and No Sensor Indicators
- ✓ Extendable Remote Temperature Sensor



OM-VLT, shown smaller than actual size

Model OM-VLT is a programmable temperature data logger, strip recorder and alarm device with integral digital display. The easy to follow menu driven programming is done via the front panel keys.

The unit records, saves and prints up to 290 temperature readings at predefined intervals. The OM-VLT produces an alarm when the temperature goes out of the defined range or after the temperature remains out of range for a certain period of time. The OM-VLT prints temperature data directly via the integral printer and can also send temperature data to an external PC. Communications with a PC is done by using Windows Hyperterminal software so no additional software is required. The OM-VLT can also send alarms to an external device via the built-in relay contact.

Specifications

Temperature Sensor: Solid state IC, 10 m (33') long sensor probe wire, 5mm diameter
Temperature Measurement Range: -40 to 130°C (-40 to 266 °F)
Temperature Measurement Accuracy: ±1°C (±1.8°F)
Temperature Writing and Storage Resolution: 0.1°C (0.2 °F)
Sample Rate: Programmable between 1 and 90 minutes in 1 minute intervals
Memory: Data logger saves the last 290 measurements; logging starts as soon as the unit is turned on
Computer Interface: RS-232: 9600 baud, 8 data bits, parity none, 1 stop bit, flow control none
LEDs: Power, low battery, out of paper, sensor, min, max



Alarms: High and low temperature, end of paper, no sensor; audible (internal buzzer)/visual (alarm LED)/normally open relay contact

Audible Alarm (Internal Buzzer): Some alarms trigger the internal alarm buzzer. The buzzer can be silenced by pressing EXIT on the front of the data logger or by connecting the optional remote buzzer silencer switch (OM-VLT-SK) which momentarily shorts the buzzer silencer contacts on the data logger. The alarm buzzer can also be enabled or disabled via the data logger front panel menu programming.

Temperature Alarm Operation: If the measured temperature goes outside the maximum or minimum temperature limits for an amount of time equal to the defined alarm delay period (if any), an alarm is sent – the internal buzzer sounds (if enabled), an alarm is sent to an external device via the alarm relay contact (if enabled) and the alarm LED lights.

Disconnected Temperature Sensor Alarm Operation: If the temperature sensor is disconnected the display shows the message nOS, the alarm LED lights and the internal buzzer sounds (if enabled).

End of Paper Alarm Operation:

If the printer paper runs out, the internal buzzer sounds (if enabled), an alarm is sent to an external device via the alarm relay contact (if enabled) and the out of paper LED lights.

Alarm Relay: 1 A, 12 Vac/Vdc

Alarm Delay Range: User selectable; No delay, 10 min, 30 min, 1 hr, 2 hrs

Printing Modes: There are three printing modes; full text report (small font), time and temperature (large font), graph format

Chart Speed Accuracy: ±1%

Time Accuracy: ±80 ppm @ 75 °F (24°C)

Thermal Chart Paper

Dimensions: 50mm wide x 40m long


Display: 4 character numeric LED

Power: 12 Vac/Vdc via included Vac adaptor

Battery Backup: 9 V alkaline for up to 60 hours operation

Clock Battery: CR2032 coin cell, used for saving logged data and configuration settings and for running the real-time clock

Operating Environment: -18 to 65°C (0 to 150 °F), 0 to 95% RH non-condensing



Download data using Windows Hyperterminal - no extra software is required.

Storage Temperature:

-40 to 65°C (-40 to 150 °F)

Mounting: Vertical or horizontal, free standing, wall or panel mount (wall mount bracket included)

Dimensions:

209 W x 135 H x 69 mm D (8.2 x 5.3 x 2.7")

Weight: 1.3 Kg (2.9 lbs) including chart paper

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.		Description
OM-VLT		Temperature data logger with printer
OM-VLT-SENSOR		Spare temperature sensor, 10 m (33')
OM-VLT-PAPER		Replacement paper roll, 40 m (131')
OM-VLT-115-ADAPTOR		115 Vac/12 Vdc power adaptor
OM-VLT-230-ADAPTOR		230 Vac/12 Vdc power adaptor
OM-VLT-BAT		3.6 V lithium battery
OM-VLT-BRKT		Wall mounting bracket
OM-VLT-PACO		Paper compartment cover
OM-VLT-BACO		Battery compartment cover
OM-VLT-SK		Alarm buzzer remote silencer kit
OM-VLT-CABLE10H		Temperature sensor extension cable, 3 m (10')
OM-VLT-CABLE33H		Temperature sensor extension cable, 10 m (33')
OM-VLT-PR		24 Vdc/ 12 Vdc power reducer
OM-61-RS232-DB9		1.8 m (6') RS-232 cable DB9F termination

OM-VLT data loggers include 2 thermal chart paper rolls, wall mounting bracket, paper compartment cover, battery compartment cover, 3.6 V lithium battery, Vac/12 Vdc power adaptor, remote temperature sensor 10 m (33' long) and complete operator's manual.

Ordering Example: OM-VLT temperature data logger with printer and **OMEGACARE** SM 1 year extended warranty for OM-VLT (adds 1 year to standard 1 year warranty).

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters