



## Toroidal Conductivity System

CDTX-45T Series  
Starts at  
**\$675**



- ✓ Concentration or Conductivity Models
- ✓ Loop-Powered, AC, or Battery Versions
- ✓ Dual Alarm Relays/Analog Outputs
- ✓ Large, 2-Line Display

The CDTX-45T toroidal conductivity system is designed for online monitoring of chemically aggressive process solutions, water applications and plating bath operations. The sensor consists of 2 metallic ribbon coils that are fixed in place by the sensor jacket material. The drive coil is used to induce a current in the process solution. The second sensing coil is used to measure the current in the process solution; the magnitude of this current is proportional to the conductivity of the process solution. Toroidal sensor is available in Noryl. The sensor material is non-conductive, thereby isolating the sensor from electrical noise and ground loops that can influence the integrity of the measurement. This material also makes the sensor resistant to electrode coating. Sensors can be submersion mounted for easy installation in open tanks or pipe mounting in the optional 2" tee fitting, which is keyed to the sensor for proper alignment. Tee fitting material contains polypropylene. For larger pipe diameters, the sensor can be insertion mounted through a 1½ NPT ball valve for easy retraction. The CDTX-45TC is the concentration monitor. The monitor comes with concentration/temperature tables for sodium hydroxide, potassium hydroxide, hydrochloric acid, nitric acid, and sulfuric acid. A configurable table allows the user to enter data points for a custom concentration curve.

## Specifications

### Common Specifications

**Main Parameter Ranges:** Automatic or manual selection of one of the following display ranges; 0 to 2000 µS, 0.0 to 2.000 mS, 0.00 to 20.00 mS, 0.0 to 200.0 mS, 0 to 2000 mS, 0.000 to 2.000 S

**Accuracy:** 0.5% range (± 2 µS)

**Repeatability:** 0.2% range (± 2 µS)

**Sensitivity:** 0.05% range (± 2 µS)

**Stability:** 0.2% range per 24 hours

**Warm-up Time:** 7 sec to rated performance

**Supply Voltage Effects:** ± 0.05% of user range (dc version only)

**Response Time:** 6 sec to 90% of step input at lowest setting

**Temperature Drift:** Span or zero, 0.04% of span/°C

**Display:** Large, high-contrast, super-twist (STN) LCD; 4-digit main display with sign, 19.1 mm (0.75") seven-segment characters 12-digit secondary display, 7.6 mm (0.3") 5 x 7 dot matrix characters

**Keypad:** 4-key membrane type with tactile feedback, polycarbonate with UV coating

### Weight

**DC Transmitter Configuration:** 0.45 kg (1 lb)

**Line Powered Unit:** 0.68 kg (1.5 lb)

**Operating Ambient:** -20 to 60°C (-4 to 140°F); 0 to 95% RH, non-condensing

**EMI/RFI Influence:** Designed to EN 61326-1

**Output Isolation:** 600V galvanic isolation

**Filter:** Adjustable 0-9.9 minutes additional damping to 90% step input

**Temperature Input:** Pt1000 RTD with automatic compensation

### Sensor

**Type:** Fully isolated, toroidal electrode sensor design for direct measurement; ¾ NPT process connection



CDTX-45T1, \$675, shown smaller than actual size.

**Wetted Material:** Noryl

**Pressure Limit:** 10 bar (150 psig) maximum

**Temperature Range:** 0 to 105°C (32 to 221°F)

**Sensor Cable:** 6.1 m (20'); 6-conductor cable

### CDTX-45T1 Loop-powered Transmitter

**Power:** 18 to 35 Vdc, 2-wire

**Enclosure:** NEMA 4X (IP66), polycarbonate, stainless steel hardware, weatherproof and corrosion resistant, 112 mm<sup>2</sup> x 89 mm D (4.4 in<sup>2</sup> x 3.5")

**Mounting:** Wall or pipe mount bracket standard. Bracket suitable for either 1.5 or 2" ID U-Bolts for pipe mounting. Conduit openings two PG-9 openings with gland seals, one 1 NPT opening with plug

**Cable:** Belden twisted-pair, shielded, 22 AWG or larger

**Insertion Loss:** 18 Vdc

### CDTX-45T2 and CDTX-45T3 Dual Relay Models

**Power:** 115/230 Vac ±10%, 50/60 Hz, 10 VA max

**Enclosure:** NEMA 4X (IP66), polycarbonate, stainless steel hardware, weatherproof and corrosion resistant, 124 mm<sup>2</sup> x 139 mm D (4.9 in<sup>2</sup> x 5.5")

**Mounting:** Wall or pipe mount bracket standard; bracket suitable for either 1.5 or 2" ID U-Bolts for pipe mounting; panel mount adaptor optional

**Conduit Openings:** Three M16 openings; gland seals plus two ½" conduit adaptors, supplied but not installed

**Relays, Electromechanical:** Two SPDT, 6 A @ 250 Vac, 5 A @ 24 Vdc contacts; programmable for setpoint, phase, delay, deadband, hi-lo alarm, and failsafe; A-B indicators on main display

**Analog Outputs:** Two 4 to 20 mA outputs; output one programmable for conductivity or PID; output 2 programmable for conductivity, temperature, or TDS. Max load 500 Ω for each output



Outputs ground isolated and isolated from each other.

### CDTX-45T4 and CDTX-45T5 Battery Powered Models

**Power:** 9 Vdc alkaline battery, low battery indication at 6.75 Vdc.

Lithium 9 Vdc battery recommended for max performance

**Battery Life:** Approx 100 hrs, alkaline; use of lithium cell increases life to approx 300 hrs

**Enclosure:** NEMA 4X (IP66), polycarbonate, stainless steel hardware, weatherproof and corrosion resistant, 112 mm<sup>2</sup> x 89 mm D (4.4 in<sup>2</sup> x 3.5"); mounting options supplied with carrying handle and cable glands installed

**Analog Outputs (CDTX-45TC4):** Two 0 to 2.5 Vdc isolated outputs

**Data Logger (CDTX-45TC5):** Removable data module holds 32,000 points from two user configured channels, time of logging is user configurable; software supplied for data download and display

### Weight:

**Loop-Powered Transmitter:** 0.45 kg (1 lb)

**Other Configurations:** 0.68 kg (1.5 lb)

**Display:** Large, high-contrast, super-twist (STN) LCD 4-digit main display with sign, 19.1 mm (0.75") 7-segment characters; 12-digit alphanumeric second-line display, 7.6 mm (0.3") 5 x 7 dot matrix characters

**Keypad:** 4-key membrane type with tactile feedback, polycarbonate with UV coating, integral EMI/static shield and conductively coated window

### Ambient Temperature:

**Operating:** -20 to 60°C (-4 to 140°F)

**Storage:** -30 to 70°C (-22 to 158°F)

**Ambient Humidity:** 0 to 95% RH, non-condensing

**Location:** Designed for hazardous and non-hazardous areas



CDE-45T2, Noryl<sup>®</sup> electrode, \$405, shown actual size.

**EMI/RFI Influence:** Designed to EN 61326-1

**Output Isolation:** 600V galvanic isolation

**Filter:** Adjustable, 0 to 9.9 minutes additional damping to 90% step input

**Temperature Input:** Selectable Pt1000 or Pt100 RTD with automatic compensation

**MOST POPULAR MODELS HIGHLIGHTED!**

To Order (Specify Model Number)		
Model No.	Price	Description
<b>Conductivity Analyzer</b>		
CDTX-45T1	\$675	Loop powered 16 to 35 Vdc, 2-wire (4 to 20 mA output)
CDTX-45T2	925	120 Vac, 2 relays, two 4 to 20 mA outputs
CDTX-45T3	925	230 Vac, 2 relays, two 4 to 20 mA outputs
CDTX-45T4	925	Battery operated (9V), two 0 to 2.5 Vdc outputs
CDTX-45T5	1325	Battery operated (9V), internal data logger
<b>Concentration Analyzer</b>		
CDTX-45TC1	\$675	24 Vdc, 2-wire (single output only)
CDTX-45TC2	925	120 Vdc, 2 relays
CDTX-45TC3	925	230 Vdc, 2 relays
CDTX-45TC4	925	Battery operated, two 0 to 2.5 Vdc outputs
CDTX-45TC5	1325	Battery operated, internal data logger
<b>Sensor with 6.1 m (20') Cable**</b>		
CDE-45T2	\$405	Noryl <sup>®</sup> electrode

### Accessories

Model No.	Price	Description
CDTX-45T-JB	\$95	NEMA 4X (IP66) junction box
CDTX-45T-C(*)	1/ft	Sensor-interconnect cable; *specify length in feet, 180' max
CDTX-45T-PT	95	51 mm (2") keyed slip-fit flow cell for use with polypro sensors
CDTX-45T-SMK	160	Submersible mounting kit for PEEK <sup>™</sup> sensor
CDTX-45T-PMK	45	Panel mount kit for analyzer
FW-303	100	Reference Book: Ground Water Injection

Comes complete with operator's manual.

\*\* For cable lengths over 6.1 m (20'), order CDTX-45T-JB junction box and CDTX-45T-C(\*) interconnect cable of desired length.

Example: CDTX-45T-C100, 30.5 m (100') cable, \$100.

Ordering Examples: CDTX-45T2, 120 Vac conductivity analyzer, and CDE-45T2, toroidal conductivity cell, \$925 + 405 = \$1330.

CDTX-45T1, 16 to 35 Vac powered conductivity analyzer and CDE-45T2 toroidal conductivity cell, \$675 + 405 = \$1080.

Order Online  
**omega.com**<sup>®</sup>  
 Over 100,000 Products Available!

To download information and to order Conductivity Instrument products online, visit **omega.com**

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA

Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)

1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenpfronn, Germany

0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England

0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)

088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)

Karviná, Czech Republic

596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters