



DISSOLVED OXYGEN INSTRUMENTATION

2-Wire Isolated Dissolved Oxygen Transmitter System

DOTX-45
\$1447
Complete System



DOTX-45 transmitter,
\$737, shown smaller
than actual size.

- ✓ Reliable 3-Electrode Amperometric Sensor
- ✓ Replaceable Sensor Cartridge
- ✓ Sensor Membrane Puncture/Tear Diagnostic
- ✓ Microprocessor-Based System
- ✓ Large, Dual-Display Format
- ✓ Loop Powered, Fully Isolated

Sensor Features

The DOE-45PA dissolved oxygen sensor is a highly dependable membrane-covered galvanic sensor. The polymer membrane has hydrophobic properties to help resist fouling from biological growth and maximize diffusion of oxygen into the sensor. The DOE-45PA also has automatic temperature compensation to correct for membrane permeability errors.

Transmitter Features

The microprocessor-based transmitter is loop powered and fully isolated for high reliability. The transmitter includes devices that protect the system from power surges and brownout events. The large, high-contrast, super-twist display is readable over a wide operating temperature range, even in low-light conditions. The main display line consists of large, segmented characters with measurement units. The secondary display line displays calibration and diagnostic messages in readable dot-matrix characters. Two of four measured parameters can be displayed simultaneously. Programming is intuitive, with a 4-button, menu-driven interface. The 4 to 20 mA transmitter output can be configured to represent any portion of the measurement range. Output hold, alarm, and simulation features give the user complete control of the system output under any condition. Diagnostic messages clearly describe system conditions, which eliminates confusing error codes. The flexible calibration method includes stability monitors that check temperature and main parameter stability before accepting data.



DOE-45PA sensor,
\$710, sold separately,
shown smaller than
actual size.

Specifications (DOE-45PA Sensor)

Measuring Range: 0 to 40 ppm
Sensor Cable: 9.1 m (30')
Measurement Response Time: 90% in less than 3 minutes
Measurement Principle: Membrane covered galvanic
Electrode Material:
Cathode: Platinum
Anode: Lead
Electrolyte: Potassium chloride based
Pressure range: 0 to 150 psig @ 25°C (77°F)
Temperature Compensation: Pt100
Temperature Range: -5 to 55°C (23 to 131°F)
Minimum Flow Rate: 6 mm (0.02") per second

Membrane Thickness: 50 microns
Membrane Material: FEP (fluorinated ethylene propylene)
Wetted Materials: 316 SS, FKM, Noryl
Sensor Cable: 5-conductor
Sensor-to-Transmitter Distance: 305 m (1000')
Mounting: Submersion 1 NPT
Shipping Weight: 0.45 kg (1 lb)

Specifications (DOTX-45 Transmitter)

Performance Specifications

Displayed Parameters: Main input, 0 to 40.0 ppm
% Saturation: 0 to 200%
Loop Current: 4 to 20 mA
Sensor Temperature: 0 to 50°C (32 to 122°F)
Power: 16 to 35 Vdc

DISSOLVED OXYGEN INSTRUMENTATION



DOTX-45, \$737, with DOE-45PA, \$710 sold separately.

Main Parameter Range: 0 to 40 ppm
Repeatability: 0.1% of span or better
Sensitivity: 0.05% of span
Non-Linearity: 0.1% of span
Stability: 0.1% of span per 24 hours, non-cumulative
Warm-Up Time: 4 seconds to rated performance
Supply Voltage Effects: ±0.05% of span
Transmitter Response Time: 4 seconds to 90% of step input at lowest setting
Temperature Drift: Span or zero, 0.02% of span/°C
Temperature Compensation: 0 to 50°C (32 to 122°F), Pt1000 element; sensor is internally compensated for membrane permeability changes with temperature
Sensor-to-Transmitter Distance: 305 m (1000')
Enclosure: NEMA 4X (IP66), polycarbonate, stainless steel hardware, weatherproof and corrosion resistant, 112 H x 112 W x 89 mm D (4.4 x 4.4 x 3.5")
Mounting Options: Wall, panel, pipe, DIN rail, integral-sensor
Conduit Openings: 2-PG9 openings, 1-1 NPT center opening, cordgrips and plug included
Weight/Shipping Weight: 0.45 kg (1 lb)
Display: Large, high-contrast, super-twist LCD; 4-digit main display with sign, 19.1 mm (0.75"), 7-segment characters; 12-digit secondary display, 7.6 mm (0.3") 5 x 7 dot matrix character
Keypad: 4-key membrane type with tactile feedback, polycarbonate with UV coating, integral EMI/static shield and conductively coated window
Operating Temperature: -20 to 60°C (-4 to 140°F)
Storage Temperature: -30 to 70°C (-22 to 158°F)
Ambient Humidity: 0 to 95%, non-condensing
Location: Designed for hazardous and non-hazardous areas
EMI/RFI Influence: Designed to EN 61326-1
Voltage Range: 16 to 35 Vdc (2-wire device)
Output Isolation: 600V galvanic isolation
Transmitter Cable Type: Belden twisted-pair, shielded
Filter: Adjustable 1 to 99 seconds additional damping to 90% step input
Temperature Input: Selectable Pt1000 or Pt100, automatic compensation

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
DOTX-45	\$737	Dissolved oxygen transmitter
DOTX-45-115VAC-R2	955	Dissolved oxygen transmitter with relays
DOE-45PA	710	Dissolved oxygen sensor
PSU-93	40	Unregulated power supply
PHTX-45-SMH	191	Submersion mounting hardware, 1.8 m (6')

Accessories

Model No.	Price	Description
DOE-45PA-DOE	\$28	DO electrolyte, 4 oz bottle
DOE-45PA-EC	28	Electrolyte chamber
DOE-45PA-MH	33	316 SS membrane holder
DOE-45PA-RLE	17	Replacement lead electrode
DOE-45PA-RM	17	Replacement membranes, 5 mil 10-pack
DOE-45PA-SE	219	Submersible sensing-element body
DOE-45PA-SH	437	Submersible sensing-element holder assembly
DOE-45PA-SM	273	Submersible sensing module
ES-2036	120	Reference Book: Handbook of Drinking Water Quality 

Comes complete with wall mount bracket and operator's manual.

Ordering Example: DOTX-45, dissolved oxygen transmitter, DOE-45PA, sensor, PSU-93, unregulated power supply, \$737 + 710 + 40 = \$1487.

Order Online
omega.com[®]
 Over 100,000 Products Available!

To download information and to order Dissolved Oxygen Instrumentation products online, visit **omega.com**

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters