

OMG-ULTRACOMM2-PCI

Dual Port PCI RS-232/422/485 Interface for DOS and Windows 3.1x/95/98/ME/NT/2000/XP




\$279
Basic Model

- ✓ Dual Port RS-232/422/485 Interface
- ✓ Onboard RS-485 Auto Enable Circuit
- ✓ Each Port Designed to Maximize DOS and Windows 3.1x/95/98/ME/NT/2000/XP Communications
- ✓ 16550 Buffered UART std./16650 or 16750 Buffered UART Optional (32 or 64 Byte FIFO)
- ✓ Supports Standard PC Data Rates and "Quad" Data Rates Up to 460.8 kbps
- ✓ Supports All PCI Interrupts
- ✓ Onboard Interrupt Status Port Provides Efficient Interrupt Sharing
- ✓ Compatible with DOS, Windows 3.1x/95/NT, and Other Operating Systems
- ✓ DOS Utilities, Windows 95 INF Files, Windows NT Driver/Utility, and Help Files are Included to Simplify Installation

The OMG-ULTRACOMM2-PCI provides two field selectable RS-232/422/485 serial ports for control and automation applications. Configure both ports as RS-232 for standard serial COM: port requirements. Choose RS-422 for long distance device connections at up to 4000 feet where noise immunity and high data integrity are essential. Multi-drop up to 31 RS-485 devices to each port in a RS-485 bus for automated data collection.

Mix the interfaces in any of the interface combinations to provide maximum flexibility to your communications.



In both RS-232 and RS-422 modes, the card works seamlessly with the standard operating system serial driver. In RS-485 mode, our auto enable feature enables the RS-485 line driver during character transmission and disables the driver afterward allowing the standard COM: driver to be utilized for RS-485 communications.

A serial utility diskette is supplied with the OMG-ULTRACOMM2-PCI which includes all the Windows and DOS tools necessary to verify the installation and operation of the board. WIN 95/98/ME/NT/2000/XP drivers are included as well as support for Linux, QNX and DOS. The drivers provide IRQ sharing, advanced UART support and serial diagnostic utilities.

OMG-ULTRACOMM2-PCI, \$279, shown smaller than actual size

Specifications

- Communications Chip:** 16550
- Number of Ports:** Two RS-232/422/485
- Max. Data Rate:** 460.8 kbps
- Max. Data Distance:** up to 4000' (RS-422/485)
- Operating Temperature:** 0 to 122°F (-18 to 50°C)
- Storage Temperature:** -4 to 158°F (-20 to 70°C)
- Humidity Range:** 10 to 90% RH
- Current Specifications:** +5V @ 480 mA, ±12 V @ 50 mA
- Connector(s):** (2) DB-9P
- Dimensions:** 5.0 L x 4.2" H (12.70 x 10.67 cm)

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model Number	Price	Description
OMG-ULTRACOMM2-PCI	\$279	Dual port RS-232/422/485 interface
OMG-ULTRACOMM2-PCI-16650	293	Dual port RS-232/422/485 interface w/16650 UART upgrade
OMG-ULTRACOMM2-PCI-16750	299	Dual port RS-232/422/485 interface w/16750 UART upgrade

Comes with complete operator's manual and serial utility disk.
Ordering Example: OMG-ULTRACOMM2-PCI dual port RS-232/422/485 interface and OMEGACARESM 1-year extended warranty (adds 1 year to standard 1-year warranty), \$279 + 27 = \$306.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters