




## Dual Channel Conductivity/Resistivity Controller

CDCN-91, \$1004, shown actual size.

CDCN-91 Series  
Starts at  
**\$1004**



### Features

- ✓ 2-Channel Input
- ✓ Simultaneous Display
- ✓ AC Line-Voltage or DC Powered
- ✓ Display and/or Control:  $\mu\text{S}$ ,  $\text{mS}$ , PPM or PPB (TDS),  $\text{k}\Omega$ ,  $\text{M}\Omega$ , % Rejection, Difference, Ratio,  $^{\circ}\text{C}$  or  $^{\circ}\text{F}$
- ✓ 3 Fully Scalable 4 to 20 mA Outputs
- ✓ Up to 4 Programmable Relays
- ✓ Time Delay Relay Function
- ✓ Proportional Pulse Control Capability
- ✓ Meets USP Requirements
- ✓ Programmable Temperature Compensation
- ✓ Output Simulation for Complete System Testing
- ✓ Simple Push-Button Operation
- ✓  $\frac{1}{2}$  DIN, NEMA 4X (IP65) Enclosure with Self-Healing Window

### Application

- ✓ RO/DI System Control
- ✓ Demineralizer Regeneration and Rinse
- ✓ Scrubber, Cooling Tower and Boiler Protection
- ✓ Chemical Concentration
- ✓ Rinse Tank Water Quality
- ✓ Desalination
- ✓ Leak Detection
- ✓ Aquatic Animal Life Support Systems
- ✓ Aquaculture
- ✓ Environmental Studies

The CDCN-91 Series dual channel conductivity/resistivity controller is a two-channel input device equipped with three scalable 4 to 20 mA outputs and four programmable relays. A selector switch activates two open collector outputs in place of two of the relays for extraordinary output versatility. Dual input and advanced control capability, including percent rejection, difference and ratio calculations, together with the CDCE-91 Series conductivity sensors listed below, form the perfect measurement and control system for water treatment applications and more. Two versions are available: one accepts AC line-voltage, the other low voltage DC for power. The four-button keypad arrangement with intuitive software design is user-friendly, and the NEMA 4X (IP65) integrity of the front panel can be extended to the entire enclosure by using the optional rear cover kit.

### Specifications

#### General

**Compatible Sensors:** CDCE-90 Series standard conductivity/resistivity sensors

#### Operating Range:

**Conductivity:** 0.055 to 400,000  $\mu\text{S}/\text{cm}$   
**Resistivity:** 10  $\text{k}\Omega/\text{cm}$  to 18.26  $\text{M}\Omega/\text{cm}$  (0.055 to 100  $\mu\text{S}/\text{cm}$ )  
**TDS:** 0.001 to 999999 ppm or ppb (display limit)  
**Temperature:** PT1000:  $-25$  to  $120^{\circ}\text{C}$  ( $-13$  to  $248^{\circ}\text{F}$ )

#### Accuracy:

**Conductivity/Resistivity:**

$\pm 2\%$  of reading

**Temperature:**  $\pm 0.5^{\circ}\text{C}$

#### Power Requirements:

**100 to 240 Vac:**

$\pm 10\%$ , 50 to 60 Hz, 20 VA

**11 to 24 Vdc:**  $\pm 10\%$  reg., 0.5A max

**Display:** Alphanumeric 2 x 16 LCD

**Contrast:** User selected, 5 levels

**Update rate:** 1.5 seconds

**Current Outputs:** (3 each) 4 to 20 mA,

isolated, fully adjustable and reversible

**Max Loop Impedance:** 150  $\Omega$  @ 12V,

450  $\Omega$  @ 18V, 750  $\Omega$  @ 24V

**Update Rate:** Approx. 100 mS

**Accuracy:**  $\pm 0.03$  mA @  $25^{\circ}\text{C}$ , 24 Vdc

**Open Collector Outputs:** (2 each)

Isolated, 50 mA sink or source, 30 Vdc

max pull-up voltage

**Operational Settings:** Hi, Lo, USP,

Pulse, Off

**Hysteresis:** User adjustable

**Time Delay:** 0 to 6400 seconds

**Maximum Pulse Rate:**

400 pulses/minute

**Alarm Contacts:** (up to 4 each)

SPDT Relays

**Maximum Voltage Ratings:**

5A @ 30 Vdc or 5A @ 250 Vac

**Operational Settings:** Hi, Lo, USP,

Pulse, Off

**Hysteresis:** User adjustable

**Time Delay:** 0 to 6400 seconds

**Maximum Pulse Rate:**

400 pulses/minute



## Enclosure

**Rating:** NEMA 4X (IP65) front and back with optional NEMA 4X (IP65) rear cover kit

### Materials:

**Case:** PBT

**Window:** Polyurethane-coated polycarbonate

**Keypad:** Sealed 4-key silicone rubber




### Weight:

**CDCN-91AC:** Approx. 581 g (20.5 oz)


**CDCN-91:** Approx. 544 g (19.2 oz)

## INSTALLATION


- ✓ Front Panel provides NEMA 4X (IP65) protection
- ✓ Standard ¼ DIN panel cutout
- ✓ 102 mm (4") mounting depth
- ✓ Optional NEMA 4X (IP65) rear cover kit with knockout ports for cable access
- ✓ 158 mm (6.3") mounting depth with optional rear cover installed




Panel mounting bracket and panel gasket are included.



Optional heavy-duty wall mount bracket CDCN-91-WMB, \$52.



Optional surface mounting bracket FPM-5000-MB, \$31.



Liquid tight connector kit 3 sets per kit, FPM-5000-LTCK, \$40. Use with optional NEMA 4X (IP65) rear cover kit, FP90-4X, \$45.

**AVAILABLE FOR FAST DELIVERY!**

## To Order (Specify Model Number)

Model No.	Price	Description
CDCN-91	\$1004	Conductivity/resistivity controller DC power
CDCN-91AC	1012	Conductivity/resistivity controller AC/DC power




## Accessories

Model No.	Price	Description
FP90-4X	\$45	NEMA 4X (IP65) rear cover kit
FPM-5000-LTCK	40	Liquid-tight kit for rear cover
CDCN-91-WMB	52	Wall mount bracket
FPM-5000-MB	31	Surface mount bracket
FP90RC	17	RC filter kit for relays
CDCE-90-001	298	Conductivity cell constant = 0.01
CDCE-90-01	298	Conductivity cell constant = 0.1
CDCE-90-1	298	Conductivity cell constant = 1.0
CDCE-90-10	511	Conductivity cell constant = 10.0
CDCE-90-20	624	Conductivity cell constant = 20.0

Comes complete with operator's manual.

Additional cells available, see pages E-27 and E-28.

**Ordering Example:** CDCN-91 conductivity/resistivity controller DC power, with CDCE-90-1 conductivity cell constant, \$1004 + 298 = \$1302.



Note: This label appears on the side of the instrument case

Order Online

**omega.com**

Over 100,000 Products Available!

To download information and to order Conductivity Instrument products online, visit [omega.com](http://omega.com)

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters