

TOP-TO-BOTTOM BUNG-ENTERING TUBE MIXERS

FMXD11
\$623



- ✓ Mixing Tubes and Motors Supplied Separately in Modular Construction for Maximum Flexibility
- ✓ TEFC Electric or Air Driven Models Available
- ✓ Mix with a Non-Vortexing, Non-Aerating Action

FMXD11 mixers efficiently mix from the top of a 55-gallon drum to the bottom, without requiring removal of the drum lid. The optional IPS drum bung adaptor allows fixed mounting of the mixer to the drum. Mixers draw approximately 14 gallons of liquid (750 cp max viscosity, 1.8 S.G. max density) per minute through the 2" diameter mixing tube. Fluid temperature range is 0 to 93°C (32 to 200°F).

A shaft-mounted turbine inside the mixing tube rotates at 3450 RPM (from 300 to 3000 RPM for the air motor), creating a steady suction effect at the four upper intake ports. Liquid is forced down through the tube and forcefully expelled through the ports at the bottom of the tube, breaking up and dissolving settled particles (maximum solid size is 1/8").

FMXD11 mixers work with a non-vortexing, non-aerating action. The mixing tubes are just under 1 m (38") long. They have PTFE bearings at the center and base of the tube, and a graphite-filled PTFE seal. The shaft, turbine, mixing tube, and sleeve are 316 stainless steel.

Mixers are available with either an air-driven or electric motor.

Note: Use the air motor and the FMXD3-SK static protection kit for mixing flammable materials or in explosive environments.

CAUTION:
DO NOT USE THE AIR MOTOR WITHOUT THE FMXD3-SK ANTI-STATIC PROTECTION KIT

FMXD11, \$623, shown smaller than actual size.



Air or TEFC electric motors available. Both shown smaller than actual size.

FMXD11-AM, \$434

FPUD411, \$677

The air-driven 3/4 HP motor operates with 10 to 15 CFM air at 3.4 to 6.2 bar (50 to 90 psig), and includes a flow regulator and muffler.

Note: Use a filter/regulator and lubricator in the air supply line if the air is not filtered and lubricated.

The TEFC electric 1/4 HP motors are thermal-overload protected, and come with an on/off switch and a 3.6 m (12') three-wire cord with plug (FPUD421 supplied without plug).

Mixing Tube

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description	Ship Weight kg (lb)
FMXD11	\$623	Standard mixing tube	4.5 (10)

Mixer Motor

Model No.	Price	HP	RPM	Power	Ph	Hz	Type	Weight kg (lb)
FPUD411	\$677	1/4	3450	115 Vac	1	60	TEFC	8.1 (18)
FPUD421	706	1/4	2850	220 Vac	1	50	TEFC	8.1 (18)
FMXD11-AM	434	3/4	3000	Air motor	N/A	N/A	Air	3.6 (8)

Accessories

Model No.	Price	Description
FPUD4-SDA-P1	\$67	2" IPS polypro drum adaptor for FMXD11 mixer
FPUD4-SDA-GS1	44	2" PS galvanized steel drum adaptor for FMXD11 mixer
FPUD4-SDA-S1	176	2" IPS 316 SS drum adaptor for FMXD11 mixer
FMXD3-SK	335	Static protection kit for FMXD11 motor
FPUD345-FL	165	Filter-lubricator assembly for FMXD11-AM air motor, 3/4 FNPT connection

Accessory

Model No.	Price	Description
CH-5752	\$93	Reference Book: Analytical Chemistry for Technicians

Comes complete with operator's manual.

Ordering Examples: FMXD11, standard mixing tube, FMXD11-AM, air motor, FMXD3-SK, static protection kit, and FPUD345-FL, filter/lubricator assembly
\$623 + 434 + 335 + 165 = \$1557

FMXD11, mixing tube, FPUD411, 115 Vac motor, \$623 + 677 = \$1300.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters