

OMEGAFLEX® VARIABLE SPEED PERISTALTIC PUMPS

FPU250 Series
Starts at
\$485



FPUVS4000, \$600, shown smaller than actual size.



FPU254, \$485, shown smaller than actual size.

For a Complete Selection of OMEGAFLEX® Tubing and Accessories, See Section T Pages T-13 to T-66

- ✓ Self-Priming, Non-Siphoning
- ✓ Metal or Plastic Benchtop Case
- ✓ Fluid Contacts Tubing Only
- ✓ Supplied with Tubing and Tube Unions
- ✓ 0.36 to 1600 mL/min Water Capacity

FPU250 Series OMEGAFLEX peristaltic pumps offer a variable speed drive system. Nine ranges are available from 0.36 to 800 mL/min. Dual pumpheads can provide flows of up to 1600 mL/min. They have all the benefits of the OMEGAFLEX pump line, including non-siphoning, self-priming, contamination-free pumping. They're supplied with a 1.8 m (6') long, 115 Vac power cord and are enclosed in a rugged polyurethane-painted steel benchtop case. Silicone or Norprene® precision-bore tubing [230 mm (9") length] with polyethylene tubing unions is included with each pump.

SPECIFICATIONS (FPU250)

Dimensions: 156 W x 165 H x 146 mm D (6 $\frac{1}{8}$ x 6 $\frac{1}{2}$ x 5 $\frac{3}{4}$ ")
Shipping Weight: 2.7 kg (6 lb)
Power Draw: 0.5 A at 115 Vac
Max Pressure: 20 psi

SPECIFICATIONS (FPUVS4000)

Electrical: 115 Vac/60 Hz; CW/OFF/CCW switch; 1.8 m (6') power cord
Mounting: Thermofil plastic case; flanges
Dimensions: 157.5 W x 185.4 H x 261.6 mm D (6.2 x 7.3 x 10.3")
Shipping Weight: 3.1 kg (6.8 lb)
Tubing: $\frac{3}{8}$ x $\frac{3}{16}$ " OD

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Metal Case Model No.	Price	Water Range (mL/min)	Tube ID mm (in)
FPU251*	\$485	0.36 to 5.5	1.59 ($\frac{1}{16}$)
FPU252	485	3.0 to 50	4.76 ($\frac{3}{16}$)
FPU253*	485	6.0 to 90	6.35 ($\frac{1}{4}$)
FPU254	485	0.9 to 24	1.59 ($\frac{1}{16}$)
FPU255	485	8.0 to 220	4.76 ($\frac{3}{16}$)
FPU256*	485	14 to 400	6.35 ($\frac{1}{4}$)
FPU257	485	1.7 to 49	1.59 ($\frac{1}{16}$)
FPU258	485	15 to 440	4.76 ($\frac{3}{16}$)
FPU259*	485	28 to 800	6.35 ($\frac{1}{4}$)
FPUVS4000	600	240 to 2000	9.53 ($\frac{3}{8}$)
CM-4396	48	Reference Book: Chemical Process Technology	

Comes complete with Norprene tubing, a 1.8 m (6') power cord, and operator's manual. To replace standard Norprene tubing with silicone, add suffix "-SL" to model number. No additional charge.

For units powered by 230 Vac @ 60 Hz, add suffix "-230VAC" to model number and \$10 to price.

* Models available with dual head option. To order dual head units with two separate outputs, add suffix "-DUAL" to model number and \$15 to price.

Ordering Examples: FPU252, variable speed peristaltic pump with plastic case, water range of 3.0 to 50 mL/min and tube with $\frac{3}{16}$ " inner diameter, \$485.

FPUVS4000, variable speed peristaltic pump, water range of 240 to 2000 mL/min, and tube with $\frac{3}{8}$ " I.D., \$600.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters