

ECONOMICAL IN-LINE FLOWMETERS

CAPACITY: 0.2 to 15 GPM of Water

FL-6400A Series

\$701

All Models



Optional †

- ✓ ±2% Full Scale Accuracy
- ✓ Direct-Reading Scale for Water
- ✓ For Corrosive Fluids
- ✓ For High-Pressure Systems
- ✓ Mounts in Any Position
- ✓ Vertical Connections for In-Line Mounting
- ✓ ±1% Repeatability
- ✓ High Viscosity Immunity
- ✓ 116°C (240°F) Standard, 204°C (400°F) Optional

OMEGA® FL-6400A in-line flowmeters are designed for use with many caustic or corrosive fluids. These meters feature stainless steel construction, and because of the unique construction design, they can be mounted in any position. The FL-6400A flowmeters have direct-reading scales for water on the metering tube, and, due to the sharp-edged orifice float, variances in viscosity have only a minimal effect. FL-6400A flowmeters feature a unique spring-bound design flow rate indicator, which can be used with both clear and opaque liquids for maximum versatility.


SPECIFICATIONS

Accuracy: ±2% FS
Repeatability: ±1%
Connections: ½ FNPT
Dimensions: 61.0 x 53.6 mm (2.4 x 2.11") for 116°C (240°F) units
Length: 168 mm (6.6") for all units
Max Pressure: 413.7 bar (6000 psig)
Max Temperature: 116°C (240°F)
Shipping Weight: 1.34 kg (2.95 lb)
Metering Tube: 316 SS
Float: 316 SS
Spring: 316 SS
Seals: FKM
Magnet: Polyphenylene sulfide/ceramic


FL-6404A-316, \$701, shown actual size.

For cutaway drawing of this unit, see page B-7.

For correlation equations for use with other fluids, see page B-8.



MOST POPULAR MODEL HIGHLIGHTED!



To Order (Specify Model Number)

Model No.	Price	Range LPM (GPM)
FL-6402A-316	\$701	0.8 to 7.5 (0.2 to 2.0) water
FL-6404A-316	701	2 to 19 (0.5 to 5.0) water
FL-6412A-316	701	3 to 38 (1.0 to 10) water
FL-6416A-316	701	4 to 56 (1.0 to 15) water
FW-345	59	Reference Book: Boiler Control Systems Engineering

Comes complete with operator's manual.

† For NIST certificate, add suffix "-NIST" to model number and \$275 to price.

For 204°C (400°F) units add suffix "-H" to model number and \$181 to price.

Ordering Examples: FL-6412A-316, water flowmeter, 10 GPM, \$701.

FL-6402A-316-H, 204°C (400°F) water flowmeter, 2 GPM, \$701 + 181 = \$882.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters