

HOT WIRE ANEMOMETER WITH REAL TIME DATA LOGGER



HHF-SD1


£335



- ✓ Slim Probe, Ideal for Grilles and Diffusers
- ✓ Type K or J Thermocouple Input
- ✓ Real Time SD Memory Card Data Logger
- ✓ LCD with Green Light Backlighting
- ✓ Velocity and Air Temperature Measurements
- ✓ RS232/USB Interface (Optional Cable)

The OMEGA® HHF-SD1 combination hot wire and standard thermistor anemometer with SD card data logger has multiple features that make it suitable to use in such applications as environmental testing, balancing of fans/motors/blowers, air conveyors, clean rooms, and flow hoods. What sets the HHF-SD1 apart from other hot wire anemometers is that it incorporates a real-time SD card data logger.


The HHF-SD1 measures velocity, and air temperature, and has an input socket that accepts a Type J or K thermocouple that can be used as a highly accurate thermometer. The integrated hot wire and standard thermistors provide fast and accurate readings-even at low velocities. The HHF-SD1 is innovative and easy to operate. Download data from the SD card into an Excel spreadsheet without the need for special software.



Free Thermocouple Included!

This model includes a free 1 m (40") Type K insulated beaded wire thermocouple with subminiature connector and wire spool caddy. **Order a Spare!**
Model No. SC-GG-K-30-36, £10.

Type K thermocouple (included).



Telescoping probe (included).



2GB-SD card (included)



HHF-SD1, £335.

C



SPECIFICATIONS

Display: 52 x 38 mm (2.05 x 1.5") LCD with green backlight (on/off)

Measurement Units:

Velocity: m/s, km/h, ft/min, knots, mile/hr

Temperature: °C or °F

Sensor Construction:

Glass bead thermistor

Sampling Time:

Auto: 1 to 3600 seconds

Manual: Push the data logger button once; will save data one time

Memory Card: SD memory card

Temperature Compensation:

Automatic

Display Update: At 1 second

Data Output (RS232/USB):

With optional cable/software

Operating Temperature: 0 to 50°C (32 to 122°F)

Operating Humidity: Less than 85% RH

Power: 6 "AAA" alkaline or heavy-duty batteries (included), or 9V power adaptor (optional)

Current Draw: 15 mA DC (without SD card or backlight), 36 mA (all functions)

Weight: 515 g (1.13 lb)

Dimensions:

Instrument: 203 L x 76 W x 38 mm D (8 x 3 x 1.50")

Probe: 12 mm (0.47") diameter, 280 to 940 mm (11 to 37") length

Air Temperature Measuring Range:

0 to 50°C (32 to 122°F)

Resolution: 0.1°C (0.1°F)

Accuracy: ± 0.8°C (1.5°F)



HHF-SD1 comes complete with hard carrying case, Type K thermocouple, telescoping probe, SD card, and operator's manual.

Measurement	Range	Resolution	Accuracy (Reading)
m/s	0.2 to 5 m/s	0.01 m/s	±(5% + a) reading or ±(1% + a) full scale whichever is greater
	5.1 to 25 m/s	0.1 m/s	
km/h	0.70 to 18 km/h	0.01 km/h	
	18 to 72 km/h	0.1 km/h	
mile/h (mph)	0.50 to 11.20 mph	0.01 mph	
	11.2 to 44.7 mph	0.1 mph	
knot	0.40 to 9.70 knot	0.01 knot	
	9.7 to 38.8 knot	0.1 knot	
ft/min	40 to 3940 ft/min	1 ft/min	

(a = 0.1 m/s, 0.3 km/h, 0.2 mile/h, 0.2 knot, 20 ft/min)

Note: m/s = meters per second, km/h = kilometers per hour, ft/min = feet per minute, mile/h = miles per hour, knot = nautical miles per hour (international knot)

Type K/J Thermometer (Sensor Sold Separately)

Sensor	Resolution	Range	Accuracy
K	0.1°C	-50 to 1300°C	±(0.4% + 0.5°C)
		-50.1 to -100°C	±(0.4% + 1°C)
	0.1°F	-58 to 2372°F	±(0.4% + 1°F)
		-58.1 to -148°F	±(0.4% + 1.8°F)
J	0.1°C	-50 to 1200°C	±(0.4% + 0.5°C)
		-50.1 to -100°C	±(0.4% + 1°C)
	0.1°F	-58 to 2192°F	±(0.4% + 1°F)
		-58.1 to -148°F	±(0.4% + 1.8°F)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
HHF-SD1	£335	Data logging airflow meter with SD card-hot wire type

Accessories

Model No.	Price	Description
HHF-SD2-RP	£80	Replacement hot wire probe
SW-U101-WIN	66	Software for data logging from meters
HC-SD	20	Replacement hard carrying case
SC-SD	10.75	Soft carrying case
ADAPTER-SD	13.50	AC adaptor
USB-SD	43.50	USB cable (SW-U101-WIN software required)
RS232-SD	16.75	RS232 cable (SW-U101-WIN software required)
2GB-SD	6.70	Spare 2 GB SD memory card

Comes complete with telescoping probe, 2 GB SD card, Type K thermocouple, hard carrying case, 6 "AAA" batteries and operator's manual.
Ordering Example: HHF-SD1, data logging airflow meter with SD card, and ADAPTER-SD, AC adaptor, £335 + 13.50 = £348.50

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters