

PTFE LIQUID FLOW SENSORS

FPR1501 Series
Starts at
\$829



- ✓ Provides Highly Linear 0 to 5 Vdc Output Signal and Buffered Linear Pulse Output Signal for Totalizing
- ✓ Micro-Liquid Flow Rates as Low as 15 mL/min Can be Measured with High Precision
- ✓ Usable with a Variety of Low-Viscosity Liquids, Including Many Corrosive Liquids
- ✓ Certificate of Conformance Included



FPR1501, \$829, shown larger than actual size.

FPR1501 Series flow sensors can measure extremely low flow rates from 15 mL/min. They are suitable for a wide variety of industrial, commercial, and laboratory flow applications.

Because the FPR1501 flow sensors have only PTFE and sapphire wetted surfaces, it is anticipated that they will replace conventional glass tube and ball flowmeters in many applications in which an electrical signal proportional to flow rate is desirable, even in very corrosive applications in which the liquid is low in viscosity (i.e., less than 10 centistokes).

Models use a Pelton-type turbine wheel to determine the flow rate of the liquid. The rotation rate of the turbine wheel is linear over a large dynamic range. The electro-optical system consists of a diode emitting energy in the infrared spectrum. Light energy is interrupted and passed from 8 small holes in the small turbine wheel. This reflected light energy is detected by a photodiode.

Thus, as the turbine wheel rotates in response to the liquid flow rate, electrical pulses are generated. Processing circuitry provides a DC voltage output and buffered square-wave output pulses that are proportional to the flow rate.



SPECIFICATIONS

Output Signal: 0 to 5 Vdc, adjustable $\pm 20\%$ (typical) and pulse output from 0 to 300/500 pps (typical) @ 7.5 Vdc peak pulse height-linear

Power Requirements: 12 to 15 Vdc regulated, 50 mA

Standard Sensor Material: PTFE, sapphire, Perfluoroelastomer gasket; PFA compression tube fittings

Pressure Rating: 4 bar (60 psig) max

Temperature Rating:

0 to 70°C (32 to 158°F)

Temperature Sensitivity: $\pm 0.2\%/^{\circ}\text{C}$

Accuracy: $\pm 1\%$ FS

Repeatability: $\pm 0.2\%$ FS from 20 to 100% of rated max flow

Dimensions: 55.6 x 48.0 x 58.9 mm (2.19 x 1.89 x 2.32") not including fittings

Applicable Liquids: Many low-viscosity (<10 centistokes) liquids; check compatibility with wetted materials; specify liquid when ordering

■ MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	Max ΔP	Range	Tube
FPR1501	\$829	10 psi	15 to 100 mL/min	1/8"
FPR1502	829	10 psi	25 to 200 mL/min	1/4"
FPR1503	829	10 psi	50 to 500 mL/min	1/4"
FPR1504	829	6 psi	100 to 1000 mL/min	1/4"
FPR1505	829	10 psi	0.2 to 2.0 L/min	1/4"
FPR1506	904	10 psi	0.5 to 5.0 L/min	3/8"

Accessories

Model No.	Price	Description
FPR1500-PW	\$85	Power supply, 115 Vac to 12 Vdc
FPR1500-230PW	85	Power supply, 230 Vac to 12 Vdc and European plug
DPF51	145	Analog input panel meter
GE-1400	110	Reference Book: Flow Measurement

Comes complete with 0.9 m (3') long cable with pigtailed, certificate of conformance, and operator's manual.

Ordering Examples: FPR1506, flow sensor with 0.5 to 5.0 L/min range, \$904.
FPR1501, flow sensor, FPR1500-PW, power supply, \$829 + 85 = \$914.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters