

PVDF TURBINE METER



FTB891



FTB891 shown larger than actual size.

- ✓ Indicates Both Rate and Total
- ✓ Field Replaceable Internal Rotor
- ✓ FM Approved
- ✓ Battery Operated (Included)
- ✓ For Use with Many Aggressive Chemicals
- ✓ GPM and LPM Display

The OMEGA® FTB890 industrial meter turbines are available with either ½ or 1 NPT fittings. Each turbine is designed to work with onboard computer electronics and/or with one of several accessory modules that can interface to a wide variety of reporting and collecting devices.

Liquid flows through the turbine housing causing an internal rotor to spin. As the rotor spins, an electrical signal is generated in the pickup coil. The electrical signal provides the output necessary to operate the on-board computer electronics for local indication. The display can be installed directly on the turbine, or one of several accessory modules that transmit the signal to external equipment.

SPECIFICATIONS

Accuracy:

Linear Range:

- ½" Size: 10:1 @ ±2% of reading;
- 1" Size: 10:1 @ ±1.5% of reading

Extended Range:

- ½" Size: 20:1 @ ±5.0% of reading;
- 1" Size: 20:1 @ ±5.0% of reading

Repeatability: ±0.3%

Pressure Rating: 100 PSIG (6.9 bar)

Wetted Components:

Housing: PVDF

Journal Bearings:

Ceramic (98% Alumina)

Shaft: Ceramic (98% Alumina)

Rotor and Supports: PVDF

O-Rings: FKM

Operating Temperature Range:

With Remote Electronics:

-10 to 60°C (14 to 140°F)

No Electronics: -28 to 82°C

(-20 to 180°F)

Battery Life: 5 years nominal

Power: Two 3V lithium batteries (included)

Viscosity: Calibrated to 1 cSt (water) meters with display can be used for fluids up to 100 cSt with field calibration

FM Approvals: Turbine meters with display and no accessories are FM approved for Class 1 Div. 1 hazardous environments

Note: Outputs and accessories are not designed for hazardous environments

Accessories for Turbine Meters With the Display:

The FLSC790-MA provides a 4 to 20 mA or 0 to 5 Vdc output for rate indication. Requires field calibration. The 4 to 20 mA dc is a two-wire system requiring 8 to 30 Vdc power (24 Vdc recommended).

The FLSC790-P pulse output Module provides an unscaled open collector sinking output operating on an applied voltage of 0 to 60 Vdc. The output is a squarewave pulse with an amplitude that is equal to the supplied voltage.

The FLSC790-P-DC external power module for the FLSC790-P allows for 9 to 30 Vdc external power for the pulse output. Internal batteries in the display can be used as an auxiliary power source.

The FTB790-RK remote kit allows remote mounting of display electronics. This option expands the applications into wider fluid temperature ranges to -40 to 121°C (-40 to 250°F). LCD display can be mounted up to 90 m (300') from the turbine meter.

The FTB790-RK-FM is an FM approved Remote Kit. It allows



FTB891 shown larger than actual size.

Field replaceable rotor included. Replacements available, order FTB891-RK.

the display electronics to be mounted in a hazardous area up to 30 m (100') from the turbine meter and for fluid temperatures of from -40 to 121°C (-40 to 250°F).

The FLSC790-BATT is the replacement battery for the display electronics. Batteries provide 5 years of actual use.

The FLSC790-90D is a 90° mounting adaptor designed to allow displays to be mounted 90° from the standard position.

To Order Visit omega.com/ftb891 for Pricing and Details

Model No. with Display	Model No. without Display**	Range GPM (LPM)	Extended Range Low Flow***	FNPT Size	Max Pressure Drop (psi)	Dimensions cm (inch)			Weight kg (lb) includes display
						Height	Width	Length	
FTB891	FTB891-ND	1.2 to 12 4.5 to 45.4	0.6 (2.27)	1/2	10	8.1 (3.2)	5.3 (2.1)	18.5 (7.3)	0.6 (1.3)
FTB893	FTB893-ND	5-50 (18.9-190)	2.5 (9.5)	1	6	8.4 (3.3)	7.1 (2.8)	20.6 (8.1)	0.8 (1.9)

** Requires signal output module model **FLSC790-P-ND**, ordered separately.

*** Extended low flow range and field calibration for viscosity not available on “-ND” (no display) units.

Field Installable Options and Accessories

Model Number	Description
FLSC790-MA	4 to 20 mA/0 to 5 Vdc output module
FLSC790-P	††Pulse output module (open collector output)
FLSC790-P-DC	External power module for FLSC790-P (9 to 30 Vdc)
FTB790-RK	Remote display kit module
FTB790-RK-FM	FM approved remote display kit module
FLSC790-P-ND	††Pulse output for models without displays (“-ND” suffix) open collector output
FLSC790-90D	90° display mounting adaptor

Except as noted, options and accessories are for display models only. Only one module can be installed per unit.

†† Customer supplied pull-up resistor required 820Ω (min).

Replacement Parts

Model No.	Description
FLSC790-BATT	Two 3V replacement batteries
FTB891-RK	Rotor assembly replacement kit for FTB891
FTB893-RK	Rotor assembly replacement kit for FTB893
FTB891-ORING	FKM O-ring for FTB891 union fitting
FTB893-ORING	FKM O-ring for FTB893 union fitting
FTB899-ORING	Computer cover O-ring

Comes complete with field replaceable rotor, two 3V lithium batteries and operator's manual.

Ordering Examples: FTB893, 1" turbine meter.

FLSC790-MA, field installable 4 to 20 mA/0 to 5 Vdc output.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters