

CAPACITANCE CONTINUOUS LEVEL MEASUREMENT PROBES

LV3000/4000 Series
Starts at

\$846



LV4021-24, \$714,
shown smaller
than actual size.

- ✓ Can Operate at High Temperatures and Pressure
- ✓ Unaffected by Coating Media
- ✓ Accurate and Reliable Measurement
- ✓ Easy, Economical Installation
- ✓ Rugged Construction
- ✓ No Moving Parts
- ✓ Compatible with Both Conductive and Non-Conductive Media
- ✓ Wide Range of Applications/Industries (e.g., Water, Oils, Corrosives)
- ✓ Sanitary Mount Available

The LV3000/LV4000 Series continuous level measurement probes are flexible, cost-effective solutions for applications involving liquids, pastes, and some solids. The built-in (one-piece) electronic module provides a 4 to 20 mA output (2-wire) signal that is proportional to the process level. Zero and span adjustment helps account for various media, tank dimensions, rod lengths, and positions of installation.

OMEGA® offers these probes in several different models. The user must choose the probe that suits his or her application and install it in the proper location. When submerged, the probe must be able to produce enough capacitance variance. The probe's success depends on these important factors:

A) Conductive materials can cause a short circuit between a bare stainless steel probe and the tank wall. For this situation, we recommend using ECTFE/ETFE sleeved coatings on the rod surface.

iSeries CNI16D33 controller, \$245, shown smaller than actual size. Visit omega.com/cni_series



B) Material buildup affects the accuracy of RF capacitive measurements. Additional adjustment to the probe's sensitivity is therefore recommended.

Housings must be compatible with the requirements for hazardous, washdown, wet, or dusty environments. For explosion-proof environments, the housing may need to be certified. In addition, the active probe might need to be intrinsically safe or have an intrinsic safety barrier.

The electronic circuitry of the probe performs several functions, such as rectifying and filtering the incoming power, generating the radio frequency signal, and measuring the changes in current flow.

SPECIFICATIONS (LV3000 SERIES)

Accuracy: 0.5%
Repeatability: ±1 mm
Level Indication:
Bar graph, 0 to 1000%
Process Connection:
¾ to 1½ NPT, Tri-Grip™ or flange
Wetted Material: 316 SS or PTFE
Enclosure Material: Aluminum die cast
Max Pressure: 290 psi (20 bar)
Operating Temperature: -10 to 120°C
(14 to 248°F)
Class Protection:
LV3000: NEMA 4 (IP65)
LVCN410: IP40
Max Probe Length: 1.8 m (6')
Dimensions:
Aluminum Die-Cast Head:
89 W x 108 mm H (3.5 x 4¼")
Diameter of Probe: 16 mm (5⁄8")
Electrical Connection: Cable gland
with ½ NPT conduit
*Note: The LV3000 Series probes require a
LVCN400 Series controller.*

SPECIFICATIONS (LVCN410 SERIES)

Operating Voltage: 24 Vdc, 110 or
240 Vac (50/60 Hz)
Current Consumption: 4 mA
Adjustment: Zero and span
(potentiometer) and 2 switch point
(potentiometer)
Range of Sensitivity: 50 to 1000 pF
Output: 4 to 20 mA and 2-relay SPDT
LVCN411/LVCN412:
73 W x 110 H x 110 mm L
(2¾ x 4¾ x 4¾")

SPECIFICATIONS (LV4000 SERIES)

Accuracy: 0.5%
Repeatability: ±1 mm
Operating Voltage: 12 to 30 Vdc
Adjustment:
Zero and span (potentiometer)
Range of Sensitivity: 100 to 5500 pF
Frequency Oscillation: 400 kHz
Output: 4 to 20 mA (2-wire)
Process Connection:
¾ to 1½ NPT, Tri-Grip or flange
Wetted Material: 316 SS or
ECTFE/ETFE
Enclosure Material: Glass-filled nylon
or aluminum die cast
Max Pressure: 290 psi (20 bar)
Operating Temperature:
-10 to 120°C (14 to 248°F)
Class Protection: NEMA 4 (IP65)
Max Probe Length: 1.8 m (6')
Dimensions:
Nylon Head: 89 W x 64 mm H
(3.5 x 2.5")
Aluminum Die-Cast Head:
89 W x 108 mm H (3.5 x 4.25")
Diameter of Probe: 16 mm (5⁄8")
Electrical Connection:
Cable gland with ½ NPT conduit
*Note: The LV4000 Series probes require a
galvanic isolator, LI-420.*

SPECIFICATIONS (LI-420)

**Input Current from the Evaluation
Instrument:** 4 to 20 mA
Input Voltage: 22 to 24 Vdc
Output Current: 4 to 20 mA
**Output Voltage to the Transducer
at 20 mA:** 12.5 V
**Output Voltage to the Transducer
at 4 mA:** 15.5 V
Resistance per Conductor: 15 Ω
Testing Voltage:
Input/output circuit: 2000 V_{eff}
Domestic Current Demand:
300 ±60 μA
Ambient Temperature:
-20 to 70°C (-4 to 158°F)
Enclosure Dimensions:
44 W x 82 H x 110 mm L
(1¾ x 3¼ x 4¾")

LI-420, \$234, shown
actual size.



LV4121-36, \$906, shown
smaller than actual size.



To Order (Specify Model Number)		
Model No.	Price	Description of Capacitance Transmitter with 4 to 20 mA Output and Switch
LV4111-24	\$846	60 cm (24") long probe with ¼ NPT connection, with ECTFE/ETFE sleeving and nylon head
LV4121-36	906	90 cm (36") long probe with 1 NPT connection, with ECTFE/ETFE sleeving and nylon head
LV4121-48	966	1.2 m (4') long probe with 1 NPT connection, with ECTFE/ETFE sleeving and nylon head
LV4121-60	1026	1.5 m (5') long probe with 1 NPT connection, with ECTFE/ETFE sleeving and nylon head
LV3123-48-HT	1110	1.2 m (4') long probe with 1 NPT connection, with ECTFE/ETFE sleeving and aluminum die-cast head, 177°C (350°F); Remote electronics required LVCN410 Series
LVCN411	803	24 Vdc powered controller with relay and 4 to 20 mA output for LV3000 Series only
LVCN412	815	115 Vac powered controller with relay and 4 to 20 mA output for LV3000 Series only

Accessories

Model No.	Price	Description
CNI16D33	\$245	¼ DIN dual display with two 3 A relays and 24 Vdc excitation
TX4-100	35	30 m (100') spool of 4-conductor wire
FPW-15	75	15 Vdc power supply
LI-420	234	Loop isolator (required for the LV4000 Series)

Recommended Reference Book: Water Wells and Septic Systems Handbook,
FW-300, \$100
 See Section Y For Additional Books



Custom Models Available

Model No.	Base Price	Description for Built to Order Unit
LV4XYZ-LENGTH (inches)	\$660	Custom capacitance system, specify X, Y, Z from Options
LV3XYZ-LENGTH (inches)	540	Custom remote capacitance system, requires LVCN410 Series remote electronics, specify X, Y, Z from Options

Specify all length in inches. Maximum length is 96" (8') for LV4000/LV3000.

Options

Ordering Suffix	Price	Description
X-Insulation Connection		
0	N/C	316 SS rod
1	\$60 ea + 36/ft	ECTFE/ETFE sleeve
Y-Process Connection		
1	N/C	¼ NPT thread
2	N/C	1 NPT thread
3	\$150	1.5 NPT thread
4	150	1.5 Tri-Grip, sanitary
5	300	Flange 2" ANSI, 15016 316 SS
Others	Consult for price	Please specify
Z-Enclosure		
1	\$6	Glass-filled nylon with ¼ NPT conduit entry and cable gland
2	336	LV4000 Aluminum die cast with ¼ NPT conduit entry
3	342	LV4000 Aluminum die cast with cable gland entry
4	84	LV3000 Aluminum die cast with ¼ NPT conduit entry
5	5	LV3000 Aluminum die cast with cable gland entry
Length of Rod (-LENGTH)		
Specify Inches	\$24/ft	Length of rod
Sheath Length (-SH_) to Render Portion of Probe Inactive		
Specify Inches	\$24/ft	Length of sheath
High Temp to 350°F (-HT)		
Add "-HT" to Model No.	\$180	High temperature to 177°C (350°F)

Comes with complete operator's manual.

Ordering Examples: LV4111-24, 60 cm (24") level transmitter, CNI16D33, process controller, and TX4-100, multiconductor wire, \$846 + 245 + 35 = \$1126.
 LV4121-36, 90 cm (36") level transmitter, FPW-15, power supply, \$906 + 75 = \$981.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters