

HIGH-TEMPERATURE LIQUID-LEVEL SWITCHES

All Stainless Steel Construction

LV-40/50 Series

\$64



- ✓ Well Suited for Rough or Corrosive Liquids
- ✓ Water-Purifying and Medical Application Models
- ✓ High-Pressure Models up to 750 psi
- ✓ Normally Open or Normally Closed SPST Switch, User Selectable
- ✓ Mounts Vertically at Top or Bottom of Tank

Constructed entirely of 316 SS, the LV-40 single-station level switch is designed to withstand the effects of a wide range of chemicals. With a maximum operating temperature of 149°C (300°F), this switch is ideal for medical and water purification. Its small float displacement allows for high accuracy and reliability in shallow tanks and reservoirs.

See chart on page K-4 for maximum voltage/current ratings.

The LV-50 Series level switches deliver superlative performance and dependability under the most severe operating conditions. The sensor incorporates a larger float displacement and all stainless steel construction for consistent level monitoring in liquids pressurized up to 750 psi. Ideal for level sensing in chemical plants and systems, models are available for temperatures up to 249°C (480°F).

SPECIFICATIONS

Stem Material: 316 SS

Float Material: 316 SS

Operating Temperature:


-40 to 149°C (-40 to 300°F);

-40 to 249°C (-40 to 480°F) for LV-52



LV-40, \$64, shown smaller than actual size.

LV-50, \$68, shown smaller than actual size.



Pressure Rating: 150 psi for LV-40; 750 psi for LV-50 Series

Mounting: 1/8 NPT for LV-40; 1/4 NPT for LV-50 Series

Switch: SPST

Switch Actuation: Approx. 1/2 the distance from end of stem to mounting, or at halfway point of float travel

Lead Wires: 22 AWG, 24\"/>

Specific Gravity of Float:

LV-40: 0.62; LV-50: 0.64

To determine fluid specific gravity, add 0.1 to float specific gravity in clean liquids and 0.3 to float specific gravity in dirty or viscous liquids.

Solid State Relays Available!



For complete technical and ordering information, please refer to the OMEGA® Temperature Measurement Handbook®.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)			
Model No.	Price	Temp. Rating	Switch Rating
LV-40	\$64	-40 to 149°C (-40 to 300°F)	10 VA
LV-50	68	-40 to 149°C (-40 to 300°F)	20 VA
LV-51	75	-40 to 149°C (-40 to 300°F)	100 VA
LV-52	106	-40 to 249°C (-40 to 480°F)	20 VA

Ordering Example: LV-51, all stainless steel high-temperature liquid-level switch with a 100 VA rating, \$75.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters