



pH FIELD & LAB ELECTRODES

pH ELECTRODES

PHE-1478
\$60



pH Electrodes

OMEGA's glass-bodied, refillable (RF), combination pH electrodes are for general purpose laboratory measurements. The inert nature of the glass body allows these electrodes to be used in aqueous and non-aqueous solutions at temperatures up to 110°C (230°F).

The PHE-1479 has a ceramic liquid junction and a saturated potassium chloride electrolyte. This electrolyte is a laboratory standard and is suitable for most measurements. The ceramic junction has a low flat rate which minimizes sample contamination from the potassium chloride solution.

The PHE-1478 has a Porous Teflon® liquid junction and a saturated potassium chloride electrolyte. The Porous Teflon® liquid junction provides a stable, non-fouling reference contact ideal for the most demanding applications. This research grade electrode should be used when the sample has a very low or very high ionic strength, where greases or oils are present, or in biological solutions containing TRIS or large amounts of protein.



PHE-1479, \$65, shown smaller than actual size.

SPECIFICATIONS

pH Range: 0 to 14 pH

Temperature Range: -5 to 100°C (23 to 212°F)

Accuracy: ±0.02 pH

Response Time: 95% of reading within 5 seconds

Impedance: 60 MΩ at 25°C

Zero Potential: 7.0 ± 0.2 pH

Dimensions (L x D): 140 x 12 mm (5.5 x 0.47")

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	Description
PHE-1478	\$60	Teflon® liquid junction
PHE-1479	65	Ceramic liquid junction
ES-2207	99	Reference Book: Handbook of Water and Wastewater Treatment Technologies

Comes with complete operator's manual.

Note: 1 m (3') of cable length is standard, for add'l length consult engineering.

Ordering Example: PHE-1478, Teflon® liquid junction electrode, \$60.

Specialty pH Electrodes

These specialty electrodes are designed for surface and subsurface measurements of semi-soft materials. The typical applications include meats, cheese, dairy products, photographic emulsions and electrophoresis gels.

The PHE-1525 Flat style is a refillable combination pH electrode with a polymer body, Porous Teflon® liquid and a flat pH glass membrane. It can be used to measure the pH of any moist surface or inverted and used as a "one-drop" electrode. Samples as small as 100 microliters are easily measured with this inverted technique.

The PHE-1526 Spear-Point is a refillable combination pH electrode with a 9.5 mm (0.37") glass body, Porous Teflon® liquid junction and pointed pH glass bulb. It is designed for sub-surface measurements of cheese, processed meats and other soft materials. These electrodes respond quickly and are easily cleaned.



PHE-1526, \$90, shown smaller than actual size.

SPECIFICATIONS

pH Range: 0 to 14 pH

Temperature Range: -5 to 100°C (23 to 212°F)

Accuracy: ±0.02 pH

Response Time: 95% of reading within 5 seconds

Impedance: 60 MΩ at 25°C

Zero Potential: 7.0 ± 0.2 pH

Dimensions (L x D):
Flat: 140 x 12 mm (5.5 x 0.47")
Spear-Point: 150 x 9.5 mm (5.9 x 0.37")



Options for Combination Electrodes

Suffix	Description	Price
-D	Double junction	\$50
-HF	HF fluoride resistant body	50
-HT	High temperature reference	30
-HPH	High pH glass	30
-ORP	Redox (ORP) measurement	35

Options available on PHE-1478, PHE-1479, PHE-1525, PHE-1526, PHE-1523 and PHE-1524 electrodes.

Note: 1 m (3') of cable length is supplied standard; for add'l length, consult Engineering.

To Order (Specify Model Number)

Model No.	Price	Description
PHE-1525	\$70	Flat surface pH electrode
PHE-1526	90	Spear-Point pH electrode

Comes with complete operator's manual.

Note: 1 m (3') of cable length is standard; for add'l length consult engineering.

Ordering Example: PHE-1525, flat surface pH electrode, \$70.



Laboratory Electrodes

Laboratory Reference Electrodes

PHE-3216
\$60



PHE-3216D, \$80, shown smaller than actual size.

Laboratory procedures require the use of a separate reference electrode. Several standard methods and techniques for pH measurement and most ion selective electrodes require the use of a "double junction" reference electrode. The PHE-3216 is an ideal choice for this application. These gel-filled electrodes feature a replaceable Porous Teflon® liquid junction in a polymer body. They are supplied ready to use with a saturated Potassium Chloride-Silver reference cell. The double junction version uses Potassium Nitrate as the screening electrolyte although it can be easily replaced with the electrolyte of your choice. The large surface area liquid junction provides a stable, low impedance contact to the solution assuring fast and accurate measurements. The chemically inert nature of Teflon® makes the sensor difficult to foul and easy to clean.

SPECIFICATIONS

- pH Range:** 0 to 14 pH
- Temperature Range:** -5 to 100°C (23 to 212°F)
- Response Time:** Stable in 30 seconds
- Resistance:** Less than 1000Ω
- Liquid Junction:** Porous Teflon®
- Electrolytes:** Saturated Potassium Chloride-Silver
- Screening Electrolyte:** 8 Molar Potassium Nitrate
- Dimensions (L x D):** 140 x 12 mm (5.5 x 0.47")

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)


Model No.	Price	Description
PHE-3216	\$60	Single junction pH junction
PHE-3216D	80	Double junction pH junction

Comes with complete operator's manual.

Ordering Example: PHE-3216, single junction pH electrode, \$60.

Laboratory Insertable Electrodes

Lab insertables are designed for pH measurement inside narrow vessels. Small volumes in test tubes or solutions in large Erlenmeyer casks can be conveniently measured using one of these responsive electrodes. The PHE-1523 is a glass-bodied, refillable, combination pH electrode. The 5.0" insertion length allows measurement in test tubes or other narrow vessels. This electrode features full span, fast response pH glass and high flow Porous Teflon® reference junction; making it a must for any laboratory.



PHE-3216, \$60, shown smaller than actual size.

SPECIFICATIONS

- pH Range:** 0 to 14 pH
- Temperature Range:** -5 to 100°C (23 to 212°F)
- Accuracy:** ±0.02 pH with proper calibration
- Sodium Error:** 0.05 pH in 0.1 Molar Na⁺ ion at 12.8 pH
- Response Time:** 95% in 10 seconds, stable in 30 seconds
- Impedance:** 60 MΩ at 25°C
- Zero Potential:** 7.0 ± 0.2 pH
- Dimensions (L x D):** Micro: 190 x 12 mm (7.5 x 0.47")



PHE-1524, \$70, shown smaller than actual size.

The PHE-1524 is a sealed, polymer-bodied, 254 mm (10") long combination pH electrode. The length allows measurements to be made in large, deep flasks or bottles. This sensor has our full span pH glass and a gel-filled Silver Chloride reference using the trouble-free Porous Teflon® liquid junction.

Accessory

Model No.	Price	Description
ES-2186	\$125	Reference Book: Environmental Monitoring Handbook 



To Order (Specify Model Number)

Model No.	Price	Description
PHE-1523	\$75	Glass body pH electrode
PHE-1524	70	Polymer body pH electrode

Comes with complete operator's manual.

Ordering Example: PHE-1523, glass body pH electrode, \$75.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters