

PUMP UP/PUMP DOWN LEVEL CONTROLS

No Hazardous Mercury Switches Required


LV600 Series
Starts as

\$33



- ✓ Use One Switch for Differential or High/Low Control
- ✓ Adjustable Level Differential from 15.2 cm to Over 30.5 m (6" to Over 100')
- ✓ Case and Cable Hermetically Sealed by Plastic Injection Molding
- ✓ Circular and Rectangular Designs

The LV600 Series unique float level switches provide an economical means of pump-up/pump-down level control with just one level switch. The ON/OFF differential is set by adjusting the length of cable over which the LV600 is allowed to float. Depending on whether the LV600 is floating with the cable UP or DOWN (see drawing), the 15 amp relay is on or off. The relay changes state when the LV600 is above or below the fixed point by 80% of the cable length. For example, if the cable is fixed for 3 m (10') of free cable, the LV600



will trigger at 2.5 m (8') above and below the fixed point. Thus, turbulence will generally not cause false switching.

The cable can be fixed to a pipe, or the accessory counterweight can be used by slipping it over the cable (see drawing). The mechanical SPDT switch has no potentially dangerous mercury, is rated for

15 A at 250 Vac, and can switch more than 100,000 times. The internal microswitch relay carries UL and CSA approvals. The case and cable are hermetically sealed by a two-step plastic injection molding process to ensure a leak-tight seal.

SPECIFICATIONS

Minimum Fluid Specific Gravity:

0.62 for LV610; 0.72 for LV620

Min/Max Level Differential:

Approximately 152 mm (6") to 3', depending on cable length

Operating Temperatures: PVC Cable;

Switch Rating: SPDT, 15 A @ 250 Vac, -25 to 50°C (-13 to 122°F); Neoprene Cable; -25 to 50°C (-13 to 122°F)

Operating Pressure: 75 psig at 21°C (70°F) Pressure rating decreases with increasing temperature

Wetted Surfaces: Polypropylene body and PVC or Neoprene cable

Counterweight: Polypropylene 50.8 mm diameter x 57.1 mm H (2" diameter x 2.25" H)

Caution:

Level switches are manufactured to the highest quality specifications. However, due to their economical construction, they should be used only for applications where, in the event of product failure, the risk of damage to equipment or personnel would be minimized. In the case of level switches, one or two back-up switches should also be used to insure that failure of any one switch will be mitigated by the back-up level switches. The user should periodically inspect the product's performance in the actual application. Use of the products beyond the recommended capabilities and lifespan are specifically not recommended.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)					
Model No. PVC Cable	Price	Model No. Neoprene® Cable	Price	Weight kg (lb)	Cable Length m (ft)
Rectangular Design					
LV611-P	\$33	LV611-N	\$34	0.23 (0.5)	0.46 (1.5)
LV612-P	49	LV612-N	63	0.64 (1.4)	4.5 (15)
LV613-P	102	LV613-N	144	1.55 (3.4)	13.7 (45)
LV614-P	128	LV614-N	184	2.00 (4.4)	18.3 (60)
Circular Design					
LV621-P	\$38	LV621-N	\$40	0.34 (0.75)	0.46 (1.5)
LV622-P	54	LV622-N	68	0.75 (1.65)	4.5 (15)
LV623-P	107	LV623-N	150	1.66 (3.65)	13.7 (45)
LV624-P	134	LV624-N	190	2.1 (4.65)	18.3 (60)






Accessory

Model No.	Price	Description	Weight kg (lb)
LV600-CW	\$15	Counterweight	0.23 (0.5)

Comes complete with operator's manual.

Ordering Examples: LV621-P, circular level control, 0.75 lb weight, PVC cable, and LV600-CW, counterweight, \$38 + 15 = \$53.

LV611-N, rectangular level control, 0.75 lb weight, neoprene cable, \$34.



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters