

# CAPACITIVE (RF) POINT LEVEL SWITCHES



LVCN6000/7000



All models shown  
smaller than actual size.



LVCN7214



LVCN7211



LVCN6241

- ✓ Separate Metal Reference Not Required
- ✓ Used for Liquids, Solids, Grains and Pastes
- ✓ Immune to Most Product Build-Up
- ✓ Programmable Time Delay and Sensitivity Adjustment

The LVCN6000/7000 Series is a capacitance switch ideal for low and high level detection for both liquid and solids. The LVCN6000/7000 Series can also detect level without being in contact with the product through a sight glass. Unlike other capacitance probes, the LVCN6000/7000 series can detect

any type of conductive, non-conductive or low dielectric materials with extremely accurate performance, almost complete immunity from build up, temperature changes or condensation. In applications with plastic or concrete tanks this series does not require an external reference.

The sensor operates in a manner that is similar to a simple capacitor. A high frequency oscillator is located within the tip of the probe. When the tip of the probe comes in contact with the medium, the frequency of the oscillation reaches a preset point and the detection circuit signals the switch to change state.

The LVCN6000/7000 series is a compact switch that can be made with many types of process connections, such as threaded flange or sanitary. The LVCN6000/7000 series is made with rigid rod or cable and both can be supplied in extended versions. The rigid rod is made with a strong and durable polyacetal plastic for standard units and is also available in PVC or PTFE. Probes are available in 24 Vdc (LVCN7000) or 85 to 240 Vac (LVCN6000) powered versions.

**Note:** These switches are not designed for use with mediums with high dielectrics such as mayonnaise or shampoo with high salt content.



## SPECIFICATIONS

**Application:** Level switch for liquids solids and granular

**Operating Voltage:**

LVCN7000: 12 to 30 Vdc

LVCN6000: 85 to 240 Vac

**Current Consumption:**

2 VA (LVCN7000), 4 VA (LVCN6000)

**Output:** Relay (SPDT) 5A maximum (250 Vac)

**Adjustment:** Potentiometer switch point

**Time Delay:** 1 to 20 seconds adjustable

**Frequency Oscillation:** 5 MHz

**Indication:** Led status on/off

**Electrical Connection:** Cable gland 1/2 NPT conduit (dual ports on large enclosures)

**Process Connection:** 3/4 NPT

standard, (BSP, NPT, flange or sanitary mounting optional)

**Sensor Tip:** Polyoxyimethalene (standard length only), PVC or PTFE optional

**Enclosure Material:**


LVCN7000: Nylon

LVCN6000: Aluminum

**Maximum Pressure:** 145 psi (10 bar)

**Operating Temperature:** -10 to 80°C (14 to 176°F)

**Class Protection:** NEMA 4 (IP65)



## Cable and Custom Built Assemblies

### Cable and Custom Ordering Guide LVCN6XYZ (85 to 240 Vac) or LVCN7XYZ (24 Vdc)

X	Mounting	Y	Enclosure	Z	Construction	LENGTH (L)	
1	3/4 BSP	1	Small nylon (LVCN7000)	1	316 SS rod Polyoxyimethalene tip (standard length only)	Standard length is 121 mm 4.75" unless otherwise specified maximum rigid probe length is 25 m (8')	
2	3/4 NPT						
3	1 BSP		Large nylon (LVCN6000)	2	316 SS rod PTFE tip		
4	1 NPT						
5	2" Tri-Grip™		Small aluminum (LVCN7000)	3	cable PTFE tip		
6	2" 150# SS ANSI						
7	2" 150# PVC ANSI	4	Large aluminum (LVCN6000)	4	PVC rod and tip		

## To Order

Model No.	Description	Power	Enclosure	Connection
LVCN6241	Level switch 316 SS rod/Polyoxyimethalene tip	85 to 240 Vac	Large aluminum	3/4 NPT
LVCN6242	Level switch 316 SS rod/PTFE tip	85 to 240 Vac	Large aluminum	3/4 NPT
LVCN6244	Level switch PVC rod and tip	85 to 240 Vac	Large aluminum	3/4 NPT
LVCN7211	Level switch 316 SS rod/Polyoxyimethalene tip	24 Vdc	Small nylon	3/4 NPT
LVCN7212	Level switch 316 SS rod/PTFE tip	24 Vdc	Small nylon	3/4 NPT
LVCN7214	Level switch PVC rod and tip	24 Vdc	Small nylon	3/4 NPT

Comes complete with operator's manual.

**Ordering Examples:** LVCN6121, level switch, 85 to 240 Vac power, 3/4 BSP mounting, large nylon enclosure with SS 4 3/4 polyacetal tip. LVCN7734, level switch, 24 Vdc power, 150# PVC flange mount, small aluminum enclosure with PVC rod and tip.



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenpfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters