

OMEGA-FLO® "BLACK MUSHROOM" 2-WAY PISTON-OPERATED DIAPHRAGM VALVE WITH PLASTIC BODY

SV-700 Series
Starts at

\$368



- ✓ For Use in Plastic Systems from 15 to 50 mm (½ to 2")
- ✓ Optical Position Indication
- ✓ High Flow Rate
- ✓ PVC (Socket Union)
- ✓ Closed or Opened by Spring Action; Pneumatically Operated
- ✓ For Contaminated and Aggressive Fluids
- ✓ Flow Direction Adjustable as Required
- ✓ Self-Draining When Appropriately Installed
- ✓ Electrical Feedback and Stroke Limitation Optional



SV-705, \$541, shown smaller than actual size.

SV-700 Series diaphragm valves are designed for use in plastic systems ranging in size from 15 to 50 mm (½ to 2"). The 2-way PVC or PVDF body and seal combination can handle ultra-pure, aggressive, viscous, or abrasive fluids. Threaded, solvent, or fusion joint end connectors link to the bodies. The glandless design of these valves makes them ideal for water treatment, reverse osmosis, ion exchange systems, or ultra-pure process plant applications. Remote control allows for use in hazardous areas.



The valves are operated by connecting an external pilot fluid to the piston actuator. The diaphragm

between the actuator and the body isolates the fluid from the actuator. The valves do not require maintenance, and they can be fitted with optional accessories for position indication or stroke limitation. The actuators provide long service life and air consumption, and they come in various sizes.

The convenient location of the pilot-air connection and the unit's compact dimensions allow space-saving side-by-side installation. The

pilot port has stainless steel inserts; 3-way pilot solenoid valves can be directly mounted. For safety, spring pressure is relieved when removing the cover to change the circuit function or install options.

The body is designed to handle high flow. Flow direction can be adjusted as the application requires. A high-quality diaphragm isolates the body from the actuator and provides the total external and internal seal integrity. The valves have no dead volume and can be installed for self-draining.



SPECIFICATIONS

VALVE

Fluid Temperature

PVC: 0 to 60°C (32 to 140°F)

Installation Connection:

PVC: Socket union

ACTUATOR

Ambient Temperature:

-10 to 60°C (14 to 140°F)

Control Pressure

Circuit Function Standard (Normally Closed):

Min Required: 5.5 bar (79.8 psi)

Max Admissible: 10 bar (145 psi)

EPDM diaphragm:

P_{ST} = 4.5 bar (65.2 psi)

PTFE diaphragm:

P_{ST} = 5.0 bar (72.5 psi)

Control Fluid: Neutral gases, air

Flow Adjustment: Variations of flow within the max and min values can be adjusted with of the piston stroke limiting feature

Electrical Position Indicator:

Mechanical or inductive position sensing (open or closed); LED display; self-adjusting trip cam for closed position

 **MOST POPULAR MODEL HIGHLIGHTED!**

To Order (Specify Model Number) PVC Body–Normally Closed Valve

Model No.	Price	Orifice	C _v	Operating Pressure bar (psi)	Diaphragm	Weight kg (lb)
SV-703	\$368	1"	15.7	9.6 (140)	EPDM	1.9 (4.2)
SV-705	541	1½"	41.9	9.6 (140)	EPDM	5.4 (11.9)
SV-706	714	2"	61.8	7.9 (115)	EPDM	5.7 (12.5)

Comes complete with operator's manual.

For recommended pilot valves, see page J-51.

Ordering Example: SV-705, PVC body valve, 1.5" orifice, \$541.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters