



VELOCITY AND TEMPERATURE MEASUREMENT SYSTEM

TVS-1000 Series
Starts at

\$3025




TVS-1004, \$3025,
shown smaller
than actual size.

- ✓ Flexible Sensors
- ✓ Thin Low Profile for Minimal Flow Disturbance
- ✓ High Accuracy
- ✓ Air Velocity and Temperature Measurements in One Sensor
- ✓ Research Quality Results

The TVS-1004 and TVS-1008 automatic temperature and velocity scanners are portable, 4- and 8-channel hot wire anemometer systems. The TVS-1100 series are factory expandable for up to 32 total sensors. Fully automated, these research-quality instruments take accurate single- or multi-point measurements of air temperature, velocity and surface temperature in complex environments, such as PCBs and electronics enclosures. When used as temperature loggers, they can measure both fluid and solid temperatures.

The TVS-1000 series employ patented, fast response, omnidirectional sensors, which measure both temperature and velocity. This patented single-sensor technology eliminates errors introduced as a result of air flow being non-isothermal. Each precisely calibrated sensor is flexible and robust with a low-profile configuration that allows minimally intrusive mounting throughout the peaks and valleys created by the



PCB components. These systems require a PC to operate and utilize the provided software for data acquisition and reporting.

The candlestick style sensor, is a flexible, robust, base-and-stem design sensor that measures both temperature and air velocity for characterizing thermal conditions in electronic systems. The candlestick sensor is narrow and low profile to minimize the disturbance of the heat flow in the test domain. It features a flexible, plastic-sleeved stem, which facilitates installation and repositioning during the testing process. Sensors are calibrated for low (natural convection) and high velocity flows. They are capable of temperature measurements ranging from -30 to 150°C $\pm 1^\circ\text{C}$. Velocity measurements range from

0 to 50 m/s (10,000 ft/min). The use of a single sensor to measure both temperature and velocity eliminates errors that can occur when airflow is non-isothermal. Multiple candlestick sensors can be easily installed to thoroughly map a system's thermal and airflow conditions. Their robust nature allows for continuous repositioning and reading.



The TVS-1004 series is supplied with one miniature candlestick sensor for each channel. Shown slightly larger than actual size.




TVS-1004 Kit, \$3025, includes 4 calibrated sensors, scanner, analysis software, power cord and complete operator's manual.



TVS-1132, \$12,103,
shown smaller than actual size.

TVS-1000-RP
sensor, \$281,
shown actual size.



SPECIFICATIONS

Scanners

Power: 115 Vac, 60 to 50 Hz

Max No of Channels: 4 for TVS-1004; 8 for TVS-1008

Temperature Range: -30 to 150°C $\pm 1^\circ\text{C}$ (-22 to 302°F) $\pm 1.8^\circ\text{F}$

Velocity Range: 0 to 50 m/s (10,000 ft/min) $\pm 2\%$ at velocity

Sensors: Up to 8 with the TVS-1008; Up to 4 with the TVS-1004; TVS-1100 series are factory expandable for up to 32 channels

Measurement Duration: Depends upon the PC storage limitation in the save file mode, unlimited without saving data
PC Software with thermal analysis module

Computer Interface: RS232 Port w/USB adaptor

Sensor

Cable: 2 m (6')

Height: 12 mm (0.5")

Base Diameter: 9.5 mm (0.4")

Sensor Stem Diameter: 0.5 mm (0.02")


Sensor Bead Diameter: 1.1 mm (0.04")

Velocity Measurements: 0 to 6 m/s or 0 to 50 m/s


Temperature Measurements: -30 to 150°C $\pm 1^\circ\text{C}$




Series	TVS-1000	TVS-1100
Depth	23.5 cm (9 1/4")	27.9 cm (11")
Width	13.4 cm (5 1/4")	34.3 cm (13.5")
Height	6.4 cm (2.5")	3.5 cm (5.3")
Weight	2 kg (4 lbs)	5 kg (10 lbs)




TVS-1000 Series PC software with thermal analysis module.



TVS-1000 Series PC software with thermal analysis module.



TVS-1000 Series PC software with thermal analysis module.



TVS-1000 Series PC software with thermal analysis module.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
TVS-1004	\$3025	Scanner, 4 velocity/temperature sensors and software
TVS-1008	4417	Scanner, 8 velocity/temperature sensors and software
TVS-1108	6791	Scanner, 8 velocity/temperature sensors and software (factory expandable)
TVS-1112	8522	Scanner, 12 velocity/temperature sensors and software (factory expandable)
TVS-1120	12,103	Scanner, 20 velocity/temperature sensors and software (factory expandable)
TVS-1132	17,503	Scanner, 32 velocity/temperature sensors and software

Accessories

Model No.	Price	Description
TVS-1000-RP	\$281	Replacement velocity/temperature sensor with calibration reference book
OP-9	135	Reference Handbook: Flow Measurement Engineering

Comes complete with calibrated sensors, scanner, analysis software, power cord and operator's manual.

Ordering Examples: TVS-1004, 4-channel with velocity/temperature sensors, and software, \$3025.

TVS-1108, expandable 8 channel scanner with sensors and software, \$6791.



omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters