



# CONSTANT TEMPERATURE HEATED DRY BATHS

HDB Series Starts at  
**\$854**



Block extraction tool with threaded fitting included.



HDB-3D, 3 blocks, 650 W, \$1471.

- ✓ Uniform Heating for Test Tubes, Cuvettes, and Other Sample Containers
- ✓ Interchangeable Insert Blocks
- ✓ Models for 2 or 3 Insert Blocks
- ✓ Solid State Temperature Control

OMEGA® HDB Series heated dry baths provide a safe, dry, constant temperature source in laboratory applications involving incubation, boiling, inactivation, wet ashing, and enzyme analysis, as well as in a variety of clinical and industrial applications.

Interchangeable aluminum insert blocks accept tubes or containers ranging from 6 to 26 mm in diameter. A close fit of the tubes in the block ensures high heat transfer, and the heater's design, thermistor temperature sensor, and solid state circuitry provide exceptionally good temperature stability and uniformity. Temperature stability is  $\pm 0.1^\circ\text{C}$ , and uniformity between blocks is  $\pm 0.2^\circ\text{C}$  (both at  $40^\circ\text{C}$ ).

On the HDB-2 and HDB-3, temperatures are adjusted with a dial calibrated in  $^\circ\text{C}$ . On the HDB-3D, the dial and digital display are used to set the temperature. The digital indicator continuously displays the temperature.

A block extraction tool, and threaded fitting built into the block, allow easy removal. The user can also insert glass thermometers into the block for accurate temperature measurement.

## SPECIFICATIONS

### Temperature Range:

HDB-2: 1.25 to  $105^\circ\text{C}$  (75 to  $219^\circ\text{F}$ )

HDB-3: 1.25 to  $200^\circ\text{C}$  (75 to  $392^\circ\text{F}$ )

HDB-3D: 1.25 to  $200^\circ\text{C}$  (75 to  $392^\circ\text{F}$ )

### Temperature Stability (at $40^\circ\text{C}$ ):

HDB-2, HDB-3, HDB-3D,  $\pm 0.1^\circ\text{C}$

Maximum Temperature Variation Between Blocks (at  $40^\circ\text{C}$ ):  $0.2^\circ\text{C}$

### Temperature Setting and Resolution:

HDB-2, HDB-3, Rotary Dial,  $2^\circ\text{C}$  increments; HDB-3D, 3 digit display,  $1^\circ\text{C}$  resolution

Control Accuracy: HDB-2, HDB-3,  $\pm 2^\circ\text{C}$ ; HDB-3D,  $\pm 1^\circ\text{C}$

### Aluminum Insert Blocks

Model Number	Price	Tube Size	Number of Holes	Dimensions (mm)
6013501	\$89	Plain block	None	95 x 76 x 51
6013502	89	6 mm	30	95 x 76 x 51
6013503	89	10 mm	20	95 x 76 x 51
6013504	89	12 mm	20	95 x 76 x 51
6013505	89	13 mm	20	95 x 76 x 51
6013506	89	15 mm	12	95 x 76 x 51
6013507	89	16 mm	12	95 x 76 x 51
6013508	89	19 mm	8	95 x 76 x 51
6013509	89	25 mm	6	95 x 76 x 51
6013510	180	10 mm cuvettes, 2 channels	—	95 x 76 x 51
6013512*	403	Plain block thermometer	Hole only	95 x 225 x 51
6014460	133	Plain block thermometer	Hole only	95 x 76 x 51
6014462	215	24 mm	6	95 x 76 x 51
6014463	153	26 mm	6	95 x 76 x 51
6014464	149	1.5 mL eppendorf	20	95 x 76 x 51
6014465	149	0.5 mL eppendorf	30	95 x 76 x 51
6014466	62	Plastic half plain blocks**	—	95 x 37 x 50

\* For HDB-3, HDB-3D only. \*\* If less than the maximum number of blocks is used, it is recommended that the plastic half blocks fill the space on either side of the aluminum block(s) to maintain temperature stability.

Ordering Examples: HDB-2, heated dry bath with 2 model 6013503 20-hole insert blocks, \$854 + 89 + 89 = \$1032.

HDB-3, heated dry bath with 3 model 6013503 20-hole insert blocks, \$1091 + 89 + 89 + 89 = \$1358.

**MOST POPULAR MODEL HIGHLIGHTED!**

## To Order (Specify Model Number)

Model No.	Price	Description
HDB-2	\$854	2 blocks, 25 to $105^\circ\text{C}$ , 450 W, 120V
HDB-3	1091	3 blocks, 25 to $200^\circ\text{C}$ , 650 W, 120V
HDB-3D	1471	3 blocks, 25 to $200^\circ\text{C}$ , 650 W, 120V, temperature and setpoint display

Comes with block extraction tool, power cord and plug, and operator's manual. Aluminum insert blocks are ordered separately (see table at right).

Note: 240V models are also available. To order, add "-240V" suffix to model number.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters