

ECONOMICAL DIGITAL FORCE GAGES WITH ANALOG AND RS232 OUTPUTS



DFG31 Series

All Models
\$1045



- ✓ User Selectable Units of Measure
- ✓ Accuracy $\pm 0.25\%$ of Full Scale
- ✓ NIST Calibration Certificate Included
- ✓ Selectable Display Languages
- ✓ Advanced Operating Modes with Statistical Calculations
- ✓ Simple Operator Interface with Menu Prompts and Function Keys for Easy Use
- ✓ RS232 and ± 2 Vdc Analog Outputs Standard
- ✓ Rechargeable Nickel Metal Hydride Batteries or Direct AC Operation with Universal Adaptor



Comes complete with hard carrying case, rechargeable batteries, universal battery eliminator, hook, flat tip, calibration certificate, and operator's manual.

OMEGAs DFG31 Series is an easy-to-use digital force gage designed for economical applications without compromising functionality. It's available in 7 ranges from 2 to 500 lb force and features a measurement accuracy of better than 0.25% full scale. A large, easy-to-read, high resolution dot matrix LCD supports a variety of standard gage functions including normal and peak readings, high/low limits, setpoints, pass/fail results, statistical results, load cell actuation and direction. Loads are displayed in ozf, gf, lbf, kgf and Newtons. The display can be inverted and displayed results may be "hidden" from the operator. RS232, and ± 2 Vdc analog outputs are standard.

SPECIFICATIONS

- Accuracy:** $\pm 0.25\%$ FS
- Display:** High resolution, dot matrix LCD, 8 lines, 40 characters with adjustable contrast
- Data Sampling Rate:** 5000 Hz
- Peak Capture Rate:** 5000 Hz
- Display Update Rate:** 10 Hz
- Operating Temperature:** 4 to 38°C (40 to 100°F)
- Temperature Effects:** $< 0.05\%$ FS per °C (0.03% per °F)
- Relative Humidity:** 20 to 80%
- Overload Protection:** 150% FS
- Tare Capacity:** 10% FS
- Power:** Rechargeable nickel metal hydride batteries or direct AC power using universal adaptor (batteries and adaptor included)
- Battery Life:** Approximately 30 hours continuous use
- Dimensions:** 173 H x 73 W x 41 mm D (6.8 x 2.9 x 1.6")
- Weight:** 0.7 kg (1.5 lb)



DFG31-200, \$1045, shown smaller than actual size.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

MODEL NO.	PRICE	FORCE RANGE VS. RESOLUTION				
		oz	g	lb	kg	Newton
DFG31-2	\$1045	32 x 0.01	1000 x 1	2 x 0.001	1 x 0.001	10 x 0.01
DFG31-10	1045	160 x 0.1	5000 x 1	10 x 0.01	5 x 0.001	50 x 0.01
DFG31-25	1045	400 x 0.1	10000 x 10	25 x 0.01	10 x 0.01	100 x 0.1
DFG31-50	1045	800 x 0.1	25000 x 10	50 x 0.01	25 x 0.01	250 x 0.1
DFG31-100	1045	1600 x 1	50000 x 10	100 x 0.1	50 x 0.01	500 x 0.1
DFG31-200	1045	—	—	200 x 0.1	100 x 0.1	1000 x 1
DFG31-500	1045	—	—	500 x 0.1	250 x 0.1	2500 x 1
DFG-850-1	70	RS232 cable				

Comes complete with hard carrying case, rechargeable batteries, universal battery eliminator, hook, flat tip, calibration certificate, and operator's manual.

Ordering Examples: DFG31-10, 10 lb digital force gage, \$1045.

DFG31-200, 200 lb digital force gage, \$1045.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters