

IMMERSION HEATER FOR LIGHT WEIGHT OIL APPLICATIONS

MTO-1 Series
Starts at
\$205





- ✓ 1 1/4 NPT Steel Screw Plug
- ✓ Steel Sheath Elements
- ✓ 10 and 20 W/in²
- ✓ 0.5 to 3 kW
- ✓ Without Thermostat
- ✓ 120 and 240 Volt, Single Phase
- ✓ General Purpose or Moisture Resistant/Explosion Resistant Terminal Enclosure



MTO-105/120, \$205, shown smaller than actual size.



MTO-120E2/120, \$472, shown smaller than actual size.



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

kW	Volts	Phase	W/in ²	No. Elem.	Dim. B cm (in)	E1 General Purpose ¹			E2 Moisture Res./Explosion Resistant ²		
						Model No.	Price	Wt. lb (kg)	Model No.	Price	Wt. lb (kg)
0.5	120	1	10	2	32 (12 1/2)	MTO-105/120	\$205	2 (1)	MTO-105E2/120	\$417	5 (2)
0.5	240	1	10	2	32 (12 1/2)	MTO-105/240	205	2 (1)	MTO-105E2/240	417	5 (2)
1	120	1	20	2	32 (12 1/2)	MTO-110/120	219	2 (1)	MTO-110E2/120	417	5 (2)
1	240	1	20	2	32 (12 1/2)	MTO-110/240	219	2 (1)	MTO-110E2/240	417	5 (2)
2	120	1	20	2	66 (26)	MTO-120/120	260	3 (1)	MTO-120E2/120	472	6 (3)
2	240	1	20	2	66 (26)	MTO-120/240	260	3 (1)	MTO-120E2/240	472	6 (3)
3	120	1	20	2	96 (38)	MTO-130/120	300	3 (1)	MTO-130E2/120	512	6 (3)
3	240	1	20	2	96 (38)	MTO-130/240	300	3 (1)	MTO-130E2/240	512	6 (3)

¹ Heaters with general purpose enclosures are UL recognized and CSA certified.

² Heaters with moisture resistant/explosion resistant enclosures are CSA NRTL/C certified.

Ordering Examples: MTO-110/240, 1 kW, 1-phase general purpose heater, \$219. MTO-105E2/120, 0.5 kW, 120 Vac, \$417.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters