

DUAL-INPUT PROCESS METERS WITH MATH FUNCTIONS FOR PROCESS VOLTAGE OR CURRENT INPUTS

DP7800
£194



DUAL INPUTS!



- ✓ Dual Inputs with Programmable Math Functions
- ✓ Programmable Ranges: ± 200 mV to ± 200 V and 4 to 20 mA
- ✓ Digital Tare (Zero) Up to 50% of Span
- ✓ Easily Programmed Span: 1000 to 30,000 Counts
- ✓ Programming and Calibration from Front Panel
- ✓ 5-Digit, 14 mm (0.56") Red LED Display with Negative Indications
- ✓ 2 Setpoints with Relay Closures (Standard)
- ✓ NEMA 4 (IP65) Rated Bezel with Panel Gasket Seal
- ✓ Heavy-Duty Aluminium Case, 101 mm (4") Behind the Panel
- ✓ 16-Bit A/D Converter

The DP7800 accepts 2 inputs simultaneously and can perform math functions: $A - B$, $A + B$, $A \times B$, and $A \div B$.

SPECIFICATIONS

Accuracy: $\pm 0.01\%$ of reading ± 1 count of LSD

Range Programming: Solderless jumpers on rear of unit; select 200 mV, ± 2 V, ± 20 V, ± 200 V or 4 to 20 mA

Conversion Rate: 3/s

DP7800, £194, shown smaller than actual size, with 2 PX41 pressure transducers, £302 each, see section B.

Display: 5-digit, 7-segment, 14.3 mm (0.56") high LED

Limit Outputs: Standard dual form "A" relays rated 0.25 A @ 28 V

Analogue Output (Optional): to 10 Vdc @ 2.5 mV resolution; 0 V and 10 V points are programmable via front-panel switches; maximum drive capability ± 2 mA; the 4 mA and 20 mA points are programmable via front-panel switches; 4 to 20 mA output, maximum load 600 Ω

CMV: 1400 Vp (AC or DC) between analog output ground and AC power line ground

Serial Interface (Optional): ASCII RS232 or RS485 compatible; format: 1 start bit, 8 data bits, 1 stop bit and no parity bits

Baud Rates: 9600, 4800, 2400, 1200, 600, 300, 150 and 75—programmable from the front panel

Operating Temperature: -20 to 60°C (-4 to 140°F)

Storage Temperature: -25 to 85°C (-12 to 185°F)

Relative Humidity: 0% to 90%, non-condensing

Power:

Standard: 115 Vac (15 to 10%) @ 50 mA (47 to 500 Hz)

Optional: 230 Vac (15 to 10%) @ 25 mA (47 to 500 Hz)

Optional: 9 to 18 Vdc or 18 to 36 Vdc

Dimensions: 1.97 H x 3.80 W x 4.0" D (50 x 97 x 102 mm); rear connectors add 0.5" to depth

Panel Cutout: 45 H x 92 mm W (1.77 x 3.58"), 1/2 DIN

Weight: 454 g (1 lb)

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
CE-1911	£117	Reference Book: Circular Storage Tanks and Silos

OPTIONS

SUFFIX	PRICE	DESCRIPTION
-S2	£33.50	ASCII RS232 serial interface
-S4	33.50	ASCII RS485 serial interface
-AMA	33.50	Analog output 4 to 20 mA
-A10	33.50	Analog output 0 to 10 Vdc
-LED	33.50	High-brightness LED display
-DC9/18	84	9 to 18 Vdc power @ 600 mA
-DC18/36	84	18 to 36 Vdc power @ 500 mA
-230VAC	6.70	230 Vac power, 50 to 400 Hz

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

MODEL NO.	PRICE	DESCRIPTION
DP7800	£194	Dual-input voltmeter

Comes with complete operator's manual.

Ordering Example: DP7800-S2, dual-input voltmeter with RS232 serial communications, \$290 + 50 = \$340.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters