


HIGH TEMPERATURE STRIP HEATERS




NSA Series Starts at
\$60



Element Width: $\frac{1}{2}$ (1.3) \pm $\frac{1}{32}$ (0.08)
Thickness: $\frac{3}{16}$ (0.5)
Dimensions: inches (cm)

- ✓ Rugged, Reliable, Premium Quality
- ✓ 125 to 400 Watts
- ✓ Seamless Construction
- ✓ $\frac{1}{2}$ " (1.27 cm) Slim Design for Space Restricted Applications

Dimension A = Total Length
Dimension B = Heated Length
Dimension C = Flattened Length



The NSA series high temperature strip heater features a slim $\frac{1}{2}$ " (1.27 cm) width design, ideal for heat applications where space is restricted. The maximum temperature rating is 260°C (1500°F) with Incoloy sheath material. Applications include heating of large tanks, vats and heating ducts while clamped to the surface.

FEATURES

$\frac{3}{16}$ " (0.5 cm) thick x $\frac{1}{2}$ " (1.27 cm) wide mini-size construction similar to NS type. The heater design, materials and construction give long life for given power densities. The Incoloy sheath encloses nickel-chromium resistance wire embedded in a densely compacted refractory material selected for dielectric insulation value and good heat conduction to the sheath. The small cross-section is often an advantage where space is a factor.

SPECIFICATIONS

Sheath Material: Incoloy
Max. Sheath Temp.: 260°C (1500°F)
Power: 120 or 240 Vac

CAUTION AND WARNING

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warnings.

STOCKED FOR FAST DELIVERY

To Order (Specify Model Number)										
Dimension-Inches (cm)										
Heated Length			Watts	W/in ²	Volts	Model No.	Price	Wt. lb (kg)		
A	B	C								
7 $\frac{1}{8}$ (18)	3 $\frac{1}{8}$ (8)	5 $\frac{1}{8}$ (13)	125	32	120	NSA-711	\$60	0.20 (0.09)		
10 $\frac{1}{16}$ (27)	6 $\frac{1}{16}$ (17)	8 $\frac{5}{16}$ (21)	300	20	120	NSA-1013	63	0.28 (0.12)		
11 $\frac{1}{8}$ (28)	7 $\frac{1}{8}$ (18)	9 $\frac{3}{8}$ (24)	350	22	240	NSA-1123	65	0.38 (0.17)		
13 $\frac{3}{8}$ (35)	9 $\frac{3}{8}$ (24)	12 (30)	200	11	240	NSA-1422	68	0.47 (0.21)		
14 $\frac{3}{8}$ (36)	10 $\frac{3}{8}$ (26)	12 $\frac{3}{8}$ (32)	200	7	120	NSA-1412	68	0.49 (0.45)		
16 $\frac{1}{4}$ (41)	12 $\frac{1}{4}$ (31)	14 $\frac{1}{2}$ (37)	400	19	240	NSA-1624	71	0.56 (0.25)		

[†] To determine maximum allowable watt density, see Figures C-8 or C-9.

Ordering Examples: NSA-711, high temperature strip heater, 120 Vac, \$60.
NSA-1624, high temperature strip heater, 240V, \$71.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters