

# ANALOG GAGING PROBES

## GP911 Series

Starts at  
£ **224**



- ✓ Spring- or Pneumatic-Actuated Models
- ✓ Exceptional Linearity Across Full Range
- ✓ Stainless Steel Body
- ✓ NEMA 12 (IP65) Environmental Rating



The GP911 Series analog gaging probes use proven LVDT technology to provide excellent linearity and repeatability in a compact, reliable unit. All analog probe heads carry a NEMA 12 (IP65) environmental rating that makes them suitable for use in harsh industrial environments.

In an analog gage probe, 2 small transformers share a common magnetic core. As the core moves, the output of one transformer increases and that of the other decreases. The out-of-balance current provides the measure of the core's position. LVDTs operate on an AC energizing voltage and require special signal conditioning.

GP911-5-P, £338,  
shown larger  
than actual size.

GP911-2.5-P, £345,  
shown close to actual size.


# ANALOG GAGING PROBES

## SPRING ACTUATED Dimensions: mm (in)

MODEL	GP911-1-S	GP911-2.5-S	GP911-5-S
A	46.0 (1.8)	72.5 (2.8)	91 (3.6)
B1	14.15 (0.56)	17.65 (0.70)	25.65 (1.01)
B2	11.65 (0.46)	11.65 (0.46)	14.65 (0.58)
B3	12.65 (0.50)	14.75 (0.58)	20.25 (0.80)
C	3.5 (0.14)	4.0 (0.16)	4.0 (0.16)
D	42.5 (1.67)	68.5 (2.70)	87.0 (3.43)

## PNEUMATICALLY ACTUATED Dimensions: mm (in)

MODEL	GP911-1-P	GP911-2.5-P	GP911-5-P
A	51.0 (2.01)	73.0 (2.88)	98.0 (3.86)
B1	14.05 (0.55)	17.55 (0.69)	25.55 (1.01)
B2	11.05 (0.44)	11.55 (0.45)	14.55 (0.57)
B3	12.75 (0.50)	14.75 (0.58)	20.25 (0.80)



**MOST POPULAR MODELS HIGHLIGHTED!**

## SPECIFICATIONS

**Excitation Voltage:** 1 to 10 Vrms  
**Excitation Frequency:** 2 to 20 kHz  
**Linearity:** 0.5% rdg or 0.1% FS, whichever is greater  
**Repeatability:** 0.15 microns  
**Calibration Voltage:** 3 Vrms  
**Calibration Frequency:** 5 kHz  
**Calibration Load:** 10 kΩ  
**Storage Temp:** -40 to 100°C (-40 to 212°F)  
**Operating Temp:** -10 to 80°C (14 to 176°F)  
**Temp Coefficient:** 0.01% FS/°C (0.03% for 0.5 mm model)

## To Order (Specify Model Number)

MODEL NO.	PRICE	RANGE: mm (in)	ACTUATION
GP911-0.5-S	£271	±0.5 (0.02)	Spring loaded
GP911-1-S	224	±1 (0.04)	Spring loaded
GP911-2.5-S	255	±2.5 (0.10)	Spring loaded
GP911-5-S	281	±5 (0.20)	Spring loaded
GP911-1-P	338	±1 (0.04)	Pneumatic
GP911-2.5-P	345	±2.5 (0.10)	Pneumatic
GP911-5-P	338	±5 (0.20)	Pneumatic

Comes with complete operator's manual.

**Ordering Example:** GP911-5-S, spring-loaded analog gaging probe with ±5 mm (0.2") stroke, £281.

## ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
CM-4365	£107	Reference Book: Actuator Saturation Control

# omega.com®

Your One-Stop Source for Process Measurement and Control!

One Omega Drive | Stamford, CT 06907 | 1-888-TC-OMEGA (1-888-826-6342) | info@omega.com

[www.omega.com](http://www.omega.com)



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters

• [click here to go to the omega.com home page](http://www.omega.com) •