

ELECTROPNEUMATIC CONVERTERS

CURRENT TO PRESSURE (I/P)

IP411 Series
IP413 Series

Starts at
\$160



IP413-020, \$180, shown larger than actual size.

- ✓ **Integral Dial Control Pressure Indicator**
- ✓ **Manual Override Available**
- ✓ **Solenoid Valve Design Eliminates Leaks**
- ✓ **Can be Used with Unfiltered Main Air Supply**
- ✓ **Zero and Span Adjustments for Field Calibration**

The IP411 and IP413 accept 4 to 20 mA, 0 to 10V, and 0 to 5V signals and convert these analog signals to proportional linear pneumatic outputs (3 to 15 or 0 to 20 psi). Unlike other units that bleed air to maintain pressure, the IP411 and IP413 use a silicon pressure sensor and an electropneumatic converter to provide the desired pneumatic pressure without constant air consumption. The converter's unique design eliminates common problems such as hose chatter and

needless air consumption from air leaks caused by heat, age, moisture, contamination, mounting, orientation error, sticky valves, valve leakage, and blockages. The IP411 and IP413 provide a reliable, repeatable, and accurate means of converting an electrical signal into a pneumatic pressure. A sourcing controller is required.

ELECTROPNEUMATIC CONVERTERS

SPECIFICATIONS

Supply Voltage: 18 to 28 Vdc or Vac

Supply Current: 150 mA/3 VA

Accuracy: 1% FS

Zero Adjustment: ±50%

Span Adjustment: ±25%

Operating Temp: 0 to 70°C
(32 to 160°F)

Compensated Temp: 0 to 70°C
(32 to 160°F)

Thermal Effects:

Zero: ±0.025% FS/°F

Span: ±0.01% FS/°F

Max Supply Pressure: 40 psig

Min Supply Pressure: 0.1 psig above maximum control pressure

Solenoid Type: Floating poppet

Solenoid Coil: 3 W

Flow Rate: 0.5 SCFM

Pressure Port: Hose barb fits
4.76 mm ($\frac{3}{16}$ " ID tubing

Minimum Control Pressure Tubing Length: 3 m (10')

Electrical Connector: Screw terminals


Weight: 350 g (12 oz)

Manifold Material: Aluminum

Case: 16-gage steel



Order with TX4-100 shielded wire, \$35 per 100'. Shown smaller than actual size.



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

MODEL NO.	PRICE	INPUT RANGES	OUTPUT RANGE	MANUAL OVERRIDE
IP411-X15	\$160	4 to 20 mA, 0 to 5V, 0 to 10V	3 to 15 psig	No
IP411-020	160	4 to 20 mA, 0 to 5V, 0 to 10V	0 to 20 psig	No
IP413-X15	180	4 to 20 mA, 0 to 5V, 0 to 10V	3 to 15 psig	Yes
IP413-020	180	4 to 20 mA, 0 to 5V, 0 to 10V	0 to 20 psig	Yes
ACCESSORY				
TX4-100	\$35	30.48 m (100') of 4-conductor shielded wire		

Comes complete with operator's manual.

Ordering Example: IP413-X15, electropneumatic converter with 3 to 15 psig output and manual override, TX4-100, 30.48 m (100') of 4-conductor wire, \$180 + 35 = \$215.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters