

Process Indicators

Miniature 1/32 DIN and Loop-Powered 1/8 DIN Models

DP35 Series
Starts at
\$180



- ✓ 3½ Digit Display
- ✓ User-Selectable Inputs
- ✓ Minimal Panel Depth
- ✓ ±0.2% Accuracy
- ✓ 10 to 30 Vdc Power, Isolated
- ✓ Scalable to Engineering Units, with Selectable Decimal Point

The DPM35A is a compact process indicator, requiring only 70 mm (2.8") of depth behind a panel. It uses a 45 x 22.2 mm (1.77 x 0.87") 1/32 DIN cutout, and has large, 10 mm (0.4") display digits and a rear screw-clamp connector for inputs.

The DPM35A can accept input voltage ranges from 0 to 200 Vdc and current from 0 to 50 mA. The unit can be scaled for both zero and span to display in engineering units. The decimal point position is jumper-selectable.

The DP35 is a 1/8 DIN loop-powered process indicator that can be configured for 1 of 3 input ranges: 1 to 5 mA, 4 to 20 mA, or 10 to 50 mA. Like the DPM35A, the DP35 can be scaled for both zero and span to display in engineering units and has a jumper-selectable decimal point position.

Specifications

Display: 3½ digit, 0 to 1999; 7-segment
DPM35A: Red LED
DP35: LCD

Display Height:
DPM35A: 10 mm (0.39")
DP35: 12.7 mm (0.5")

Inputs:
DPM35A: 0 to 200 Vdc or 0 to 20 mA
DP35: 1 to 5 mA, 4 to 20 mA, 10 to 50 mA (jumper-selectable)

Input Configuration: Bipolar single

A/D Converter: Dual slope, average value



DP35 1/8 DIN loop-powered LCD meter, \$200, shown smaller than actual size.

Reading Rate:

DP35: 3/s
DPM35A: 2.5/s

CMRR: 65 dB

Warm-Up to Rated Accuracy: 2 min

Polarity: Automatic, minus sign indicator

Accuracy:
DPM35A: 0.2% ±1 count;
DP35: 0.2% ±1 count

Span Temp Coefficient:

DP35: 80 ppm
DPM35A: <50 ppm

Zero Temp Coefficient: 2 µV/°C

Overrange:


DP35: Only "1" or "-1" displayed
DPM35A: Positive = display blank, negative = "." is displayed

Decimal Point: Jumper-selectable for 1.XXX, 1X.XX or 1XX.X

Operating Temperature:

DPM35A: -20 to 60°C (-4 to 140°F)
DP35: 0 to 70°C (32 to 158°F)

Panel Punches Available Visit omega.com/panelpunches



The compact DPM35A, LED 1/32 DIN meter with a bezel of 24 H x 48 mm W, \$180. Shown smaller than actual size.

Power: 10 to 30 Vdc, isolated

Ripple: 10%

Power Consumption:

DP35: 0.3 mA
DPM35A: 0.6 W @ 24 Vdc

Electrical Connection:

Screw-clamp connector

Dimensions:

DPM35A: 24 H x 48 W x 70 mm D (0.94 x 1.89 x 2.76")
DP35: 48 H x 96 W x 117 mm D (1.89 x 3.78 x 4.61")

Panel Cutout:

DPM35A: 22.2 x 45 mm (0.87 x 1.77")
DP35: 44.5 x 92.5 mm (1.75 x 3.64"); DIN 43700

Weight:

DPM35A: 60 g (2.1 oz)
DP35: 150 g (5.3 oz)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
DPM35A	\$180	1/32 DIN LED process indicator
DP35	200	1/8 DIN LCD process indicator, loop powered

Comes complete with operator's manual.

Ordering Example: DPM35A, 1/32 DIN process indicator, \$180.

Accessories

Model No.	Price	Description
DPP-1	\$400	1/32 DIN panel punch
DPP-5	525	1/8 DIN panel punch
AV-1043	150	Reference Book: Dictionary of Scientific and Technical Terms



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters