

# DIGITAL TORQUE METER WITH RS232 OUTPUT REMOTE SENSOR INCLUDED

HHTQ88  
**\$889**

See Pages  
F-9 thru F-15 for Digital  
Force Gages



Remote sensor included.



- ✓ 3 Selectable Torque Units: kgf-cm, lb-in, N-cm
- ✓ High (0.01) and Low (0.1) Resolution Modes
- ✓ Fast and Slow Sampling Modes
- ✓ Auto Shut-Off Extends Battery Life
- ✓ Reading Hold
- ✓ Stores Minimum and Maximum Readings with Pushbutton Recall
- ✓ RS232 PC Interface to Load Data into Logging or Recording Programs

**Operating Humidity:**  
<80% RH (non-condensing)

**Sensor Chuck:**  
12 mm (0.5")

**Power:** 9V alkaline battery (included)

**Sampling Time:**  
Fast: Approximately 0.125 s  
Slow: Approximately 0.334 s

**Data Output:** RS232 PC serial output

**Meter Dimensions:**  
180 H x 72 W x 32 mm D (7.1 x 2.8 x 1.3")

**Sensor Dimensions:**  
48 D x 160 mm L (1.9 x 6.3")

**Meter Weight:** 225 g (0.5 lb)

**Sensor Weight:** 665 g (1.5 lb)

**Sensor Cable:** 1 m (39")

The HHTQ88 is a precision test instrument for automotive, automation, laboratory, and general industrial applications. The unit comes with a torque sensor with built-in 12 mm (0.5") chuck and chuck key. Three selectable torque units (kgf-cm, lb-in, N-cm) make this instrument compatible with virtually all measuring systems. The HHTQ88 also has fast and slow sampling rates to fit most automation applications. The large, 15 mm (0.6") high digits are easy to read. The RS232 serial interface allows for use with data logging or recording programs.

Recommended Reference Book:  
CRC Handbook of Mechanical Engineering,  
**ME-1708, \$190.**  
See Section Y  
For Additional Books

Chuck key included.



HHTQ88, torque sensor included, \$889, shown smaller than actual size.

## SPECIFICATIONS

**Units:** kgf-cm, lb-in, N-cm  
(N = Newtons)

**Range:** Up to 15 kgf-cm

**Safe Overload:** 150% of range

**Functions:** Auto-off (after about 20 min), reading hold, min and max

**Accuracy:** ±1.5% FS + 5 digits, 23 ±5°C (73 ±9°F), includes linearity, repeatability and hysteresis

**Operating Temperature:**  
0 to 50°C (32 to 122°F)

UNIT	MAX RANGE	HIGH RESOLUTION	LOW RESOLUTION
kgf-cm	15 kgf-cm	0.01 kgf-cm	0.1 kgf-cm
lb-in	13.02 lb-in	0.01 lb-in	0.1 lb-in
N-cm	147 N-cm	0.1 N-cm	1 N-cm

(N = Newtons)

**AVAILABLE FOR FAST DELIVERY!**

## To Order (Specify Model Number)

MODEL NO.	PRICE	DESCRIPTION
HHTQ88	\$889	Handheld torque meter

## ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
SW-U101-WIN	\$99	Application software and cables for RS232

Comes complete with 9V alkaline battery, torque sensor, chuck key, hard carrying case and operator's manual.

† To order with NIST traceable calibration, add suffix "-NIST" to model number and \$150 to price.

**Ordering Example:** HHTQ88, handheld torque meter with sensor and case, \$889.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters