

HYDROSTATICALLY COMPENSATED LOAD CELLS FOR UNDERWATER APPLICATIONS

LCUW Series

**Tension/Compression
Calibrated in Tension
0-100 lb to 0-10,000 lb
0-45 kg to 0-4537 kg**

1 Newton = 0.2248 lb
1 daNewton = 10 Newtons
1 lb = 454 g
1 t = 1000 kg = 2204 lb



Starts at
\$1175



- ✓ All Stainless Steel Construction
- ✓ 0.25% Accuracy
- ✓ Heavy-Duty Construction for High-Capacity Loads
- ✓ FM Intrinsically Safe Models (Standard)

The LCUW Series hydrostatically compensated load cells are designed for operation underwater. Applications include dry docks, marine weighing, submerged platforms, and industrial weighing where pit flooding occurs. The all stainless steel construction and rugged design make the LCUW a high-accuracy, high-reliability load cell in the difficult submerged environment.

SPECIFICATIONS

Output: 2 mV/V ±0.25 % FSO

Excitation: 10 Vdc (15 V max)

Accuracy: 0.25% FSO combined linearity, hysteresis and repeatability

Hydrostatic Effect on Zero:

±2.5% FSO per 500 psi

(10 K ±0.1% FSO per 100 psi)

Zero Balance: ±1.0% FSO

Agency Approvals: FM Intrinsically Safe IS/I.II.III/1/CDEFG


Operating Temp Range:

2 to 93°C (35 to 200°F)

Compensated Temp Range:

16 to 71°C (60 to 160°F)

Protection Class: IP68



Thermal Effects:

Zero: ±0.005% FSO/°F

Span: ±0.005% rdg/°F

Safe Overload: 150% of capacity

Ultimate Overload: 300% of capacity

Input Resistance: 360 Ω minimum

Output Resistance: 350 ±5 Ω

Construction: 17-4 PH stainless steel

Electrical: 0.9 m (3') 4-conductor

TFE wrapped cable

Dimensions: mm (in)

CAPACITY (lb)	A	B	D	T
100 to 1K	64 (2.5)	19 (0.75)	51 (2.0)	½-20 UNF-2A
2K to 6K	76 (3.0)	25 (1.0)	64 (2.5)	¾-16 UNF
10K	137 (5.38)	32 (1.25)	165 (6.5)	1-14 UNS

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

CAPACITY		MODEL NO.	PRICE	COMPATIBLE METERS*
lb	kg			
100	45	LCUW-100	\$1175	DP41-B, DP41-S, DP25B-S
250	114	LCUW-250	1175	DP41-B, DP41-S, DP25B-S
500	227	LCUW-500	1175	DP41-B, DP41-S, DP25B-S
1000	455	LCUW-1K	1175	DP41-B, DP41-S, DP25B-S
2000	909	LCUW-2K	1395	DP41-B, DP41-S, DP25B-S
6000	2721	LCUW-6K	1395	DP41-B, DP41-S, DP25B-S
10,000	4537	LCUW-10K	2595	DP41-B, DP41-S, DP25B-S

Comes with 5-point NIST-traceable calibration.

* See section D for compatible meters.

Consult Engineering for quotation on side cable exit.

Ordering Example: LCUW-100, 100 lb capacity hydrostatically compensated universal load cell, 0.9 m (3') cable, \$1175.

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
OP-17	\$15	Reference Book: Measure for Measure



LCUW-1K-SE,
\$1175, shown
larger than
actual size.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters