

POCKET TEST GAUGES

76 mm (3") DIAL AND STAINLESS STEEL CASE

PGT Series

All Models
\$170



- ✓ 0.5% FS Accuracy
- ✓ Ideal "Tool Box" Test Gauge
- ✓ All Stainless Steel Construction

SPECIFICATIONS

Accuracy: 0.5% FS
Case: Polished stainless steel
Dial: White background with mirrored band
Pointer: Adjustable with knife-edge tip
Movement: Stainless steel
Element: 316 SS
Connection: ¼ NPT



PGT-30L-150, cover included, \$170, shown actual size.

 MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

MODEL NO.	PRICE	DIAL DIA. mm (in)	RANGE	GRADUATIONS FIGURE	
				MAJOR	MINOR
PGT-30L-15	\$170	76 (3)	0 to 15	1	0.1
PGT-30L-30	170	76 (3)	0 to 30	2	0.2
PGT-30L-60	170	76 (3)	0 to 60	5	0.5
PGT-30L-100	170	76 (3)	0 to 100	10	1
PGT-30L-150	170	76 (3)	0 to 150	10	1
PGT-30L-200	170	76 (3)	0 to 200	20	2
PGT-30L-300	170	76 (3)	0 to 300	20	2
PGT-30L-400	170	76 (3)	0 to 400	50	2
PGT-30L-600	170	76 (3)	0 to 600	50	5
PGT-30L-1000	170	76 (3)	0 to 1000	100	10

Ordering Example: PGT-30L-100, pocket test gauge with 0 to 100 psi range, and stainless steel cover, \$170.

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
ME-1834	\$125	Reference Book: Water Quality Control Handbook



LOW-PRESSURE DIAPHRAGM GAUGES

PGL Series


All Models
\$40



- ✓ Corrosion-Resistant Bronze Diaphragm
- ✓ 150% Overpressure Protection
- ✓ Recalibration Screw on Dial
- ✓ 2-1-2 ANSI Grade A Accuracy*

SPECIFICATIONS

Dial: 64 mm (2.5") Dia.
 Pointer: Black aluminum
 Movement: Brass
 Element: Bronze diaphragm
 Connection: 1/4 NPT
 Window: Polycarbonate
 Media: Clean, dry, non-corrosive gas only



PGL-25L-60, \$40, shown larger than actual size.



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)							
MODEL NO.	PRICE	RANGE/GRADUATIONS					
		OUTER SCALE	INNER SCALE	INNER SCALE		OUTER SCALE	
FIG. INTERVALS	MINOR GRAD.			FIG INTERVALS	MINOR GRAD.		
PGL-25L-10	\$40	0/10 inH ₂ O	—	1	0.1	—	—
PGL-25L-15	40	0/15 inH ₂ O	0/9 oz/in ²	1	0.2	5	0.2
PGL-25L-35	40	0/35 inH ₂ O	0/20 oz/in ²	5	0.5	5	0.5
PGL-25L-60	40	0/60 inH ₂ O	0/35 oz/in ²	5	0.5	5	0.5
PGL-25L-100	40	0/100 inH ₂ O	0/60 oz/in ²	10	1	10	1
PGL-25L-160	40	0/160 inH ₂ O	—	20	2	—	—
PGL-25L-200	40	0/200 inH ₂ O	—	20	2	—	—
PGL-25L-300	40	0/300 inH ₂ O	—	50	5	—	—

* 2% first 10%, 1% middle 80%, 2% last 10%.

Note: Cannot be oxygen cleaned.

Ordering Example: PGL-25L-100, low-pressure gauge with 0 to 100 inH₂O range, \$40.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters