

# OMEGA® KFH SERIES PRE-WIRED STRAIN GAGES

**IN STOCK!**  
**For Fast Delivery**  
**Visit [omega.com/kfh](http://omega.com/kfh)**




**Proven Omega  
Quality Strain Gages  
with Two or Three  
Wires Attached  
to Make  
Installation Easy!**



**Fast  
Delivery!**

- ✓ No Soldering at the Measuring Point
- ✓ Each Gage has 50 mm of PTFE Cable before Transitioning to AWG 28 Leads to Prevent Leads from Adhering During Installation
- ✓ Short, Medium and Long Grid Linear Gages
- ✓ Short and Medium Grid XY Gages (T-Rosettes)
- ✓ Short and Medium Grid 0°/45°/90° Planar Rosettes
- ✓ Rugged Polyimide Carrier
- ✓ Fully Encapsulated Gages for Protection from the Environment



Strain gage  
shown actual size.

STRAIN GAGES 



# PRE-WIRED STRAIN GAGES

## PRECISION LINEAR PATTERN

### KFH Series

2- or 3-Wire Models


120 or 350 Ω

0.6 to 20 mm Grid Lengths

- ✓ Pre-Wired for Fast Installation
- ✓ No Soldering at Measurement End
- ✓ Broad Temperature Range
- ✓ 2- or 3-Wire Models
- ✓ Clear Alignment Marks








- ✓ Bonds with Hot or Cold Cure Adhesives
- ✓ PTFE Wire at Attachment End Prevents Sticking During Installation

Linear pattern precision gages with miniature and medium length grids are for general purpose and stress analysis applications. Available with either two 1-meter leads or three 3-meter leads and 120 or 350 Ω resistance. All models are compensated for steel.



Strain gage shown larger than actual size.

To Order Visit [omega.com/kfh](http://omega.com/kfh) for Pricing and Details

GAGE PATTERN Leads not shown	MODEL NO. Pkg of 10	NOM. RESISTANCE (Ω)	DIMENSIONS mm (inch)				MAX V* (Vrms)	TEMP COMP	TERMINATION AND LEAD LENGTH
			GRID		CARRIER				
			A	B	C	D			
 Shown larger than actual size, 0.3 mm	<b>0.3 mm GRID</b>								
	KFH-03-120-C1-11L1M2R	120	0.3 (0.012)	1.96 (0.077)	4.5 (0.18)	3.9 (0.15)	1.5	ST	Two 1 m leads
KFH-03-120-C1-11L3M2R	120					1.5	ST	Three 3 m leads	
 Shown larger than actual size, 0.6 mm	<b>0.6 mm GRID</b>								
	KFH-06-120-C1-11L1M2R	120	0.6 (0.024)	1.1 (0.043)	4.8 (0.19)	3.9 (0.15)	1.5	ST	Two 1 m leads
KFH-06-120-C1-11L3M3R	120					1.5	ST	Three 3 m leads	
 Shown larger than actual size, 1.5 mm	<b>1.5 mm GRID</b>								
	KFH-1.5-120-C1-11L1M2R	120	1.5 (0.059)	1.5 (0.059)	5.8 (0.23)	3.9 (0.15)	2.5	ST	Two 1 m leads
KFH-1.5-120-C1-11L3M3R	120					2.5	ST	Three 3 m leads	
Shown actual size, 3 mm 	<b>3 mm GRID</b>								
	KFH-3-120-C1-11L1M2R	120	3.0 (0.118)	2.0 (0.079)	7.4 (0.29)	3.9 (0.15)	4	ST	Two 1 m leads
	KFH-3-120-C1-11L3M3R	120					4	ST	Three 3 m leads
	KFH-3-350-C1-11L1M2R	350					9	ST	Two 1 m leads
KFH-3-350-C1-11L3M3R	350	9					ST	Three 3 m leads	
Shown actual size, 6 mm 	<b>6 mm GRID</b>								
	KFH-6-120-C1-11L1M2R	120	6.0 (0.24)	2.0 (0.079)	10.5 (0.41)	3.9 (0.15)	8	ST	Two 1 m leads
	KFH-6-120-C1-11L3M3S	120					8	ST	Three 3 m leads
	KFH-6-350-C1-11L1M2R	350					15	ST	Two 1 m leads
KFH-6-350-C1-11L3M3R	350	15					ST	Three 3 m leads	
Shown actual size, 10 mm 	<b>10 mm GRID</b>								
	KFH-10-120-C1-11L1M2R	120	10 (0.39)	3.0 (0.12)	14.8 (0.58)	4.8 (0.19)	14	ST	Two 1 m leads
KFH-10-120-C1-11L3M3R	120					14	ST	Three 3 m leads	
Shown actual size, 20 mm 	<b>20 mm GRID</b>								
	KFH-20-120-C1-11L1M2R	120	20 (0.79)	3.0 (0.12)	25.2 (0.99)	4.8 (0.19)	7	ST	Two 1 m leads
KFH-20-120-C1-11L3M3R	120					7	ST	Three 3 m leads	

### ACCESSORIES

MODEL NO.	DESCRIPTION
TT300	Complete heat cure adhesive kit
SG496	1 oz methyl-based cyanoacrylate (approximately 750 gages)
SG401	0.1 oz ethyl-based cyanoacrylate (approximately 50 gages)

\* Maximum permitted bridge energizing voltage (Vrms)

Ordering Examples: *KFH-1.5-120-C1-11L1M2S*, a linear 1.5 mm grid, 120 Ω, with two 1 m leads.

*KFH-3-350-C1-11L3M3S*, a linear 3 mm grid, 350 Ω, with three 3 m leads per grid.



# PRE-WIRED STRAIN GAGES

## PRECISION PLANAR X-Y PATTERN



### KFH Series

2- or 3-Wire Models


120 or 350 Ω

0.6 to 6 mm Grid Lengths

- ✓ Pre-Wired for Fast Installation
- ✓ No Soldering at Measurement End
- ✓ Broad Temperature Range
- ✓ 2- or 3-Wire Models
- ✓ Clear Alignment Marks





- ✓ Bonds with Hot or Cold Cure Adhesives
- ✓ PTFE Wire at Attachment End Prevents Sticking During Installation

The planar XY pattern allows precision strain measurement by eliminating the errors often associated with a stacked XY pattern. These gages are available with either two 1-meter leads or three 3-meter leads per grid and are compensated for steel.



**Dimensions Key:**  
**GRID**  
**A:** Active gage length  
**B:** Active gage width  
**CARRIER**  
**C:** Matrix length  
**D:** Matrix width

To Order Visit [omega.com/kfh](http://omega.com/kfh) for Pricing and Details

GAGE PATTERN Leads not shown	MODEL NO. Pkg of 10	NOM. RESIS- TANCE (Ω)	DIMENSIONS mm (inch)				MAX V* (VRMS)	TEMP COMP	TERMINATION AND LEAD LENGTH PER GRID
			GRID		CARRIER				
			A	B	C	D			
 Shown larger than actual size, 0.6 mm	<b>0.6 mm GRID</b>								
	KFH-06-120-D16-11L1M2S	120	0.6	1.0	5.1	6.9	1.5	ST	Two 1 m leads
	KFH-06-120-D16-11L3M3S	120	(0.024)	(0.039)	(0.20)	(0.27)	1.5	ST	Three 3 m leads
 Shown larger than actual size, 1.5 mm	<b>1.5 mm GRID</b>								
	KFH-1.5-120-D16-11L1M2S	120	1.5	1.6	5.8	6.9	3	ST	Two 1 m leads
	KFH-1.5-120-D16-11L3M3S	120	(0.059)	(0.063)	(0.23)	(0.27)	3	ST	Three 3 m leads
Shown actual size, 3 mm 	<b>3 mm GRID</b>								
	KFH-3-120-D16-11L1M2S	120	3.0	3.2	7.5	9.4	5.5	ST	Two 1 m leads
	KFH-3-120-D16-11L3M3S	120					5.5	ST	Three 3 m leads
	KFH-3-350-D16-11L1M2S	350	(0.12)	(0.13)	(0.30)	(0.37)	10	ST	Two 1 m leads
	KFH-3-350-D16-11L3M3S	350					10	ST	Three 3 m leads
Shown actual size, 6 mm 	<b>6 mm GRID</b>								
	KFH-6-120-D16-11L1M2S	120	6.0	6.3	11	16	11	ST	Two 1 m leads
	KFH-6-120-D16-11L3M3S	120					11	ST	Three 3 m leads
	KFH-6-350-D16-11L1M2S	350	(0.24)	(0.25)	(0.43)	(0.63)	20	ST	Two 1 m leads
	KFH-6-350-D16-11L3M3S	350					20	ST	Three 3 m leads

### ACCESSORIES

MODEL NO.	DESCRIPTION
TT300	Complete heat cure adhesive kit
SG496	1 oz methyl-based cyanoacrylate (approximately 750 gages)
SG401	0.1 oz ethyl-based cyanoacrylate (approximately 50 gages)

\* Maximum permitted bridge energizing voltage (Vrms)

Ordering Examples: **KFH-1.5-120-D16-11L1M2S**, two 1.5 mm grids in a planar XY pattern, 120 Ω, with two 1 m leads per grid.  
**KFH-3-350-D16-11L3M3S**, two 3 mm grids in a planar XY pattern, 350 Ω, with three 3 m leads per grid.



# PRE-WIRED STRAIN GAGES

## PLANAR 0°/45°/90° ROSETTE PATTERN


### KFH Series

2- or 3-Wire Models  
120 or 350 Ω  
0.6 to 6 mm Grid Lengths





- ✓ Pre-Wired for Fast Installation
- ✓ No Soldering at Measurement End
- ✓ Broad Temperature Range
- ✓ 2- or 3-Wire Models
- ✓ Clear Alignment Marks

- ✓ Bonds with Hot or Cold Cure Adhesives
- ✓ PTFE Wire at Attachment End Prevents Sticking During Installation

The planar rosette pattern allows precision strain measurement by eliminating the errors often associated with a stacked pattern. These gages are available with either two 1-meter leads or three 3-meter leads per grid and are compensated for steel.



To Order Visit [omega.com/kfh](http://omega.com/kfh) for Pricing and Details

GAGE PATTERN Leads not shown	MODEL NO. Pkg of 10	NOM. RESIS- TANCE (Ω)	DIMENSIONS mm (inch)				MAX V* (VRMS)	TEMP COMP	TERMINATION AND LEAD LENGTH PER GRID
			GRID		CARRIER				
			A	B	C	D			
 Shown larger than actual size, 0.6 mm	<b>0.6 mm GRID</b>								
	KFH-06-120-D17-11L1M2S	120	0.6	1.1	4.8	9.9	1.6	ST	Two 1 m leads
	KFH-06-120-D17-11L3M3S	120	(0.024)	(0.043)	(0.19)	(0.39)	1.6	ST	Three 3 m leads
 Shown larger than actual size, 1.5 mm	<b>1.5 mm GRID</b>								
	KFH-1.5-120-D17-11L1M2S	120	1.5	1.5	5.8	10.2	2.5	ST	Two 1 m leads
	KFH-1.5-120-D17-11L3M3S	120	(0.059)	(0.059)	(0.23)	(0.40)	2.5	ST	Three 3 m leads
Shown actual size, 3 mm 	<b>3 mm GRID</b>								
	KFH-3-120-D17-11L1M2S	120	3.0	2.0	7.4	13.9	3	ST	Two 1 m leads
	KFH-3-120-D17-11L3M3S	120					3	ST	Three 3 m leads
	KFH-3-350-D17-11L1M2S	350	(0.12)	(0.079)	(0.29)	(0.55)	5.5	ST	Two 1 m leads
	KFH-3-350-D17-11L3M3S	350	(0.12)	(0.079)	(0.29)	(0.55)	5.5	ST	Three 3 m leads
Shown actual size, 6 mm 	<b>6 mm GRID</b>								
	KFH-6-120-D17-11L1M2S	120	6.0	2.0	10.5	18.7	7.5	ST	Two 1 m leads
	KFH-6-120-D17-11L3M3S	120					7.5	ST	Three 3 m leads
	KFH-6-350-D17-11L1M2S	350	(0.24)	(0.079)	(0.41)	(0.74)	13	ST	Two 1 m leads
	KFH-6-350-D17-11L3M3S	350	(0.24)	(0.079)	(0.41)	(0.74)	13	ST	Three 3 m leads

### ACCESSORIES

MODEL NO.	DESCRIPTION
TT300	Complete heat cure adhesive kit
SG496	1 oz methyl-based cyanoacrylate (approximately 750 gages)
SG401	0.1 oz ethyl-based cyanoacrylate (approximately 50 gages)

\* Maximum permitted bridge energizing voltage (Vrms)

Ordering Examples: **KFH-1.5-120-D17-11L1M2S**, three 1.5 mm grids in a planar 0°/45°/90° pattern, 120 Ω, with two 1 m leads per grid.  
**KFH-3-350-D17-11L3M3S**, three 3 mm grids in a planar 0°/45°/90° pattern, 350 Ω, with three 3 m leads per grid.

## SPECIFICATIONS

<b>Strain Gage Construction</b> <b>Measuring Grid</b> Material Thickness <b>Carrier</b> Material Thickness <b>Connections</b>	       	Foil strain gage with embedded measuring grid  Constantan 3.8 or 5 (150 or 197), depending upon strain gage type  Polyimide 45 ± 10 (1.772 ± 394)  PTFE wire, Ø - 0.051 mm <sup>2</sup> , approximately 50 mm long, connected to AWG 28 ribbon cables (PVC insulated) through solder sleeves in 2- or 3-wire configurations
<b>Nominal Resistance</b> <sup>1</sup> <b>Resistance Tolerance</b> <sup>1</sup> with 0.6 mm and 1.5 mm grid length <b>Gage Factor</b> <b>Gage Factor Tolerance</b> with 0.6 mm and 1.5 mm grid length Temperature coefficient of gage factor Nominal value of gage factor temperature coefficient	 Ω % % % % 1/K [1/°F]	120 or 350 depending upon gage ±0.35 ±1 approximately 2 (stated on package) ±1 ±1.5 (115 ± 10) x 10 <sup>-6</sup> [(64 ± 5.5) x 10 <sup>-6</sup> ] Specified on each package
<b>Reference Temperature</b> <b>Operating Temperature Range</b> for static measurement (zero point related) for dynamic measurement (not zero point related)	 °C (°F) °C (°F) °C (°F)	23 PTFE cable -10 to 155 (-14 to 320) -10 to 155 (-14 to 320)
<b>Transverse Sensitivity</b> for linear 3 mm 120Ω gage	%	±0.2
<b>Temperature Response</b> Temperature response as required, adapted to coefficient of thermal expansion α for aluminum α for plastic material α for austenitic steel α for titanium α for molybdenum α for quartz Tolerance of temperature response	 1/K [1/°F] 1/K [1/°F] 1/K [1/°F] 1/K [1/°F] 1/K [1/°F] 1/K [1/°F] °C (°F)	Specified on each package  10.8 x 10 <sup>-6</sup> (6.0 x 10 <sup>-6</sup> ) 23 x 10 <sup>-6</sup> (12.8 x 10 <sup>-6</sup> ) 65 x 10 <sup>-6</sup> (36.1 x 10 <sup>-6</sup> ) 16 x 10 <sup>-6</sup> (8.9 x 10 <sup>-6</sup> ) 9 x 10 <sup>-6</sup> (5.0 x 10 <sup>-6</sup> ) 5.4 x 10 <sup>-6</sup> (3.0 x 10 <sup>-6</sup> ) 0.05 x 10 <sup>-6</sup> (0.3 x 10 <sup>-6</sup> ) -10 to 120 (-14 to 248)
<b>Mechanical Hysteresis</b> 1) at reference temperature and strain $L = 1000 \mu\text{m}/\text{m}$ (microstrain) on linear 3 mm 120Ω gage at 1 <sup>st</sup> load cycle and adhesive SG496 at 3 <sup>rd</sup> load cycle and adhesive SG496	 μm/m (microstrain) μm/m (microstrain)	 1 0.5
<b>Maximum Elongation</b> at reference temperature on linear 3 mm 120Ω gage Absolute strain value for positive direction Absolute strain value for negative direction	 μm/m (microstrain) μm/m (microstrain)	 20,000 ± 2% 25,000 ± 2.5%
<b>Fatigue Life</b> at reference temperature on linear 3 mm 120Ω gage <b>Achievable Number of Load Cycles <math>L_w</math> at Alternating Strain <math>L_w = \pm 1000 \mu\text{m}/\text{m}</math> and</b> zero point variation ≤ 300 zero point variation ≤ 30	 μm/m (microstrain) μm/m (microstrain)	 >1 x 10 <sup>7</sup> (test was stopped) 5 x 10 <sup>6</sup>
<b>Minimum Radius of Curvature, Longitudinal and Transverse, at Reference Temperature</b> within measuring grid area within solder tab area <b>Applicable Bonding Materials</b> <b>Cold Cure Adhesives</b> <b>Heat Cure Adhesives</b>	 mm (inch) mm (inch)	 0.3 (0.012) 10 (0.394) SG496, SG401 TT300



# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters