

GENERAL PURPOSE PRESSURE SWITCHES IN NEMA 4X (IP66) ENCLOSURES

PSW-100 Series Vacuum to 3000 psi

Starts at
\$123



- ✓ Ranges from 0.5 inH₂O to 3000 psi
- ✓ SPDT or DPDT Switches
- ✓ Adjustment Lock
- ✓ Safe, Easy Wiring Access

OMEGA's affordable, general purpose pressure switches offer distinct advantages over most similar-style switches, including DPDT or adjustable deadband switches, as well as a wide selection of adjustable ranges from 0.5 inH₂O to 3000 psi.

SPECIFICATIONS

Approval: UL listed, CSA certified

Storage Temperature: -55 to 70°C (-67 to 158°F)

Process Temperature:

Stainless Steel:

-55 to 205°C (-67 to 401°F)

Phosphor Bronze:

-40 to 150°C (-40 to 302°F)

Buna-N: -25 to 95°C (-13 to 203°F)

Ambient Temperature: -40 to 70°C (-40 to 158°F), except models PSW-107 to PSW-117 and PSW-134 to PSW-139: -20 to 70°C (-4 to 158°F); setpoint typically shifts less than 1% of range for a 30°C (54°F) ambient temperature change

Shock: Setpoint repeats after 15 g, 10 ms duration

Vibration: Setpoint repeats after 2.5 g, 5 to 500 Hz

Setpoint Repeatability: All models ±1% of adjustable range, except models PSW-118 to PSW-125 and PSW-132 to PSW-133, which are ±1.5%

Switch Output: One SPDT or DPDT switch can be wired "normally open" or "normally closed"

Electrical Rating: Standard 15 A 125/250/480 Vac resistive

External Manual Reset: 15 A 125/250 Vac resistive

PSW-114, \$106, shown smaller than actual size.

Double Pole Double Throw: 10 A 125/250 Vac resistive

Enclosure: Die-cast aluminum (max 0.6% copper); epoxy-coated blue enclosure, gasketed, complies with NEMA 4X (IP66)

Weight: Approximately 0.9 kg (2 lb)


Electrical Connection: ½ NPT and two ¼" diameter knockouts

Pressure Connection: See "To Order" on next page

Dimensions: 191 max H x 101 W x 60 mm D (7.5 x 4 x 2.3")



PSW-114, \$106, shown smaller than actual size.



Gasketed Cover

Long-Life Switch

Vibration-Resistant Setpoint and Scale

Rugged NEMA 4X (IP66) Enclosure



GENERAL PURPOSE PRESSURE SWITCHES

 **MOST POPULAR MODELS HIGHLIGHTED!**

PRESSURE SWITCHES **H**

To Order (Specify Model Number)							
MODEL NO.	PRICE	ADJUSTABLE RANGE		DEADBAND STANDARD UNITS	PROOF PRESSURE	SWITCH	ADDED FEATURE
		STANDARD	METRIC				
BUNA-N DIAPHRAGM, O-RING AND ¼ NPTF NICKEL-PLATED BRASS PRESSURE CONNECTION							
PSW-107	\$123	1.5 to 30 psi	0.1 to 2 bar	1 to 2 psi	600 psi	15 A SPDT	—
PSW-108	123	3 to 100 psi	0.2 to 6.9 bar	1 to 4 psi	600 psi	15 A SPDT	—
PSW-109	157	3 to 100 psi	0.2 to 6.9 bar	—	600 psi	15 A SPDT	External Manual Reset
PSW-110	201	3 to 100 psi	0.2 to 6.9 bar	11.3 Typ.	600 psi	10 A DPDT	DPDT Switch
PSW-111	149	3 to 100 psi	0.2 to 6.9 bar	3 to 7 psi	600 psi	15 A SPDT	Adjustable Deadband
PSW-112	123	9 to 300 psi	0.7 to 20.7 bar	1 to 5 psi	600 psi	15 A SPDT	—
PSW-113	149	9 to 300 psi	0.7 to 20.7 bar	4 to 11 psi	600 psi	15 A SPDT	Adjustable Deadband
PSW-114	123	15 to 500 psi	1 to 34.5 bar	2 to 8 psi	2500 psi	15 A SPDT	—
PSW-115	149	15 to 500 psi	1 to 34.5 bar	5 to 12 psi	2500 psi	15 A SPDT	Adjustable Deadband
PSW-116	157	15 to 500 psi	1 to 34.5 bar	—	2500 psi	15 A SPDT	External Manual Reset
PSW-117	123	30 to 1000 psi	2 to 69 bar	3 to 20 psi	2500 psi	15 A SPDT	—
BUNA-N DIAPHRAGM, O-RING AND ½ NPTF ALUMINUM PRESSURE CONNECTION							
PSW-134	\$296	300 inWC vac to 0 inWC	747.24 to 0 mbar	0.2 to 8 inWC	400 psi	15 A SPDT	—
PSW-135	296	10 inWC vac to 10 inWC	-24.91 to 24.91 mbar	0.1 to 0.6 inWC	400 psi	15 A SPDT	—
PSW-136	296	50 inWC vac to 50 inWC	-124.54 to 124.54 mbar	0.1 to 3.0 inWC	400 psi	15 A SPDT	—
PSW-137	296	0.5 to 5 inWC	1.25 to 12.45 mbar	0.1 to 0.3 inWC	400 psi	15 A SPDT	—
PSW-138	296	2.5 to 50 inWC	6.23 to 124.54 mbar	0.1 to 0.8 inWC	400 psi	15 A SPDT	—
PSW-139	296	10 to 250 inWC	24.91 to 622.70 mbar	0.1 to 6.0 inWC	400 psi	15 A SPDT	—
316 SS DIAPHRAGM AND ½ NPTF PRESSURE CONNECTION*							
PSW-104	\$266	1 to 20 psi	70 mbar to 1.4 bar	0.1 to 1 psi	500 psi	15 A SPDT	—
PSW-105	266	2 to 50 psi	140 mbar to 3.4 bar	0.1 to 1.5 psi	500 psi	15 A SPDT	—
PSW-118	148	5 to 30 psi	0.4 to 2 bar	1 to 3 psi	2500 psi	15 A SPDT	—
PSW-120	148	10 to 100 psi	0.7 to 6.9 bar	1 to 8 psi	2500 psi	15 A SPDT	—
PSW-121	148	15 to 300 psi	1 to 20.7 bar	3 to 18. psi	2500 psi	15 A SPDT	—
PSW-123	174	15 to 300 psi	1 to 20.7 bar	3 to 18 psi	2500 psi	15 A SPDT	Adjustable Deadband
PSW-124	148	20 to 500 psi	1.4 to 34.5 bar	4 to 30 psi	2500 psi	15 A SPDT	—
PSW-125	148	80 to 1700 psi	5.5 to 117 bar	5 to 120 psi	2500 psi	15 A SPDT	—
PHOSPHOR BRONZE BELLOWS AND ¼ NPTF BRASS PRESSURE CONNECTION							
PSW-127	\$141	30 inHg vac to 0	-1 to 0 bar	1 to 2 inHg	0 psi	15 A SPDT	—
PSW-128	219	30 inHg vac to 0	-1 to 0 bar	3 to 6.5 inHg	0 psi	10 A DPDT	DPDT Switch
PSW-129	141	4 to 200 psi	0.3 to 13.7 bar	1 to 4 psi	250 psi	15 A SPDT	—
316 SS BELLOWS AND ¼ NPTF PRESSURE CONNECTION							
PSW-130	\$204	15 to 200 psi	1 to 13.7 bar	1 to 3 psi	250 psi	15 A SPDT	—
PSW-131	204	25 to 500 psi	1.8 to 34.5 bar	1.5 to 5 psi	575 psi	15 A SPDT	—
PSW-132	257	100 to 1700 psi	6.9 to 11.7 bar	9 to 40 psi	2500 psi	15 A SPDT	—
303 SS PISTON, BUNA N O-RING AND ¼ NPTF SS PRESSURE CONNECTION							
PSW-133	\$177	125 to 3000 psi	8.6 to 206 bar	40 to 250 psi	10000 psi	15 A SPDT	—

* Note: The use of metallic diaphragms where higher pressures, shock or heavy cycling is expected should be avoided. When choosing a pressure range, it is recommended that the switch operate in the middle 80% of its adjustable range. Switching may not be accurate in the lower and upper 10% of the range. Switches come with complete operator's manual.
Oxygen Clean Option: Available on -SS models only; add suffix "-X6B", \$85.
Ordering Example: PSW-115, Buna-N diaphragm, ¼ brass NPTF thread, range of 50 to 500 psi and adjustable deadband, \$149.

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
CM-4425	\$105	Reference Book: Liquid Filtration



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters