



SILICON/BRASS PRESSURE TRANSMITTER WITH 4 TO 20 mA OUTPUT

PX182B Series

Starts at
\$210



- ✓ Digitally Compensated for Excellent Total Accuracy and Interchangeability
- ✓ Gage Pressure, Vacuum, and Compound Ranges Available
- ✓ Rugged, Compact Design
- ✓ 2-Wire 4 to 20 mA Current Loop Output
- ✓ RFI/EMI Protection
- ✓ Reverse Polarity Protection

OMEGA's PX182B Series transducers, designed for general industrial and commercial requirements, offer excellent performance in a wide range of applications. They are based on proven micro-machined silicon technology, providing high reliability, long-term stability, and low cost.

The PX182B is fully digitally compensated for the effects of pressure and temperature change. It is extremely accurate, with less than 0.3% FS reference accuracy and less than 1% FS over its compensated temperature range.

SPECIFICATIONS

Excitation: 11 to 30 Vdc

Output: 4 to 20 mA (2 wire)

Accuracy: 0.3% BFSL maximum (includes linearity, hysteresis and repeatability)

Total Error Band: 1% FS (includes temperature effects within compensated temperature range)

Operating Temperature: -40 to 80°C (-40 to 176°F)

Compensated Temperature: -25 to 75°C (-13 to 167°F)

Process Temperature: -40 to 100°C (-40 to 212°F)

1-Year Stability: <0.25% FS

PX182B-100GI, \$210, shown larger than actual size.



WIRING:
Red +
Black -



Proof Pressure: 2x FS (750 psig for 500 psig range)
Burst Pressure: 3x FS or 750 psig, whichever is less
Wetted Parts: Brass, borosilicate, silicon, RTV and epoxy
Vibration: 10 g, 55 to 2000 Hz

Shock: 30 g
Process Connection: 1/8 NPT male
Electrical Connection: 0.4 m (18") 24-gage cable
Weight: 142 g (5 oz)
Dimensions: 1 1/8 hex; 72 H x 29.7 mm Dia. (2.84 x 1.17")

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

GAGE PRESSURE RANGES

psi	bar	MODEL NO.	PRICE	COMPATIBLE METERS*
0 to -14.7	0 to -1.0	PX182B-015VACI	\$210	DP24-E, DP25B-E, DP41-E, DPi Series
0 to 1	0 to 68.9 mbar	PX182B-001GI	230	DP24-E, DP25B-E, DP41-E, DPi Series
0 to 6	0 to 414 mbar	PX182B-006GI	210	DP24-E, DP25B-E, DP41-E, DPi Series
0 to 15	0 to 1.0	PX182B-015GI	210	DP24-E, DP25B-E, DP41-E, DPi Series
0 to 30	0 to 2.1	PX182B-030GI	210	DP24-E, DP25B-E, DP41-E, DPi Series
0 to 60	0 to 4.1	PX182B-060GI	210	DP24-E, DP25B-E, DP41-E, DPi Series
0 to 100	0 to 6.9	PX182B-100GI	210	DP24-E, DP25B-E, DP41-E, DPi Series
0 to 200	0 to 13.8	PX182B-200GI	210	DP24-E, DP25B-E, DP41-E, DPi Series
0 to 300	0 to 20.7	PX182B-300GI	210	DP24-E, DP25B-E, DP41-E, DPi Series
0 to 500	0 to 34.5	PX182B-500GI	210	DP24-E, DP25B-E, DP41-E, DPi Series
-14.7 to 15	-1.0 to 1.0	PX182B-015CI	210	DP24-E, DP25B-E, DP41-E, DPi Series
-14.7 to 30	-1.0 to 2.1	PX182B-030CI	210	DP24-E, DP25B-E, DP41-E, DPi Series
-14.7 to 60	-1.0 to 4.1	PX182B-060CI	210	DP24-E, DP25B-E, DP41-E, DPi Series

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
PS-8E	\$10	Pressure snubber for water or light oils
PS-8D	10	Pressure snubber for dense liquids or oils
PS-8G	10	Pressure snubber for gases and steam
PE-1011	110	Reference Book: Instrumentation for Engineering Measurements

* See section D for compatible meters.

Comes with complete operator's manual.

Ordering Example: PX182B-100GI, 0 to 100 psig transducer with 4 to 20 mA output, \$210.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters