

# RUGGED, HANDHELD PROCESS CALIBRATORS

## PORTABLE VOLTAGE AND CURRENT CALIBRATORS

- ✓ Backlighted Display for Visibility in Low-Light Areas or at Night
- ✓ Midrange Key Sets
- ✓ Output to 1 V, 10 V, or 10 mA Depending on Preselected Range
- ✓ Built-In 20 V Supply for Driving Current Loop
- ✓ 2 Modes of Operation (Source and Simulate)

PCL422A  
**\$625**



PCL422A, \$625, shown smaller than actual size, comes with lead set, soft carrying case, 9 V battery and complete operator's manual.



## SPECIFICATIONS

**Accuracy:** 0.05% FS  
**Ranges:** 0 to 19.99 mA, 0 to 1.999 V, 0 to 19.99 V  
**Operating Temperature:** -18 to 40°C (0 to 104°F)  
**Temperature Stability:** 50 ppm/°C  
**Power:** 9 V battery (included)  
**Weight:** 340 g (12 oz)

PCL401  
**\$229**



PCL401, \$229, shown smaller than actual size, comes with 203 mm (8") leads with alligator clips, 9 V battery and complete operator's manual.



## MINIATURE LOOP CALIBRATORS

- ✓ 5 Precalibrated Settings: 4, 8, 12, 16, and 20 mA
- ✓ Easy One-Handed Operation

### Two Operating Modes

1. **Source:** Unit Controls Loop Current and Provides Loop Excitation Up to 30 Vdc
2. **Simulate:** Unit Controls Loop Current Using External Loop Power Supply

## SPECIFICATIONS

**Accuracy:** +0.075% FS  
**Temperature Stability:** 100 ppm/°C  
**Internal Power:** 9 V battery (included)  
**External Power:** Up to 30 Vdc max  
**Max Loop Resistance:** 300 Ω  
**Operating Temperature:** -18 to 49°C (0 to 120°F)  
**Power:** 9 V battery (included)  
**Battery Life:** >25 hr  
**Dimensions:** 25 H x 61 W x 96.5 mm D (1.0 x 2.4 x 3.8")  
**Weight:** 227 g (8 oz)

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters