



SENSITIVE PRESSURE, VACUUM, OR DIFFERENTIAL PRESSURE SWITCHES

PSW20 Series

All Models
\$30



These sensitive single-pole switches can be used as pressure, vacuum, or differential switches.

SPECIFICATIONS

Approvals: UL recognized, CSA certified

Temperature: -30 to 65°C (-23 to 149°F)

Setpoint Accuracy: ±10% of setting at 21°C (70°F)

Note: Pressure settings may change over the temperature range.

Materials of Construction

Body: Acetal

Diaphragm: EPDM bonded to steel ring

Contacts: Gold-plated silver

Springs: Plated phosphor bronze

Terminals: Plated copper or brass

Pressure Connection:

Spout for 1/8" ID tubing


Adjusting Screw:

Stainless steel or zinc-plated steel; setting as shipped, 2 inH₂O negligible deadband


Media: Clean, dry, non-corrosive gases only

Note: The pressure media entering through port A are in direct contact with the electrical contacts in the switch. The media entering through port B are separated from the electrical contacts by the diaphragm.

Weight: 9 g (0.3 oz)



PSW20A, \$30, shown larger than actual size.



Pressure Switching—Normally Open Contacts

Connect the pressure source to inlet port B, and set the adjusting screw to the desired pressure setpoint. Turning the screw clockwise narrows the gap between contacts and decreases the setpoint. Turning the screw counterclockwise increases the gap, thereby increasing the setpoint.

Pressure Switching—Normally Closed Contacts

Connect the pressure source to port A and monitor continuity across the terminals. Slowly turn the adjusting screw clockwise, narrowing the gap

between the contacts until the contacts are closed. Apply the setpoint pressure, which will open the contacts. Continue to turn the adjusting screw clockwise until the contacts make and break at the desired setpoint.

Vacuum Switching: Repeat above using port A for normally open contacts and port B for normally closed contacts.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

MODEL NO.	PRICE	PRESSURE RANGE	PROOF PRESSURE	SWITCH RATING 250 Vac
PSW20A	\$30	0.4 to 15 inH ₂ O	8 psig	750 mA (resistive)
PSW20B	30	1 to 20 inH ₂ O	8 psig	1 A (resistive)

Ordering Example: PSW20A, sensitive differential pressure switch adjustable from 0.4 to 15 inH₂O column, \$30. Custom switches and pre-fixed setpoint at customer-specified value available, 50 piece minimum order.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters