

# ELECTRONICALLY CONTROLLED PROPORTIONING VALVES

## PV Series


Starts at  
**\$920**



- ✓ Programmable Direct- or Reverse-Acting Control
- ✓ Precision Control is Achieved via a 10-Bit Converter Controlling a 200 Step per Revolution Motor
- ✓ Rugged Construction for Industrial Applications
- ✓ External Safety Override Contacts to Open/Close Valve
- ✓ NEMA 4 (IP65) Rating for Outdoor Use
- ✓ Ideal for Liquid and Gas Applications

An electronically controlled proportioning valve (ECV) will take an electrical input signal (usually 4 to 20 mA) and proportion the amount of flow through a pipe from fully closed to fully open. The OMEGA® ECV valve features programmable direct-acting or reverse-acting control. Direct-acting means that, as the current signal rises, the valve allows more flow, while reverse-acting will decrease the flow rate with an increasing current signal.

These units can also be programmed to sense a failure in the current loop and fully close/open the valve when the signal level drops below 3.5 mA. Dry-contact remote switches can be used in conjunction with the standard current signal to provide an alarm signal that fully closes/opens the valve. An internal 5 Vdc signal is used to sense the state of the external switches.





Available with brass or stainless steel body.

The rugged epoxy-coated aluminum package ensures NEMA 4X (IP66) protection for the powerful microprocessor and servo actuator. Internally, a 10-bit A/D converter is positioning a 200 step/revolution stepper motor for precise flow. The

PV14-SS, \$1145, shown smaller than actual size.

stepper motor is directly connected to the valve stem without gearing, thereby eliminating backlash (hysteresis) effects. The valve can also be manually controlled with a screwdriver.





PV series valve (with cover removed).



## SPECIFICATIONS

### Electronics

**Power Requirements:** 12 Vdc @ 3 A

*Caution: Using an underrated power supply will damage the unit.*

**Inputs:** 4 to 20 mA control signal (250  $\Omega$  impedance) and dual external switch contact sensing via 5 Vdc signal

**Control Modes:** Direct or reverse, full or split range, high or low range, fail condition open or closed

**Adjustments:** Zero offset  $\pm 0.5$  mA

**Operating Temp:** 0 to 49°C (32 to 120°F)

**Enclosure:** NEMA 4X (IP66), epoxy-painted aluminum

**Connections:**  $\frac{1}{2}$  NPT conduit (16" 22 AWG pigtail leads)

### Actuator

**Type:** DC step motor, 200 steps/rev, 4 rev travel

**Resolution:** 200:1 (0.5%)  
(4 steps increment)

**Speed:** 45 rpm (5 s full stroke) except  $\frac{3}{4}$ " valves: 18 rpm (12 s) full stroke

**Torque:** 57.5 in-oz (188 in-oz  $\frac{3}{4}$  valve)

### Valve

**Type:** In-line globe

**Temp:** -18 to 120°C (0 to 250°F)

**Pressure:** 120 psi max (70 psi on  $\frac{3}{4}$ " valve)

**Max Flow:** GPM = Cv ( $\Delta P/SG$ )  $\frac{1}{2}$  liquids; for gases, use standard equation found on page L-27

**Wetted Parts:** Ethylene propylene rubber O-ring, PTFE washer and valve body (brass models have 303 SS internal trim)

### COMPLETE UNIT:

**Dimensions:** 216 H x 185 W x 137 mm D (8.5 x 7.3 x 5.4")

**$\frac{1}{2}$  Valve:** 229 H x 185 W x 137 mm D (9 x 7.3 x 5.4")

**$\frac{3}{4}$  Valve:** 305 H x 203 W x 191 mm D (12 x 8 x 7.5")

**Weight:** 3.2 kg (7 lb);  $\frac{1}{2}$  valve: 4.5 kg (10 lb);  $\frac{3}{4}$  valve: 8.2 kg (18 lb)

### U12Y100 SPECIFICATIONS:

**Power Supply:** 120 Vac or 240 Vac @ 50 to 60 Hz, switchable

**Output:** 12 Vdc unregulated @ 3 A

**Connections:** 2.1 m (7') power cord, 3-pin DIN connector with 1.8 m (6') 3-conductor 22 AWG, pigtail leads

**Dimensions:** 102 W x 152 L x 76 mm H (4 x 6 x 3")

**Weight:** 1.4 g (3 lb)

## MOST POPULAR MODELS HIGHLIGHTED!

### To Order (Specify Model Number)

MODEL NO.	PRICE	VALVE SIZE mm (in)	FITTING SIZE	C <sub>V</sub>	MAX FLOW @ 50 psi	BODY MATERIAL
PV14-B	\$920	6.35 ( $\frac{1}{4}$ )	$\frac{1}{2}$ NPT	0.6	4 GPM	Brass
PV14-SS	1145	6.35 ( $\frac{1}{4}$ )	$\frac{1}{2}$ NPT	0.6	4 GPM	316 SS
PV516-B	930	7.94 ( $\frac{5}{16}$ )	$\frac{1}{2}$ NPT	1.0	8 GPM	Brass
PV516-SS	1155	7.94 ( $\frac{5}{16}$ )	$\frac{1}{2}$ NPT	1.0	8 GPM	316 SS
PV38-B	950	9.53 ( $\frac{3}{8}$ )	$\frac{1}{2}$ NPT	1.7	12 GPM	Brass
PV38-SS	1170	9.53 ( $\frac{3}{8}$ )	$\frac{1}{2}$ NPT	1.7	12 GPM	316 SS
PV12-B	1140	12.70 ( $\frac{1}{2}$ )	$\frac{3}{4}$ NPT	3.5	24 GPM	Brass
PV12-SS	1420	12.70 ( $\frac{1}{2}$ )	$\frac{3}{4}$ NPT	3.5	24 GPM	316 SS
PV34-B	1510	19.05 ( $\frac{3}{4}$ )	1 NPT	6.5	45 GPM	Brass
PV34-SS	1890	19.05 ( $\frac{3}{4}$ )	1 NPT	6.5	45 GPM	316 SS
ACCESSORIES	PRICE	DESCRIPTION				
U12Y100	\$145	Unregulated power supply 12 Vdc, 3 A				
MS-1783	80	Reference Book: Bottom-Line Automation				

Comes complete with operator's manual.

**Ordering Examples:** PV14-B, 4 GPM brass proportioning valve, \$920.

U12Y100, unregulated power supply, \$145.





#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenpfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters