

PREMIUM TEMPERATURE COMPENSATION PRESSURE TRANSDUCER

STANDARD AND METRIC MODELS

mV/V Output

0-15 to 0-30,000 psi-Standard Units

0-1 to 0-400 bar-Metric Models

1 bar = 14.5 psi
 1 kg/cm² = 14.22 psi
 1 atmosphere = 14.7 psi
 = 29.93 inHg = 760.2 mmHg
 = 1.014 bar


STANDARD
 PX35D0-1KGV shown
 actual size.



PX35/PXM35 Series



- ✓ All Stainless Steel Construction
- ✓ 5-Point Calibration Standard
- ✓ Available in Gage, Sealed Gage, and Absolute Pressure Models



The OMEGA PX35/PXM35 are high-accuracy, millivolt output, industrial pressure transducers. They can be ordered with a hermetically sealed gage, making them suitable for the harshest environments. Both units are available in gage, sealed gage, and absolute models. Three meters (10') of 4-conductor shielded cable is standard. A twist-lock-connector electrical termination is also available.

SPECIFICATIONS

Excitation: 10 Vdc (15 V maximum)
Output: 3 mV/V nominal
Accuracy: 0.25% linearity, hysteresis and repeatability combined
Zero Balance: $\pm 2.0\%$ FSO
Input Resistance: 350 Ω minimum
Output Resistance: 315 to 530 Ω
Operating Temp Range: -73 to 149°C (-100 to 300°F)
Compensated Temp Range: 16 to 71°C (60 to 160°F)

Thermal Effects:

Span: 0.0054% rdg/°C
Zero: 0.008% FSO/°C

Proof Pressure:

150% of rated pressure

Burst Pressure:

300% of rated pressure

Wetted Parts:

17-4 PH stainless steel

Pressure Port:

See dimensional drawing above

Electrical Connection:

3 m (10') 4-conductor cable standard, or PTIH-10-6P

TEMPERATURE COMPENSATION PRESSURE TRANSDUCER



MILLIVOLT OUTPUT
PRESSURE TRANSDUCERS

B

STANDARD CUSTOM CONFIGURATIONS

PX35 SERIES	PRESSURE PORT [1]	ELECTRICAL CONNECTION [2]	RANGE (PSI) [3]	UNITS [4]	OUTPUT [5]	OPTIONS [6]
C = 1/4-18 NPT-M	cost no charge cost no charge as shown (ranges ≥ 10,000 psi)		10	A, G, S	V = mV/V Base price PX35D ≤1000 psi >1000 psi	OX = Cleaned for oxygen service + cost plus 2 weeks
D = 1/4-18 NPT-F			15	A, G, S		
J = 7/16-20 UNF-M			20	A, G, S		
K = 7/16-20 UNF-F			25	A, G, S		
S = 1/4 HP tube fitting			30	A, G, S		
			50	A, G, S		
			75	A, G, S		
			100	A, G, S		
			150	A, G, S		
			200	A, G, S		
			250	A, G, S		
			300	A, G, S		
			500	A, G, S		
			750	A, G, S		
			1K	A, G, S		
	1K	A, G, S				
	2K	A, G, S				
	2.5K	A, G, S				
	3K	A, G, S				
	3.5K	A, G, S				
	5K	A, G, S				
	7.5K	A, G, S				
	10K*	A, G, S				
	15K*	A, G, S				
	20K*	A, G, S				
	30K*	A, G, S				

0 = 3 m (10') cable (std)
add cost per (ft)
over 3 m (10')

1 = PT1H-10-6P connector (or equal, no charge).
Mating connector (sold separately), order **PT06F10-6S**

See omega.com for additional options including extended compensated temperatures.

* 7/16-18, 1/4" HP tube connection

To order a custom configuration:


1. Select a pressure port
2. Select electrical connection
3. Select a pressure range
4. Select pressure units – absolute gage or sealed gage
5. Select output
6. Select options

Ordering Examples: *PX35K1-300GV*, 300 psi gage pressure transducer with 7/16-20 UNF female connection and PT1H-10-6P connector, **PT06F10-6S**, mating connector (sold separately).


PX35S1-15KGV, 15,000 psi gage pressure transducer with 7/16-18, 1/4" HP tube connection and PT1H-10-6P connector.

PT06F10-6S, mating connector (sold separately)

CA-4TE24-2-015, cable assembly with twist lock connector (sold separately).



G 1/4 Pressure Snubbers:
PS-4G-MG = Gas
PS-4E-MG = Lt Oil
PS-4D-MG = Dense Liquid



1/4 NPT Pressure Snubbers:
PS-4G = Gas
PS-4E = Lt Oil
PS-4D = Dense Lq

METRIC CUSTOM CONFIGURATIONS

PXM35 SERIES	PRESSURE PORT [1]	ELECTRICAL CONNECTION [2]	RANGE (BAR) [3]	UNITS [4]	OUTPUT [5]	OPTIONS [6]
MB = G 1/8 B Female	no charge no charge 0 = 3 m (10') cable (std) add cost per/m over 3 m (10') 1 = PT1H-10-6P connector (or equal, no charge). Mating connector (sold separately), order PT06F10-6S		1.0	A, G, S	V = mV/V Base price PXM35 <100 bar ≥100 bar	OX = Cleaned for oxygen service + cost plus 2 weeks
MD = G 1/8 B Female			1.6	A, G, S		
			2.5	A, G, S		
			4.0	A, G, S		
			6.0	A, G, S		
			10	A, G, S		
			16	A, G, S		
			25	A, G, S		
			40	A, G, S		
			60	A, G, S		
			100	A, G, S		
			160	A, G, S		
			250	A, G, S		
			400	A, G, S		

See omega.com for additional options including extended compensated temperatures.

To order a custom configuration:

1. Select a pressure port
2. Select electrical connection
3. Select a pressure range
4. Select pressure units – absolute, gage or sealed gage
5. Select output
6. Select options

Ordering Examples: *PXM35MB0-010BARSV*, 10 bar sealed gage pressure transducer with G 1/8 B female connection and 3 m (10') cable termination.

PXM35MD1-010BARAV, 10 bar absolute pressure transducer with G 1/8 B female connection and twist-lock connector. **PT06F10-6S**, mating connector (sold separately).

PREMIUM TEMPERATURE COMPENSATED PRESSURE TRANSDUCER

STANDARD
PX35D0-1KGV shown
actual size.



STANDARD MODELS

To Order Visit omega.com/px35d0 for Pricing and Details

RANGE		MODEL NO.	COMPATIBLE METERS*
ABSOLUTE PRESSURE (All Ranges Available in Absolute Pressure)			
0 to 30 psia	0 to 2.1 bar	PX35D0-030AV	DP41-S, DP25B-S
0 to 50 psia	0 to 3.4 bar	PX35D0-050AV	DP41-S, DP25B-S
0 to 100 psia	0 to 6.9 bar	PX35D0-100AV	DP41-S, DP25B-S
0 to 150 psia	0 to 10.3 bar	PX35D0-150AV	DP41-S, DP25B-S
GAGE PRESSURE (All Ranges Also Available in Sealed Gage Pressure)			
0 to 20 psi	0 to 1.4 bar	PX35D0-020GV	DP41-S, DP25B-S
0 to 30 psi	0 to 2.1 bar	PX35D0-030GV	DP41-S, DP25B-S
0 to 50 psi	0 to 3.4 bar	PX35D0-050GV	DP41-S, DP25B-S
0 to 100 psi	0 to 6.9 bar	PX35D0-100GV	DP41-S, DP25B-S
0 to 200 psi	0 to 13.8 bar	PX35D0-200GV	DP41-S, DP25B-S
0 to 300 psi	0 to 20.7 bar	PX35D0-300GV	DP41-S, DP25B-S
0 to 500 psi	0 to 34.5 bar	PX35D0-500GV	DP41-S, DP25B-S
0 to 1000 psi	0 to 68.9 bar	PX35D0-1KGV	DP41-S, DP25B-S
0 to 2000 psi	0 to 138 bar	PX35D0-2KGV	DP41-S, DP25B-S
0 to 3000 psi	0 to 207 bar	PX35D0-3KGV	DP41-S, DP25B-S
0 to 5000 psi	0 to 345 bar	PX35D0-5KGV	DP41-S, DP25B-S
0 to 10,000** psi	0 to 689 bar	PX35S0-10KGV	DP41-S, DP25B-S
0 to 15,000** psi	0 to 1034 bar	PX35S0-15KGV	DP41-S, DP25B-S***
0 to 20,000** psi	0 to 1379 bar	PX35S0-20KGV	DP41-S, DP25B-S***
0 to 30,000** psi	0 to 2069 bar	PX35S0-30KGV	DP41-S, DP25B-S*

Comes complete with 5-point calibration.

* Visit omega.com for compatible meters. ** $\frac{9}{16}$ -18, $\frac{1}{4}$ " HP tube fitting.

*** 4-digit meter; counts in increments of 10.

To order sealed gage pressure models, replace "G" in model number with "S" (no extra charge). To order absolute pressure models, replace "G" in model number with "A" (no extra charge).

Ordering Example: PX35D0-3KSV, 3000 psi sealed gage pressure transducer.

METRIC MODELS

To Order Visit omega.com/pxm35 for Pricing and Details

Models with G 1/4 Female Pressure Connection, Integral Connector & mV/V Output

RANGE		MODEL NO.	COMPATIBLE METERS*
0 to 1 bar	0 to 15 psi	PXM35MD1-001BARGV	DP41-S, DP25B-S
0 to 1.60 bar	0 to 23 psi	PXM35MD1-1.60BARGV	DP41-S, DP25B-S
0 to 2.50 bar	0 to 36 psi	PXM35MD1-2.50BARGV	DP41-S, DP25B-S
0 to 4 bar	0 to 58 psi	PXM35MD1-004BARGV	DP41-S, DP25B-S
0 to 6 bar	0 to 87 psi	PXM35MD1-006BARGV	DP41-S, DP25B-S
0 to 10 bar	0 to 145 psi	PXM35MD1-010BARGV	DP41-S, DP25B-S
0 to 16 bar	0 to 232 psi	PXM35MD1-016BARGV	DP41-S, DP25B-S
0 to 25 bar	0 to 363 psi	PXM35MD1-025BARGV	DP41-S, DP25B-S
0 to 40 bar	0 to 580 psi	PXM35MD1-040BARGV	DP41-S, DP25B-S
0 to 60 bar	0 to 870 psi	PXM35MD1-060BARGV	DP41-S, DP25B-S
0 to 100 bar	0 to 1450 psi	PXM35MD1-100BARGV	DP41-S, DP25B-S
0 to 160 bar	0 to 2321 psi	PXM35MD1-160BARGV	DP41-S, DP25B-S
0 to 250 bar	0 to 3626 psi	PXM35MD1-250BARGV	DP41-S, DP25B-S
0 to 400 bar	0 to 5802 psi	PXM35MD1-400BARGV	DP41-S, DP25B-S

Comes complete with 5-point calibration. * Visit omega.com for compatible meters.

To order sealed gage pressure models, replace "G" in model number with "S" (no extra charge). To order absolute pressure models replace "G" in model number with "A" (no extra charge).

Ordering Examples: PXM35MD1-010BARSV, 10 bar sealed gage pressure transducer. PXM35MD1-001BARAV, 1 bar absolute (relative) pressure transducer.

METRIC
PXM35D0-200AV
shown actual size.



omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters