

HIGH-ACCURACY FULL BRIDGE OUTPUT PRESSURE TRANSDUCER

PX931 Series
 0-10 to 0-7500 psi
 0-0.70 to 0-517 bar

Starts at
\$530




PX931-3KSV, \$530, shown smaller than actual size.

- ✓ Rugged Stainless Steel Case Protects Components in Industrial Environments
- ✓ Connects to a PT06F-10-6S Connector for Easy Field Connections
- ✓ Stainless Steel Diaphragm Welded for Compatibility with Most Media
- ✓ Uses a Standard 10 Vdc Regulated Power Supply for Maximum Versatility
- ✓ 1/4 NPT Process Fitting for Fast, Easy, and Secure Installation
- ✓ Excellent Temperature Stability
- ✓ Units 100 psi and Below are Vented Gage for High Precision

Thermal Zero Effect: ±0.005% FS/°F
Thermal Sensitivity Effect: ±0.005% rdg/°F
Proof Pressure: 150% of range
Burst Pressure: 300% of range
Body Material: 17-4 PH stainless steel, hermetically sealed

Diaphragm Material: 17-4 PH SS
Pressure Port: 1/4-18 NPT
Male Thread: 10 to 1000 psi
Female Thread: 3000 to 7500 psi
Mating Connector: PT06F-10-6S (not included)
Pressure Cavity Volume: 0.171 in³
Weight: 290 g (10 oz)



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)				
RANGE		MODEL NO.	PRICE	COMPATIBLE METERS*
0 to 10 psi	0 to 0.69 bar	PX931-010GV	\$560	DP41-S, DP25B-S, DP3002-S
0 to 25 psi	0 to 1.72 bar	PX931-025GV	560	DP41-S, DP25B-S, DP3002-S
0 to 50 psi	0 to 3.4 bar	PX931-050GV	530	DP41-S, DP25B-S, DP87
0 to 100 psi	0 to 6.9 bar	PX931-100SV	530	DP41-S, DP25B-S, DP87
0 to 200 psi	0 to 13.8 bar	PX931-200SV	530	DP41-S, DP25B-S, DP3002-S
0 to 500 psi	0 to 34.5 bar	PX931-500SV	530	DP41-S, DP25B-S, DP87
0 to 1000 psi	0 to 68.9 bar	PX931-1KSV	530	DP41-S, DP25B-S, DP87
0 to 3000 psi	0 to 207 bar	PX931-3KSV	530	DP41-S, DP25B-S, DP41-S
0 to 5000 psi	0 to 345 bar	PX931-5KSV	530	DP41-S, DP25B-S, DP87
0 to 7500 psi	0 to 517 bar	PX931-7.5KSV	530	DP41-S, DP25B-S, DP87

SPECIFICATIONS

Excitation: 10 Vdc (15 Vdc max) @ 30 mA
Output: 30 mV ±0.25% @ 10 Vdc
Sensitivity: 3 mV/V
Input Impedance: 350 Ω min
Output Resistance: 350 ±5 Ω
Insulation Resistance: >5 MΩ @ 75 Vdc
Accuracy: 0.15%
Hysteresis: ±0.10%
Repeatability: ±0.05%
Zero Balance: ±1.0%
Shunt Calibration: 59 kΩ
Operating Temperature Range: -73 to 163°C (-100 to 325°F)
Compensated Temperature Range: 16 to 71°C (60 to 160°F)

Comes with 5-point calibration.
 * See section D for compatible meters.
 Absolute ranges available. Change "G" to "A" in model number, add \$25.
Ordering Examples: PX931-500SV, 500 psi sealed gage pressure transducer, \$530.
 PX931-025GV, 25 psi gage pressure transducer, \$560. PT06F-10-6S, mating connector (sold separately), \$26.50.

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
ES-2070	\$210	Reference Book: Hazardous Materials Handbook

MILLIVOLT OUTPUT PRESSURE TRANSDUCERS **B**

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters