

2-WAY GENERAL PURPOSE SOLENOID VALVES



SV120 Series

Starts at
\$85



SV121, \$85, shown close to actual size.

- ✓ Stainless Steel Valve Body Resists Corrosion
- ✓ Rugged NEMA 4 (IP65) Housing
- ✓ Mounts in Any Position
- ✓ Rated for Continuous Duty
- ✓ High-Pressure Models

TYPICAL APPLICATIONS

- ✓ Automation
- ✓ Humidifiers
- ✓ Water Treatment
- ✓ Dispensing
- ✓ Laundry, Dry Cleaning Equipment
- ✓ Machine Tools
- ✓ Vending Machines

The direct-acting SV121 to SV127 solenoid valves consist of a coil, plunger, and sleeve assembly. In a normally closed state, a plunger return spring holds the plunger against the orifice, preventing flow through the valve. When current flows through the coil, a magnetic field is produced and it turns the stop into an electromagnet that attracts the magnetic plunger. This action compresses the return spring, allows the body orifice to open, and permits fluid flow through the valve. The pressure and flow capabilities of the direct-acting valves are limited by the power of the solenoid.

The SV128 is a pilot-operated solenoid valve. It uses the energy stored in the pressurized fluid to actuate the valving mechanism. The valves require the minimum pressure differential specified for proper valve operation. A direct-acting solenoid valve is an integral part of the pilot-operated valve and is used to affect the balance of pressure above and below a diaphragm or piston.



SV126, \$105, shown close to actual size.



DIRECT-ACTING OR PILOT-OPERATED SOLENOID VALVES, NORMALLY CLOSED, STAINLESS STEEL VALVE BODY

Note: 5 to 11 psi is the operating pressure range for bubble-tight sealing. Valves may leak if the pressure differential falls below 5 psi.

SPECIFICATIONS

Operation:

SV121 to SV127: Direct acting
SV128: Pilot operated

Wetted Parts: Stainless steel, copper and seal

Medium: Liquid or gases



Max Static Pressure: 1.5 times max psid, vacuum (>5 microns ABS)

Ambient Temp: -9 to 50°C (15 to 122°F)

Mounting: Pipe mounting, any direction

Power: 10 W, 120 Vac coils, 50 to 60 Hz

Weight: 500 g (1.1 lb)



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

MODEL NO.	PRICE	NPT FITTING	ORIFICE	C _v	SEAL	DIFF PRESSURE (psid)		TEMP		RESPONSE TIME	
						MIN	MAX	°C	(°F)	OPEN	CLOSE
SV121	\$85	1/4	3/64	0.06	KEL-F	0	1000	74	(165)	4 to 15 ms	4 to 15 ms
SV122	105	1/4	3/64	0.06	FKM	0	450	116	(240)	4 to 15 ms	4 to 15 ms
SV123	105	1/4	1/16	0.10	FKM	0	350	116	(240)	4 to 15 ms	4 to 15 ms
SV124	105	1/4	3/32	0.18	FKM	0	275	116	(240)	4 to 15 ms	4 to 15 ms
SV125	105	1/4	1/8	0.28	FKM	0	200	116	(240)	4 to 15 ms	4 to 15 ms
SV126	105	1/4	5/32	0.40	FKM	0	90	116	(240)	4 to 15 ms	4 to 15 ms
SV127	105	1/4	1/4	0.75	FKM	0	40	116	(240)	4 to 15 ms	4 to 15 ms
SV128*	235	1/4	1/4	0.76	PTFE	5	1500	99	(210)	30 to 60 ms	30 to 60 ms

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
SVCOIL-110AC	\$45	Replacement coil, 110 Vac
SVCOIL-220AC	50	Replacement coil, 220 Vac
SVCOIL-24VDC	50	Replacement coil, 24 Vdc
GE-2317	131	Reference Book: Valve Handbook

* Pilot operated.

Note: Some solenoid valves are available with 24 Vdc coils. Five piece minimum order. UL approval is not available with 24 Vdc coils. Specifications effected; pressure ratings may decrease; coil wattage ratings may increase. Consult Engineering.

Ordering Examples: SV121, direct-acting stainless steel normally closed valve with 3/64 orifice and KEL-F seal, \$85.

SV128, pilot operated stainless steel normally closed valve with 1/4 orifice and PTFE seal, \$235.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters