

SOCKET EXTENSION REACTION TORQUE SENSORS

WITH 1/4, 3/8, 1/2, AND 3/4" SQUARE DRIVES

TQ103 Series

All Models
\$775



TQ103-125 torque sensor, \$775, shown close to actual size.


- ✓ Ideal for Use with Drive/Socket Systems to Monitor or Verify Bolt Torque
- ✓ Measures Torque in Clockwise and Counterclockwise Directions
- ✓ Compact, Low Cost, and Accurate
- ✓ Easily Inserted Between Socket and Drive
- ✓ Rugged Construction for Industrial Applications

The OMEGA® TQ103 Series socket extension torque sensors are installed between a socket and drive to measure or verify bolt torque. These sensors can measure torque in both clockwise and counterclockwise directions. Their accuracy, cost, and size make them ideal for a variety of industrial and laboratory applications.



Dimensions: inches

MODEL NO.	A, IN.	B, IN.
TQ103-25	3.0	1/2 Dia.
TQ103-50	3.0	1/2 Dia.
TQ103-125	3.0	1/2 Dia.
TQ103-200	3.0	11/16 Dia.
TQ103-600	3.0	11/16 Dia.
TQ103-1.5K	3.5	7/8 Dia.
TQ103-2.4K	3.5	7/8 Dia.
TQ103-6K	5.0	1 1/2 Dia.



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

MODEL NO.	PRICE	RANGE (in-lb)	DRIVE	RANGE OUTPUT (mV/V)	COMPATIBLE METERS*
TQ103-25	\$775	0 to 25	1/4"	1.0	HHP-SG, DP25B-S, DP41-S
TQ103-50	775	0 to 50	1/4"	2.0	HHP-SG, DP25B-S, DP41-S
TQ103-125	775	0 to 125	1/4"	2.0	HHP-SG, DP25B-S, DP41-S
TQ103-200	775	0 to 200	3/8"	1.5	HHP-SG, DP25B-S, DP41-S
TQ103-600	775	0 to 600	3/8"	3.0	HHP-SG, DP25B-S, DP41-S
TQ103-1.5K	775	0 to 1500	1/2"	3.0	HHP-SG, DP25B-S, DP41-S
TQ103-2.4K	775	0 to 2400	1/2"	3.0	HHP-SG, DP25B-S, DP41-S
TQ103-6K	775	0 to 6000	3/4"	3.0	HHP-SG, DP25B-S, DP41-S

* The HHP-SG is a standard handheld meter; DP25B-S and DP41-S are panel meters. See section D for compatible meters.

Comes with complete operator's manual.

Ordering Example: TQ103-125, socket extension torque sensor for 1/4" drive ratchet, with 0 to 125 in-lb range, HHP-SG, handheld strain gage indicator (page F-141), \$775 + 575 = \$1350.

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
CM-4365	\$160	Reference Book: Actuator Saturation Control

SPECIFICATIONS

Rated Output: 1 to 3 mV/V (see chart)

Excitation: 10 Vdc, 20 Vdc maximum

Accuracy: ±0.37% FS

Linearity: ±0.25% FS

Hysteresis: ±0.25% FS

Repeatability: ±0.1% FS

Zero Balance: ±0.1% FS

Operating Temperature Range:

-54 to 121°C (-65 to 250°F)

Compensated Temperature Range:

21 to 76°C (70 to 170°F)

Thermal Effects:

Zero: 0.002% FS/°F

Span: 0.002% rdg/°F

Maximum Load: 150% FS, safe; 300% FS, ultimate

Bridge Resistance: 1000 Ω

Angular Deflection at FS: 3°

Construction: Alloy steel

Electrical: 0.6 m (2') of 4-conductor, shielded, color-coded cable with pigtail termination

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters