


Transition Adaptors

ANSI color code shown To order IEC color code see page A-9

All shown smaller than actual size



- ✔ Rugged, One-Piece Molded Construction
- ✔ ANSI or IEC[†] Color-Coded
- ✔ For Use with a Variety of Meters and Probes

TAS adaptors provide quick and easy connections between standard and miniature connector systems. These color-coded units are available in all thermocouple calibrations including Tungsten-Rhenium alloys. Any combination of male and female contacts for miniature and standard positions of the adaptor are available. The TAS-U-5, TAS-U-6 and TAS-U-7 are only available in uncompensated calibration.

MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)		
Model No. ANSI Color Code	Description	Price
TAS-(*)-1	Male standard to male mini	\$5.00
TAS-(*)-2	Female standard to male mini	5.00
TAS-(*)-3	Male standard to female mini	5.00
TAS-(*)-4	Female standard to female mini	5.00
TAS-U-5	Male banana plug to female mini	5.00
TAS-U-6	Sheathed banana plug to banana plug	5.00
TAS-U-7	Sheathed banana plug to banana plug set	5.00

PATENTED

Covered by U.S. and International Patents and Pending Applications

For connector dimensions, please see pages G-71 to G-74

*Specify Calibration: J, K, T, E, R/S or U (uncompensated). May be ordered with G, C, or D calibration, add \$1.50 to price (models 1 and 3 not available) for a total of \$9.50. Add \$4.00 to price for N calibration for a total of \$12.00.

Ordering Example: TAS-K-2, adaptor for type K thermocouples with female connection on the standard end and male connection on the miniature end, \$5.00

[†]add suffix "-IEC" for IEC color code





Round Terminal Blocks

- ✔ ANSI or IEC[†] Color-Coded
- ✔ Allows Single or Dual Wire Pair Connection
- ✔ Rugged Glass-Filled Nylon Terminal Block Construction
- ✔ -29 to 220°C (-20 to 425°F) Temperature Rating
- ✔ Fits 1.5 to 6 mm (1/16 to 1/4") Probes, Tubes and Cable Sheaths

OMEGA's color-coded CH series terminal blocks are designed to fit metal-sheathed cable or probes between 1.5 and 6 mm (1/16 and 1/4") in diameter. The CH terminal blocks use a 1/8 NPT compression fitting to adapt to probes or cables (sold separately; please see page A-131).

Terminal block diameter: 31.7 mm (1.25")
thickness: 9.7 mm (0.38")

Shown actual size



MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model No.)		
Model No. ANSI Color Code	# Terminals	Price
CH62-(*)	2	\$3.25
CH63-(*)	3	3.50
CH64-(*)	4	3.75

*Insert calibration code: J, K, T, E or S, for thermocouple type desired, or U for uncompensated lugs.

Ordering Example: CH62-K, two-position round terminal block, type K, \$3.25.

[†]add suffix "-IEC" for IEC color code

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters