

# Smart Powered Strain Bridge/ Load Cell Conditioner

## TXDIN1600s

- ✓ Suitable for load cell / strain gauge applications
- ✓ Universal current, bipolar voltage outputs
- ✓ Input range (0.2 to 7.5) mv/v, 5 v excitation
- ✓ Powered ( 10 to 32) v ac or (10 to 48) v dc supply
- ✓ (2 to 6) point calibration with active set option
- ✓ Remote tare, front panel push button configuration
- ✓ USB programmable




The TXDIN1600s is a “smart” powered bridge amplifier for use with strain gauges or load cell signals. The product has a built in capability to scale the input signal to a process value while the output stage offers either voltage, bipolar voltage or active / passive current re-transmission signals.

The TXDIN1600s comes with an AC/DC power supply that will operate in the range (10 to 48) V DC and (10 to 32) V AC making the device ideal for battery operation. An additional volt free contact input is available for tare setting using a remote switch. The high precision input stage of the device allows for a bridge excitation voltage of 5V DC to be used as opposed to the traditional 10V DC. This reduces the power requirement for the bridge supply and up to four bridges (cells) may be connected to the input.

The device is provided with two front panel push buttons that can be configured to perform one of two functions or be disabled. Set as function 1, the buttons allow the user to push button configure the output range at high and low scale against a live input signal, set as function 2, the buttons allow the operator to trim the output at high and low scale. The device uses ratio metric measurement to obtain high stability.

The product uses a USB port for configuration, together with a simple to use menu driven software configuration tool, allowing the user to take advantage of the product’s comprehensive specification. Additionally, the user may read live process data when connected to the PC, allowing for offset and span calibration.

If configuration is not specified at the time of order, the product will be shipped with the default range 2 mV/V input (4 to 20) mA output.



## Specifications

### BRIDGE INPUT

**Full Range:** (-7.6 to 7.6) mV/V (-38 to 38) mV @ 5V excitation

**Type:** Four Wire radiometric

**Drift:**  $< \pm 0.05\%$

**Linearity:**  $\pm 0.01\%$

**Update:** Selectable, 10 or 80 SPS (Samples per second)

### BRIDGE EXCITATION

**Voltage:** 5 Volts DC  $\pm 0.1\text{ V}$  @ 59 mA

**Bridge Impedance:** Total (85 to 10000)  $\Omega$  (operates with four 350  $\Omega$  cell in parallel)

### TARE INPUT

**Type:** Remote volt free contact, up to 10 metres distance

### OUTPUT CURRENT

**Current Source:** Range (0 to 21.5) mA , Max Load 750  $\Omega$

**Current Sink:** Range (0 to 21.5) mA , Supply (10 to 30) V dc, Voltage effect 0.2 uA/V

**Accuracy:** (mA Out/ 2000) or 5 uA which ever is the greater, Drift 1 uA/ $^{\circ}\text{C}$

### OUTPUT VOLTAGE

**Range:** (0 to 10.1) V or (-10.1 to 10.1) V, Accuracy  $\pm 5\text{ mV}$

**Current Drive:**  $\pm 2\text{ mA}$ , Min load 5000  $\Omega$  @ 10 V

### PUSH BUTTON CONFIGURATION

**Type:** Independent "low" "High" front panel push buttons allow user to manually set low and high output points.

### SUPPLY

**Range:** (10 to 48) VDC , (10 to 32) VAC Protected by internal 500 mA resettable fuse.

**Power:**  $< 1\text{ W}$  Full Power

### GENERAL

**Isolation:** Supply to input to output 500 V dc.

**Indication:** LED, Green when output (-0.1 to 100.1) %, else red

### USER INTERFACE

**Type:** USB 2.0

**Baud rate:** 19,200 baud

**Equipment:** PC running windows XP or later, USB cable.

### USER INTERFACE FUNCTIONS

**Calibration Scaling:** (2 to 6) points signal against process

**Filter:** (1 to 20) Seconds to reach 70 % of final value

**Tare:** Remote set tare offset with programmable user set point.

**Active Calibration:** Active Calibration against live load cell

**Process Units:** 4 Characters

**Tag Number:** 20 Characters

**Process Output:** Process Output Range

**Signal Output:** Select type, signal range

**Active scaling output:** Set output process range against active sensor input

**Sensor Information:** Model, sensitivity and balance

### ENVIRONMENT

**Operating Ambient:** (-30 to 70)  $^{\circ}\text{C}$  ; (10 to 90) %RH (non condensing)

**Storage Ambient:** (-30 to 70)  $^{\circ}\text{C}$  ; (10 to 90) %RH (non condensing)

**Configuration Ambient:** (10 to 30)  $^{\circ}\text{C}$

**Installation Enclosure:** DIN Rail enclosure offering Protection  $\geq$  IP65.


### APPROVALS

**CE:** BS EN 61326

### MECHANICAL

**Style:** DIN 43880, Colour grey, material Polyimide 6.6, weight  $< 70\text{ grams}$

**Terminals:** 2.5 mm Maximum



**AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)	
Model No.	Description
TXDIN1600s	DIN-Rail Mount Load-Cell Transmitter

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters