

Leaf Surface Probes For Instant Measurement of Flat Surfaces

88L40K
\$75



ANSI color code shown
To order IEC color code see page A-9


- ✓ Measures 0 to 300°C (32 to 572°F)
- ✓ Type K Thermocouple
- ✓ Accuracy ±2°C (±4°F)
- ✓ Fast Response <5 Sec
- ✓ 40 and 75 mm (1.5 and 3") Lengths



88L75K, \$75, shown smaller than actual size.

Supplied with

- ✓ Coiled Cord — 25 mm (1') Stretches to Over 1.5 m (5')
- ✓ Protective Leaf Cover
- ✓ Ergonomic Handle
- ✓ SMPW Miniature Connector with Mating Connector or TAS with Clip and Clamp



These unique leaf style surface probes are designed for instant measurement of temperature on flat surfaces.

Their ultra low thermal mass and flexible construction make them ideal for rugged industrial applications. Their Type K thermocouple is compatible with all standard handheld digital thermometers.

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

| Model No. | Price | Max Temperature | A Dimension | Applications |
|-----------|-------|-----------------|--------------|---------------------|
| 88L40K | \$75 | 300°C (572°F) | 40 mm (1.5") | Type K Thermocouple |
| 88L75K | 85 | 300°C (572°F) | 75 mm (3") | For flat surfaces |

Response time for probes is under 5 seconds. Probes come with a protective cover and a coiled cable that stretches to 1.5 m (5') and a miniature Type K connector.

Ordering Example: 88L75K 75 mm Leaf probe, \$85.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters