

1/8 DIN Vertical Temperature Controllers



Panel punches available, visit omega.com/panelpunches

CN710 Series
\$98
All Models



- ✓ Dual Display
- ✓ Autotune
- ✓ RS485 Communications
- ✓ Free Software
- ✓ Alarm Functions
- ✓ Thermocouple/RTD Inputs
- ✓ Output Status

The CN710 Series temperature controllers offer easy-to-use programming menus designed for quick installation. These units are designed for direct or reverse acting (cooling or heating) control. The CN710 Series can be programmed for simple ON/OFF or more complex PID control functions. PID control is supported with manual or auto-tuning. Select relay, DC pulse, or current output control methods. The controller also includes two additional alarm outputs. The alarm outputs can be configured from 12 different preprogrammed settings. The temperature controller accepts a variety of thermocouple and RTD inputs. The process value and setpoint value are displayed simultaneously on the large dual LED. Auto-tuning, engineering units (°F or °C) and alarm status is also indicated on the faceplate.

Specifications

Inputs: Thermocouple and RTD (see chart)

Display: Two 4-digit, 7-segment 9.53 mm H (0.38") LEDs

PV: Red
SV: Green

Accuracy: ±0.25% span, ±1 least significant digit

Supply Voltage: 100 to 240 Vac, 50/60 Hz

Power Consumption: 5 VA max

Operating Temperature: 0 to 50°C (32 to 122°F)

Memory Backup: Nonvolatile memory

Control Output Ratings:

Relay: SPDT, 5 A @ 250 Vac resistive
Voltage Pulse: 14V, 10 to -20% (max 40 mA)
Current: 4 to 20 mA
Communication: RS485 MODBUS® communication protocol
Weight: 425 g (15 oz)
Panel Cut-Out: 92 x 46 mm (3.6 x 1.8")
Maximum Panel Thickness: 9.50 mm (0.375")
Panel Depth: 79.2 mm (3.125")
Front Panel Rating: IP66



CN713, \$98, shown smaller than actual size.

| Input Types | Range |
|----------------------------|--|
| Pt100Ω RTD | 0 to 100°C (32 to 212°F) -20 to 500°C (-4 to 932°F) -200 to 600°C (-328 to 1112°F) |
| Thermocouple Type B | 100 to 1800°C (212 to 3272°F) |
| Thermocouple Type S | 0 to 1700°C (32 to 3092°F) |
| Thermocouple Type R | 0 to 1700°C (32 to 3092°F) |
| Thermocouple Type N | -200 to 1300°C (-328 to 2372°F) |
| Thermocouple Type E | 0 to 600°C (32 to 1112°F) |
| Thermocouple Type T | -20 to 400°C (-4 to 752°F) -200 to 400°C (-328 to 752°F) |
| Thermocouple Type J | -20 to 400°C (-4 to 752°F) -100 to 850°C (-148 to 1562°F) |
| Thermocouple Type K | -200 to 1300°C (-328 to 2372°F) -200 to 500°C (-328 to 932°F) |
| Thermocouple Type L | -200 to 500°C (-328 to 932°F) |
| Thermocouple Type U | -200 to 800°C (-328 to 1472°F) |

IN STOCK FOR FAST DELIVERY!

To Order (Specify Model Number)

| Model No. | Price | Description |
|--------------|-------------|--|
| CN713 | \$98 | Relay output with RS485 communications* |
| CN712 | 98 | DC pulse output with RS485 communications* |
| CN715 | 98 | 4 to 20 mA output with RS485 communications* |

Accessories (Field Installable)

| Model No. | Price | Description |
|----------------------|------------|---------------------------------------|
| CNQUENCHARC | \$8 | Noise suppression kit, 110 to 230 Vac |
| DPP-5 | 525 | 1/8 DIN panel punch |
| CN7-485-USB-1 | 82 | RS485 to USB mini-node converter |
| GE-2117 | 23 | Reference Book: Controller Tuning/PID |

* Free CN7-A software download available at omega.com/cn710

Comes complete with operator's manual.

Ordering Example: CN713, single output controller, mechanical relay, RS485 communications, \$98.



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters