


Models A and R

Model A or R
\$52
 With 6" Stem



All of Stainless Steel (except dial). Hermetically sealed. Model A has external pointer reset.



Shown smaller than actual size.

Ranges and °Divisions

Fahrenheit		Celsius	
Range	Div	Range	Div
-100 to 100°F	2°	-50 to 200°C	2°
-80 to 120°F	2°	-50 to 100°C	2°
-40 to 160°F	2°	-50 to 50°C	1°
-20 to 120°F	2°	-40 to 70°C	1°
*0 to 100°F	1°	-40 to 160°C	2°
0 to 140°F	2°	*-30 to 30°C	1°
*25 to 125°F	1°	-20 to 120°C	2°
0 to 150°F	1°	-10 to 110°C	1°
0 to 200°F	2°	*0 to 50°C	½°
0 to 220°F	2°	0 to 100°C	1°
0 to 250°F	2°	0 to 150°C	1°
0 to 300°F	2°	0 to 200°C	2°
20 to 240°F	2°	0 to 300°C	2°
-50 to 300°F	5°	0 to 400°C	5°
50 to 300°F	2°	100 to 500°C	5°
50 to 400°F	5°	-80 to 220°C	5°
50 to 500°F	5°	*0 to 60°C	5°
50 to 550°F	5°	0 to 250°C	5°
50 to 750°F	10°	100 to 550°C	5°
100 to 800°F	10°		
150 to 750°F	10°		
200 to 1000°F	10°		
250 to 600°F	10°		
-100 to 200°F	10°		
-70 to 150°F	10°		

* Minimum stem length 4".

MOST POPULAR RANGES HIGHLIGHTED!

Dual Range	
°C (°F)	Div
-50 to 100°C (-50 to 210°F)	5°/2°
-70 to 40°C (-100 to 100°F)	2°/1°
-5 to 50°C (*25 to 125°F)	1°/1°
-40 to 70°C (-40 to 160°F)	2°/1°
-10 to 90°C (0 to 200°F)	2°/1°
-20 to 120°C (0 to 250°F)	2°/2°
10 to 150°C (50 to 300°F)	2°/2°
10 to 260°C (50 to 500°F)	5°/5°
10 to 290°C (50 to 550°F)	5°/5°
70 to 400°C (150 to 750°F)	10°/5°
100 to 150°C (200 to 1000°F)	10°/5°
-20 to 70°C (0 to 150°F)	10°/5°
-10 to 115°C (20 to 240°F)	10°/5°
10 to 200°C (50 to 400°F)	10°/5°
100 to 500°C (200 to 1000°F)	10°/5°

To order A and R, specify*:
Model - Range - Stem Length - Mounting
Ordering Example: A-0-250F-9-1/2, model A with 0 to 250°F range, 9" stem and 1/2 NPT bushing, \$55.


* For stem lengths, pricing, see page E-19.

Models B and S

Model S
\$75
 With 6" Stem



All of Stainless Steel (except dial). Hermetically sealed. Model B has external pointer reset.



Dual Ranges are Available! Consult Sales for Information.



Shown smaller than actual size.

Ranges and °Divisions

Fahrenheit		Fahrenheit	
Range	Div	Range	Div
-100 to 100°F	2°	-50 to 300°F	5°
-80 to 120°F	2°	50 to 300°F	5°
-40 to 160°F	2°	50 to 400°F	5°
*-20 to 120°F	2°	50 to 500°F	5°
*0 to 100°F	2°	50 to 550°F	5°
0 to 140°F	2°	50 to 750°F	5°
*25 to 125°F	5°	100 to 800°F	10°
0 to 150°F	2°	150 to 750°F	10°
0 to 200°F	2°	200 to 1000°F	10°
0 to 220°F	5°	-100 to 200°F	10°
0 to 250°F	5°	-70 to 150°F	10°
0 to 300°F	5°	200 to 300°F	10°
20 to 240°F	5°	300 to 400°F	10°

* Minimum stem length 4".

MOST POPULAR RANGES HIGHLIGHTED!

Celsius		Celsius	
Range	Div	Range	Div
-50 to 200°C	1°	0 to 200°C	2°
-50 to 100°C	1°	0 to 300°C	5°
-50 to 50°C	1°	0 to 400°C	5°
-40 to 70°C	1°	100 to 500°C	5°
-40 to 160°C	1°	-80 to 220°C	5°
*-30 to 30°C	1°	-20 to 220°C	5°
-20 to 120°C	1°	*0 to 30°C	5°
-10 to 110°C	1°	*0 to 60°C	5°
*0 to 50°C	1°	0 to 250°C	5°
0 to 100°C	1°	50 to 450°C	5°
0 to 150°C	2°	100 to 550°C	5°

To order B and S, specify*:
Model - Range - Stem Length - Mounting
Ordering Example: B-50-300F-9-1/2, model B with 50 to 300°F range, 9" stem and 1/2 NPT bushing, \$81.

* For stem lengths, pricing, see page E-19.



Models X, XR, V and VR

Heads: X, XR: 3" O.D.
V, VR: 5" O.D.

Normally supplied with 1/2" NPT Mounting;
1/4" NPT or 3/4" NPT Thread Optional.
Made Entirely of Stainless Steel,
Hermetically Sealed.

X, XR, V and VR
Ranges and °Divisions





**MOST POPULAR
RANGES HIGHLIGHTED!**

Fahrenheit		Celsius		Dual Range			
Range	Div	Range	Div	°F	Div.	°C	Div
-100 to 100°F	2°	-50 to 200°C	2°	-50 to 210°F	5°	-50 to 100°C	2°
-80 to 120°F	2°	-50 to 100°C	2°	-100 to 100°F	2°	-70 to 40°C	1°
-40 to 160°F	2°	-50 to 50°C	1°	*25 to 125°F	1°	-5 to 50°C	1°
-20 to 120°F	2°	-40 to 70°C	1°	-40 to 160°F	2°	-40 to 70°C	1°
*0 to 100°F	1°	-40 to 160°C	2°	0 to 200°F	2°	-10 to 90°C	1°
0 to 140°F	2°	*-30 to 30°C	1°	0 to 250°F	2°	-20 to 120°C	2°
*25 to 125°F	1°	-20 to 120°C	2°	50 to 300°F	2°	10 to 150°C	2°
0 to 150°F	1°	-10 to 110°C	1°	50 to 500°F	5°	10 to 260°C	5°
0 to 200°F	2°	*0 to 50°C	1/2°	50 to 550°F	5°	10 to 290°C	5°
0 to 220°F	2°	0 to 100°C	1°	150 to 750°F	10°	70 to 400°C	5°
0 to 250°F	2°	0 to 150°C	1°	200 to 1000°F	10°	100 to 500°C	5°
0 to 300°F	2°	0 to 200°C	2°	0 to 150°F	10°	-20 to 70°C	5°
20 to 240°F	2°	0 to 300°C	2°	20 to 240°F	10°	-10 to 115°C	5°
-50 to 300°F	5°	0 to 400°C	5°	50 to 400°F	10°	10 to 200°C	5°
50 to 300°F	2°	100 to 500°C	5°	**200 to 1000°F	10°	100 to 550°C	5°
50 to 400°F	5°	-80 to 220°C	5°				
50 to 500°F	5°	†-20 to 220°C	5°				
50 to 550°F	5°	*0 to 30°C	5°				
50 to 750°F	10°	*0 to 60°C	5°				
100 to 800°F	10°	0 to 250°C	5°				
150 to 750°F	10°	†50 to 450°C	5°				
200 to 1000°F	10°	100 to 550°C	5°				
**250 to 600°F	10°						
-100 to 200°F	10°						
-70 to 150°F	10°						
†200 to 300°F	10°						
‡300 to 400°F	10°						



* Minimum stem length 4".
** Range available in X and XR models only.
† Range available in V and VR models only.

Model XR With
Reset Screw
\$86
With 6" Stem



Dimensions: in

Model VR With
Reset Screw
\$116
With 6" Stem




To order X, XR, V and VR, specify*:
Model - Range - Stem Length - Mounting
Ordering Example: XR-0-100F-6-1/2, model XR with
0 to 100°F range, 6" stem and 1/2 NPT bushing, \$86.
* For stem lengths, pricing, see page E-19.

Thermometers of this design are well adapted to installation on top of tanks, boilers, in high locations or other areas where it would be difficult to read a standard angle-form instrument.

Stems are 1/4" in diameter. Stem lengths up to 36" can be supplied.

Normally supplied with the stem at the BOTTOM (6 o'clock) position, to order special positions add the bolded suffix. These thermometers can be set with the stem protruding at: **"-LEFT"** (9 o'clock), **"-TOP"** (12 o'clock) or **"-RIGHT"** (3 o'clock) positions. If not specified, the standard **BOTTOM** (6 o'clock) position will be supplied.



J-SF, shown smaller than actual size.

Silicone-Filled Thermometers

Silicone-filled thermometers are offered for severe industrial applications, where vibration is a problem. Silicone dampening prolongs instrument life by preventing wear and fatigue in the instrument's internal parts. The silicone also improves readability by reducing pointer flutter, and promotes faster temperature response.

Any Pro/Temp 3" or 5" dial bi-metal thermometer can be silicone filled, in any stem length, and any temperature range up to 500°F. (Silicone filling with ranges over 500°F is not recommended.) All silicone-filled thermometers come with a durable polycarbonate crystal. Also available with Models G and H.

To order Silicon-Filled, specify:
the thermometer per its ordering example and add suffix **"-SF"** to model number.

See accessories and options on page E-18 for pricing.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters