

Compact Benchtop Controllers

Optional Communications Bundled with Free Software


CSC32 Series
Starts at
\$345



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

- ✓ Rugged Metal Benchtop Enclosure
- ✓ 4-Digit Display, 1 or 0.1° Resolution
- ✓ Full Autotune PID Heat-Cool Control
- ✓ Single Ramp and Soak Capability
- ✓ High Accuracy ($\pm 0.25\%$ full scale $\pm 1.5^\circ\text{C}$)
- ✓ Models with Dedicated Thermocouple, RTD, Process Voltage or Current Input
- ✓ Two 5 Amp 120 Vac SSR Outputs Standard
- ✓ Second Output May be Used for Control or One of Five Types of Alarms
- ✓ Optional RS232 or RS485 MODBUS Communications with Free CN9-SW Communications Software and Cable

CN9500 Series Controllers are used in the CSC32 series benchtop units.



CSC32K Benchtop Controller shown with LHM Series Heating Mantle, \$139, (Flask not included), and KMTXL-125G-12 Thermocouple Probe, \$27.95. See page A-45.

The CSC32 series compact benchtop controllers are ideal for laboratory use and applications requiring portable temperature and process control. Pre-wired input and output receptacles in the rear of the case enable quick and easy connections to power, input, power output and digital communications. These benchtop controllers are factory configured and calibrated for a dedicated input type by model number.

The $\frac{1}{2}$ DIN CN9500 controller used in this benchtop controller series can be programmed for either On/Off, or PID Autotune Control (with autotune Feature) via the front panel or through the use of a PC and CN9-SW communications software.

CN9-SW software is designed to interface with the CN9300, CN9400, CN9500 and CSC32 Series benchtop controllers with optional communication hardware. Benefits:

- Time-saving benefit and convenience of remotely configuring and adjusting units.
- Saving and retrieving settings to and from files.
- Highly flexible logging and “real time” charting capability for providing hard copy QA records for ISO-9000 and other management purposes.
- Software is capable of logging readings from up to 128 instruments which it stores in data files.
- The data can be exported into text files in Comma Separated Variable format.
- In addition, up to 12 controllers can be displayed on a single chart, or individual charts can be set up for each instrument.
- A virtual full color chart recorder can log process variables such as: °C, °F, Bar, PSI, pH, rH, or user defined engineering units

Specifications

Power: 115 Vac, $\pm 10\%$, 50/60 Hz
Display: 4-digit LED, 10 mm (0.4"), high brightness green display
Display Range: -199 to 9999 counts (hi-res mode -199.9 to 999.9)
Range: Sensor limited 2000°C/3500°F; -99.9 to 999.9° in 0.1° resolution



CSC32K-C2 Front View

Dimensions:
mm (in)

RJ12, RS232
or RS485
Communications

The Patented
UPJ-K-F Uni-Connector
Accepts Either a Miniature or
Standard Male Connector

Fused Outputs

Dual 5A @ 120 Vac SSR outputs

AC power

CSC32K-C2 Rear View



Graph Displaying Real Time Charting Using CN9-SW Software

Software included
FREE with “C2”
or “C4” options.



Computer screen depicting the internal parameters setup for tuning mode, ramp/soak sequence and security lockouts when using CN9-SW Software. When a satisfactory instrument configuration has been achieved, these settings can be saved to a file for later use or cloned to other instruments on the network.

Display Indicators: Process variable (PV), Setpoint (SP), LED output indicators-flashing
Output 1 (SP1 square), green;
Output 2 (SP2 round), red; error messages, Function/Option mnemonics

Control Modes: PID Autotune, ON/OFF, Direct/Reverse,

Alarm Modes: Deviation high, deviation low, deviation band, full Scale high, or full scale low

Thermocouple External Resistance: 100 Ω max

Thermocouple: See Input and Range Table

Standards: IPTS/68/DIN43710
RTD Input: Pt100 2-wire (.00385)

Linear Process Inputs: mV range: 0 to 50 mV (1 Ω shunt resistor supplied for mA inputs)

Calibration Accuracy: ±0.25% of Full Scale ±1.5°C (±2.7°F)

Sampling Frequency: Input 10 Hz, CJC 2 sec

Common Mode Rejection:

Negligible effect up to 140 dB, 240V, 50 to 60 Hz

Temperature Coefficient: 150 ppm/°C sensor max

Input Connection:

Thermocouple: Accepts both miniature and standard male

Thermocouple Connectors

Note: A miniature and standard size male mating connector is included with each benchtop controller

RTD, mA or mV: Accepts OMEGA® T series model TA3F Keyed-3-pin locking connector

Note: A mating connector is included with each benchtop controller

Outputs: Two solid state relays rated for 5 A @120 Vac (internally, the controller provides two DC pulse outputs to drive a built-in dual solid state relay)

Operating Ambient Range: 0 to 50°C (32 to 130°F)

Benchtop Case Material:

Aluminum

Controller Case: Flame retardant polycarbonate

Power Connection: Std. three prong power cord (provided)

Output Connections: Two standard 120 Vac outlets

Weight: 0.9 kg (2 lbs)

Input and Range Table

Input Code	Input Type	Linearized Range (Units are °C/°F Switchable)	Linearity °C (°F)
J	Iron-Constantan	-0 to 800°C/32 to 1472°F	0.5 (0.9)
K	CHROMEGA®-ALOMEGA®	-50 to -1200°C/-58 to 2192°F	0.25 (4.5)
T	Copper-Constantan	-200 to -250°C/-273 to 482°F	0.25 (4.5)
E	CHROMEGA®-Constantan	0 to 600°C/32 to 1112°F	0.5 (0.9)
R	Pt-13%Rh/Pt	-50 to 40°C/40 to 1768°F	2.0 (3.6)
S	Pt-10%Rh/Pt	0 to 1600°C/32 to 2912°F	2.0 (3.6)
N	OMEGA-P®-OMEGA-N®	-50 to 1200°C/-58 to 2912°F	0.25 (0.45)
RTD	100ΩPt, 2-Wire	-200 to 400°C/-273 to 752°F	0.25 (0.45)
MA	LINEAR CURRENT	0 to 20 mA (-250 to 3000 Max. Scale)	±0.5% (±0.9%)
MV	LINEAR VOLTAGE	0 to 20 mV (-250 to 3000 Max. Scale)	±0.5% (±0.9%)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model Number	Price	Description
CSC32(*)	\$345	Benchtop controller

* Insert Input Code: J, K, T, E, R, S, N, RTD, MV or MA from Input and Range Table
Comes complete with operator's manual, 120 Vac power cord and input connector.

Ordering Example: CSC32K-C2, benchtop controller, Type K input and RS232 communications option, \$345 + 125 = **\$470**. OCW-3 OMEGACARE™ extends standard 1-year warranty to a total of 4 years (\$117), \$470 + 117 = **\$587**.

Communications Options

(Pre-Wired 6' Communications Cable Included)

Suffix	Price	Description
-C2	\$125	RS232 communications bundled with free CN9-SW
-C4	125	RS485 communications bundled with free CN9-SW

Protocol Manual for CN9-SW Software

Model Number	Price	Description
BD9-PROTOCOL*	N/C	MODBUS® Protocol Manual (not required when using the CN9-SW software)

* Note: This protocol manual provides the address information necessary to communicate with the CN9300/CN9400/CN9500 and CSC32 Series, with communications options installed, when interacting with custom or other commercially available software.



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters