



Handheld Fiber Optic Meter

FOH201
\$2650  

- ✓ Measures Temperature, Pressure and Strain
- ✓ Easy to Use
- ✓ High Linearity and Precision
- ✓ 20 Hz Sampling Rate
- ✓ ±5V Analog and RS232 Output Interfaces
- ✓ Windows Software Included
- ✓ Large LCD Display
- ✓ 9V Battery or Wall Transformer-Operated
- ✓ Rugged Case with Rubber Boot Protection

Applications

- ✓ High Voltage Environments
- ✓ EMI, RFI and Microwave Environments
- ✓ Microwave and Food Processing
- ✓ Hazardous Environments
- ✓ Civil Engineering and Geotechnical

The FOH201 is a compact and portable fiber optic handheld meter to be used with OMEGA's interferometric fiber optic sensors, for temperature, pressure, and strain measurements. At the heart of the FOH201 is the white light polarization interferometry (WLPI) technology which is patent pending. This technology provides a means for making accurate and absolute measurements of the path length difference of any type of interferometric fiber optic sensors. The difference varies according to the parameter of interest.

The FOH201 is equipped with a large visible LCD display and can be battery operated. It comes with a standard ±5V analog output and a RS232 communication port for real-time data acquisition. The FOH201 can be controlled directly using the



FOH201, Fiber optic kit, \$2650, shown smaller than actual size.

front-panel keypad or remotely using the standard RS232 interface. A rugged casing with a removable rubber boot provides good mechanical protection against intensive handling in tough environments.

The FOH201 is compatible with all OMEGA WLPI sensors providing a multi-purpose tool for measuring various parameters. With a 20 Hz sampling rate, a ±0.003% full scale resolution, and a ±0.01% full scale precision, the FOH201 delivers the performance needed for a wide range of critical measurement applications.

Specifications

Number of Channels: 1
Measurement Range: -40 to 250°C (-40 to 482°F)
Accuracy: ±1.0°C full scale
Compatibility: All OMEGA WLPI fiber optic sensors

Full Scale: 30,000 nm (path length difference)
Resolution: ±0.003% of FS (no averaging)
Precision: ±0.01% of FS @ ±3.3 sigma limit (99.9% confidence level)
Sampling Rate: 20 Hz standard
Output Interface: ±5V analog and RS232 standard
Operating Mode: Front panel, PC software (included), or RS232 commands
Power: 9V battery or AC adaptor
Enclosure: Plastic casing with removable rubber boot
Dimensions (Without Rubber Boot): 45 H x 105 W x 165 mm L (1.77 x 4.14 x 6.50")
Storage Temperature: -40 to 70°C (-40 to 158°F)
Operating Temperature: 0 to 45°C (32 to 113°F)
Humidity: 95% non-condensing
Light Source Life Span: 40,000-hr MTBF

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
FOH201	\$2650	Fiber optic kit
Accessories		
FOH200-P	\$250	Replacement pressure probe
FOH200-S	155	Replacement strain probe
FOH200-T	295	Replacement temperature probe
FOH200-RS232C	24	Replacement RS232 cable
FOH200-PS	24	Replacement power supply
FOH200-CK	32	Replacement cleaning kit
EE-2517	130	Reference Book: Microwave and Wireless Synthesizers: Theory and Design 

Comes complete with Windows software, RS232C cable, AC adaptor, 9V battery, temperature probe, strain probe, pressure probe, cleaning kit, and operator's manual.
Ordering Example: FOH201, fiber optic kit, \$2650.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters